

SAID-M12S-5-9SMT**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Similar to illustration**

Weidmüller is one of the industry's leading international providers of connectors. An important mainstay in this product family are the circular connectors, which Weidmüller groups under the product name SAI. In the development of SAI products, Weidmüller engineers have always concentrated on achieving rational, cost-effective installation concepts, and – in cooperation with major users – have supplied the markets with well-conceived products which set standards in terms of functionality and quality across the globe. The best examples are the new power distributors with S and T coded M12. These modules are characterised by particularly high currents and voltages. This enables them to also be used, for example, with three-phase motors.

General ordering data

| | |
|------------|--|
| Version | Built-in plugs, M12, Mounting thread: , Number of poles: 5, Strand / cable length: |
| Order No. | 2422600000 |
| Type | SAID-M12S-5-9SMT |
| GTIN (EAN) | 4050118431360 |
| Qty. | 25 items |

SAID-M12S-5-9SMT

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

| | |
|------|---------|
| ROHS | Conform |
|------|---------|

Dimensions and weights

| | |
|------------|--------|
| Net weight | 2.63 g |
|------------|--------|

Environmental Product Compliance

| | |
|--------------------------------------|--------------------------------------|
| RoHS Compliance Status | Compliant with exemption |
| RoHS Exemption (if applicable/known) | 6c |
| REACH SVHC | Lead 7439-92-1 |
| SCIP | 0ea6d931-f9e9-40a6-89d9-8d67103189d3 |

Technical data of PCB plug-in connector

| | | | |
|--|------------------------------|-----------------------|--|
| Number of poles | 5 | Coding | A-coded |
| Housings | M12 pin | Shield connection | No |
| Nominal voltage | 60 V | Rated voltage | 250 V (4-pole) / 60 V (5-pole) / 30 V (8-pole) |
| Nominal current | 4 A | Rated current | 4 A (4- and 5-pole) / 2 A (8-pole) |
| Temperature range | -25...95 °C | Protection degree | IP67 |
| Contact surface | Au (Gold) | Housing main material | LCP |
| Connection thread | M12 | Tightening torque | M12: 0.8 Nm |
| Pollution severity | 3 (2 within the sealed area) | Plugging cycles | ≥ 100 |
| Contact material | Cu-alloy | Lock nut material | Nickel-plated CuZn |
| Material of the flange-mounted housing | Nickel-plated CuZn | | |

General Info

| | | | |
|-----------------------|----------|---------------------------|-----------|
| Number of poles | 5 | UL 94 flammability rating | V-0 |
| Housing main material | LCP | Connection thread | M12 |
| Contact material | Cu-alloy | Contact surface | Au (Gold) |
| Protection degree | IP67 | Plugging cycles | ≥ 100 |

Material data

| | | | |
|---------------------------|-----------|------------------|----------|
| UL 94 flammability rating | V-0 | Contact material | Cu-alloy |
| Contact surface | Au (Gold) | | |

System parameters

| | | | |
|-------------------|------|---------------------|-------|
| Number of poles | 5 | Pin series quantity | 1 |
| Protection degree | IP67 | Plugging cycles | ≥ 100 |

Important note

Notes

Classifications

| | | | |
|----------|----------|----------|----------|
| ETIM 6.0 | EC000438 | ETIM 7.0 | EC003557 |
| ETIM 8.0 | EC003557 | ETIM 9.0 | EC003557 |

SAID-M12S-5-9SMT

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 10.0 | EC003557 | ECLASS 9.1 | 27-44-02-05 |
| ECLASS 10.0 | 27-44-02-23 | ECLASS 11.0 | 27-44-02-23 |
| ECLASS 12.0 | 27-44-02-23 | ECLASS 13.0 | 27-44-02-23 |
| ECLASS 14.0 | 27-44-02-23 | ECLASS 15.0 | 27-44-02-23 |


SAID-M12S-5-9SMT

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany


www.weidmueller.com

Drawings


Dimensioned drawing



PCB design



Pole scheme



M12 = A-coded

SAID-M12S-5-9SMT

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Accessories

Accessories



Weidmüller is one of the industry's leading international providers of connectors. An important mainstay in this product family are the circular connectors, which Weidmüller groups under the product name SAI. In the development of SAI products, Weidmüller engineers have always concentrated on achieving rational, cost-effective installation concepts, and – in cooperation with major users – have supplied the markets with well-conceived products which set standards in terms of functionality and quality across the globe. The best examples are the new power distributors with S and T coded M12. These modules are characterised by particularly high currents and voltages. This enables them to also be used, for example, with three-phase motors.

General ordering data

| | | |
|------------|----------------------------|---|
| Type | SAIFG-M14X1-S-1 | Version |
| Order No. | 2423980000 | Built-in plug housing, M12 pin, Installation height: 9 mm |
| GTIN (EAN) | 4050118432527 | |
| Qty. | 25 ST | |
| Type | SAIE-KMM14X1-SW15 | Version |
| Order No. | 2424010000 | Locknut |
| GTIN (EAN) | 4050118431230 | |
| Qty. | 25 ST | |