

## PAC-HE26-HE26-HF-10M

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)



Similar to illustration

### General ordering data

|            |                                      |
|------------|--------------------------------------|
| Order No.  | 2425740100                           |
| Type       | <a href="#">PAC-HE26-HE26-HF-10M</a> |
| GTIN (EAN) | 4099986598294                        |
| Qty.       | 1 items                              |

## PAC-HE26-HE26-HF-10M

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Approvals

|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

## Dimensions and weights

|            |        |
|------------|--------|
| Net weight | 1491 g |
|------------|--------|

## Temperatures

|                     |             |                       |             |
|---------------------|-------------|-----------------------|-------------|
| Storage temperature | -10...60 °C | Operating temperature | -10...50 °C |
|---------------------|-------------|-----------------------|-------------|

## Environmental Product Compliance

|                        |                       |
|------------------------|-----------------------|
| RoHS Compliance Status | Compliant             |
| REACH SVHC             | No SVHC above 0.1 wt% |

## General Data

|                       |                      |                     |                                  |
|-----------------------|----------------------|---------------------|----------------------------------|
| Cable length          | 10 m                 | Suitable for        | Digital signals                  |
| Cable                 | Cable LIHH           | Interface connector | FLAT CABLE CONNECTOR<br>HE10 26P |
| Number of poles, min. | 26-pole              | Connector PLC side  | FLAT CABLE CONNECTOR<br>HE10 26P |
| Wire cross-section    | 0.14 mm <sup>2</sup> |                     |                                  |

## Electrical Data

|                          |                     |                                             |            |
|--------------------------|---------------------|---------------------------------------------|------------|
| Total current, max.      | 3 A                 | Permissible current strength per path, max. | 1 A        |
| Rated voltage            | ≤ 60 V DC ≤ 25 V AC | Resistance                                  | ≤ 150 mΩ/m |
| Operating voltage        | ≤ 60 V DC ≤ 25 V AC | Capacity (wire / wires)                     | 300 pF/m   |
| Capacity (wire / shield) | 300 pF/m            |                                             |            |

## Rated data UL

|                     |     |
|---------------------|-----|
| Total current, max. | 3 A |
|---------------------|-----|

## Classifications

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 8.0    | EC000237    | ETIM 9.0    | EC000237    |
| ETIM 10.0   | EC000237    | ECLASS 14.0 | 27-24-22-20 |
| ECLASS 15.0 | 27-24-22-20 |             |             |