

## PAC-HE14-HE14-HF-1M5

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)



Similar to illustration

### General ordering data

|            |                                      |
|------------|--------------------------------------|
| Order No.  | 2425940015                           |
| Type       | <a href="#">PAC-HE14-HE14-HF-1M5</a> |
| GTIN (EAN) | 4099986598317                        |
| Qty.       | 1 items                              |

**PAC-HE14-HE14-HF-1M5****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Technical data****Approvals**

|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

**Dimensions and weights**

|            |       |
|------------|-------|
| Net weight | 120 g |
|------------|-------|

**Temperatures**

|                     |             |                       |             |
|---------------------|-------------|-----------------------|-------------|
| Storage temperature | -10...60 °C | Operating temperature | -10...50 °C |
|---------------------|-------------|-----------------------|-------------|

**Environmental Product Compliance**

|                        |                       |
|------------------------|-----------------------|
| RoHS Compliance Status | Compliant             |
| REACH SVHC             | No SVHC above 0.1 wt% |

**General Data**

|                       |                      |                     |                                 |
|-----------------------|----------------------|---------------------|---------------------------------|
| Cable length          | 1.5 m                | Suitable for        | Digital signals                 |
| Cable                 | Cable LIHH           | Interface connector | FLAT CABLE CONECTOR<br>HE10 14P |
| Number of poles, min. | 14-pole              | Connector PLC side  | FLAT CABLE CONECTOR<br>HE10 14P |
| Wire cross-section    | 0.14 mm <sup>2</sup> |                     |                                 |

**Electrical Data**

|                        |                     |                                             |            |
|------------------------|---------------------|---------------------------------------------|------------|
| Total current, max.    | 3 A                 | Permissible current strength per path, max. | 1 A        |
| Rated voltage          | ≤ 60 V DC ≤ 25 V AC | Resistance                                  | ≤ 150 mΩ/m |
| Operating voltage      | ≤ 60 V DC ≤ 25 V AC | Capacity wire / wires                       | 300 pF/m   |
| Capacity wire / shield | 300 pF/m            |                                             |            |

**Classifications**

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 8.0    | EC000237    | ETIM 9.0    | EC000237    |
| ETIM 10.0   | EC000237    | ECLASS 14.0 | 27-24-22-20 |
| ECLASS 15.0 | 27-24-22-20 |             |             |