

PAC-D37M-F-HF-5M

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



Similar to illustration

General ordering data

| | |
|------------|----------------------------------|
| Order No. | 2426000050 |
| Type | PAC-D37M-F-HF-5M |
| GTIN (EAN) | 4099986598720 |
| Qty. | 1 items |

PAC-D37M-F-HF-5M

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

| | |
|------|---------|
| ROHS | Conform |
|------|---------|

Dimensions and weights

| | |
|------------|-----------|
| Net weight | 1759.82 g |
|------------|-----------|

Temperatures

| | | | |
|---------------------|-------------|-----------------------|-------------|
| Storage temperature | -10...60 °C | Operating temperature | -10...50 °C |
|---------------------|-------------|-----------------------|-------------|

Environmental Product Compliance

| | |
|--------------------------------------|--------------------------------------|
| RoHS Compliance Status | Compliant with exemption |
| RoHS Exemption (if applicable/known) | 6c |
| REACH SVHC | Lead 7439-92-1 |
| SCIP | 4bbf2c0d-0764-4fc8-bb24-9351c28c190d |

General Data

| | | | |
|---------------------|------------------------------------------|-----------------------|----------------------|
| Cable length | 5 m | Suitable for | Analogue signals |
| Interface connector | SUB-D MALE 37P | Number of poles, min. | 37-pole |
| Connector PLC side | H0.25/10 (FERRULES 0.25mm ²) | Wire cross-section | 0.25 mm ² |

Electrical Data

| | | | |
|------------------------|---------------------|---------------------------------------------|-----------|
| Total current, max. | 3 A | Permissible current strength per path, max. | 1 A |
| Rated voltage | ≤ 60 Vdc ≤ 25 Vac | Resistance | ≤ 80 mΩ/m |
| Operating voltage | ≤ 60 V DC ≤ 25 V AC | Capacity wire / wires | 300 pF/m |
| Capacity wire / shield | 300 pF/m | | |

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 8.0 | EC000237 | ETIM 9.0 | EC000237 |
| ETIM 10.0 | EC000237 | ECLASS 14.0 | 27-24-22-20 |
| ECLASS 15.0 | 27-24-22-20 | | |