Data sheet

# PAC-D37F-D37F-HF-4M

**Weidmüller Interface GmbH & Co. KG**
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



Similar to illustration

## General ordering data

| | |
|---|---|
| Order No. | 2426130040 |
| Type | PAC-D37F-D37F-HF-4M |
| GTIN (EAN) | 4099986599499 |
| Qty. | 1 items |

# Data sheet

## PAC-D37F-D37F-HF-4M

**Weidmüller Interface GmbH & Co. KG**
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

# Technical data

### Approvals

| | |
|---|---|
| ROHS | Conform |

### Dimensions and weights

| | |
|---|---|
| Net weight | 1521.37 g |

### Temperatures

| | | | |
|---|---|---|---|
| Storage temperature | -10...60 °C | Operating temperature | -10...50 °C |

### Environmental Product Compliance

| | |
|---|---|
| RoHS Compliance Status | Compliant |
| REACH SVHC | No SVHC above 0.1 wt% |

### General Data

| | | | |
|---|---|---|---|
| Cable length | 4 m | Suitable for | Analogue signals |
| Interface connector | SUB-D FEMALE 37P | Number of poles, min. | 37-pole |
| Connector PLC side | SUB-D FEMALE 37P | Wire cross-section | 0.25 mm² |

### Electrical Data

| | | | |
|---|---|---|---|
| Total current, max. | 3 A | Permissible current strength per path, max. | 1 A |
| Rated voltage | ≤ 60 Vdc ≤ 25 Vac | Resistance | ≤ 80 mΩ/m |
| Operating voltage | ≤ 60 V DC ≤ 25 V AC | Capacity wire / wires | 300 pF/m |
| Capacity wire / shield | 300 pF/m | | |

### Classifications

| | | | |
|---|---|---|---|
| ETIM 8.0 | EC000237 | ETIM 9.0 | EC000237 |
| ETIM 10.0 | EC000237 | ECLASS 14.0 | 27-24-22-20 |
| ECLASS 15.0 | 27-24-22-20 | | |