

## UR67-MP-78-16DI-12-60M

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)



More performance. Simplified.

u-remote.

Weidmüller u-remote – our innovative remote I/O concept with IP 67 which focuses purely on user benefits: tailored planning, faster installation, safer start-up, no more downtime. For considerably improved performance and greater productivity. u-remote stands for "More Performance". Simplified

### General ordering data

Version	Automation Products - u-remote IP67, Sensor-actuator active distributor, PROFINET V2.3
Order No.	<a href="#">2426300000</a>
Type	UR67-MP-78-16DI-12-60M
GTIN (EAN)	4050118434439
Qty.	1 items

## UR67-MP-78-16DI-12-60M

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technical data

## Approvals

Approvals



ROHS Conform

UL File Number Search [UL Website](#)

Certificate no. (cULus) E141197

## Dimensions and weights

Height	51 mm	Height (inches)	2.0079 inch
Width	60 mm	Width (inches)	2.3622 inch
Length	255 mm	Length (inches)	10.0394 inch
Net weight	520 g		

## Environmental Product Compliance

RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	6c
REACH SVHC	Lead 7439-92-1
SCIP	82327f13-cd27-455a-ab5b-a62e1996dcf8

## Connections

Supply voltage (AUX-IN)	PushPull-Power	Supply voltage (AUX-OUT)	PushPull-Power
-------------------------	----------------	--------------------------	----------------

## Digital inputs

Diagnostic display	Per channel, via LED, red	
Input current, high	Type 1 in acc. with IEC 61131-2	
Status indicator	Per channel, via LED, yellow	
Digital inputs	Short-circuit protection	Yes
	Overload protection	Yes
	Reverse polarity protection	Yes
Input current, low	Type 1 in acc. with IEC 61131-2	
Input voltage, high	> 11 V	
Input voltage, low	<5 V	

## General data

UL 94 flammability rating	UL 94	Housing main material	Zinc diecast
Protection degree	IP67		

## Supply voltage

Reverse polarity protection	Yes	Operating voltage	24 V
Power consumption of module electronics	100 mA typical		

## Classifications

ETIM 8.0	EC001599	ETIM 9.0	EC001599
ETIM 10.0	EC001599	ECLASS 14.0	27-24-26-04
ECLASS 15.0	27-24-26-04		