

**WQV 10/6****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Product image**

The distribution or multiplication of a potential to adjoining terminal blocks is realized via a cross-connection. Additional wiring effort can be easily avoided. Even if the poles are broken out, contact reliability in the terminal blocks is still ensured. Our portfolio offers pluggable and screwable cross-connection systems for modular terminal blocks.

**General ordering data**

|            |  |
|------------|--|
| Version    | Cross-connector (terminal), when screwed in, yellow, 63 A, Number of poles: 6, Pitch in mm (P): 9.90, Insulated: Yes, Width: 7.55 mm |
| Order No.  | <a href="#">2226500000</a>   |
| Type       | WQV 10/6   |
| GTIN (EAN) | 4032248793761  |
| Qty.       | 20 items   |

## WQV 10/6

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Approvals

ROHS Conform

## Dimensions and weights

|            |         |                 |             |
|------------|---------|-----------------|-------------|
| Depth      | 18 mm   | Depth (inches)  | 0.7087 inch |
| Height     | 56.5 mm | Height (inches) | 2.2244 inch |
| Width      | 7.55 mm | Width (inches)  | 0.2972 inch |
| Net weight | 11.3 g  |                 |             |

## Temperatures

|                                  |                |                                  |                |
|----------------------------------|----------------|----------------------------------|----------------|
| Storage temperature              | -25 °C...55 °C | Ambient temperature              | -60 °C...85 °C |
| Continuous operating temp., min. | -60 °C         | Continuous operating temp., max. | 130 °C         |

## Environmental Product Compliance

|                        |                             |
|------------------------|-----------------------------|
| RoHS Compliance Status | Compliant without exemption |
| REACH SVHC             | No SVHC above 0.1 wt%       |

## Material data

|                           |       |        |        |
|---------------------------|-------|--------|--------|
| Basic material            | PA 66 | Colour | yellow |
| UL 94 flammability rating | V-0   |        |        |

## System specifications

Version For the terminals

## Additional technical data

|                |                 |                          |    |
|----------------|-----------------|--------------------------|----|
| Type of fixing | when screwed in | Explosion-tested version | No |
|----------------|-----------------|--------------------------|----|

## Dimensions

Pitch in mm (P) 9.90 mm

## General

Number of poles 6

## Rating data

|               |       |                 |      |
|---------------|-------|-----------------|------|
| Rated voltage | 400 V | Nominal current | 63 A |
|---------------|-------|-----------------|------|

## Classifications

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 8.0    | EC000489    | ETIM 9.0    | EC000489    |
| ETIM 10.0   | EC000489    | ECLASS 14.0 | 27-25-03-03 |
| ECLASS 15.0 | 27-25-03-03 |             |             |