


KLBUE 4-6 Z/1

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Product image

With our wide range of KLBÜ shield connections, you can achieve flexible and self-adjusting shield contacting and ensure error-free plant operation.

General ordering data

Version	Clamping yoke, Clamping yoke
Order No.	2269800000
Type	KLBUE 4-6 Z/1
GTIN (EAN)	403224826455 1
Qty.	10 items

KLBUE 4-6 Z/1

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

ROHS	Conform
------	---------

Dimensions and weights

Depth	8.5 mm	Depth (inches)	0.3346 inch
Height	45.2 mm	Height (inches)	1.7795 inch
Width	8.9 mm	Width (inches)	0.3504 inch
Net weight	3.17 g		

Temperatures

Storage temperature	-25 °C...55 °C	Ambient temperature	-5 °C...40 °C
Continuous operating temp., min.	-60 °C	Continuous operating temp., max.	130 °C

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption		
REACH SVHC	No SVHC above 0.1 wt%		
Product Carbon Footprint	Cradle to gate	0.397 kg CO2 eq.	

Material data

Colour	silver	UL 94 flammability rating	None
--------	--------	---------------------------	------

System specifications

Version	For a shield connection	End cover plate required	No
---------	-------------------------	--------------------------	----

Additional technical data

Type of fixing	Snap-on	Installation advice	Direct mounting, Busbar
Explosion-tested version	No		

Conductors for clamping (rated connection)

Stripping length	8.5 mm	Type of connection	Spring connection
Number of connections	1	Cable diameter, max.	6 mm
Cable diameter, min.	4 mm	Connection cross-section, stranded, max.	6 mm ²
Connection cross-section, stranded, min. 4 mm ²			

Dimensions

Pitch in mm (P)	20.00 mm
-----------------	----------

General

Installation advice	Direct mounting, Busbar
---------------------	-------------------------

Rating data

Rated cross-section	6 mm ²
---------------------	-------------------

Technical data

Classifications

ETIM 8.0	EC002020	ETIM 9.0	EC002020
ETIM 10.0	EC002020	ECLASS 14.0	27-25-01-20
ECLASS 15.0	27-25-01-20		

