


LX 15.00/09/90 4.5SN BK BX

Weidmüller Interface GmbH & Co. KG
Klingenbergsstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Product image

High-performance PCB terminal with proven clamping yoke connection at 15.00 mm pitch, conductor outlet direction in 90° design. Version and test point.

General ordering data

Version	Printed circuit board terminals, 15.00 mm, Number of poles: 9, 90°, Solder pin length (l): 4.5 mm, tinned, black, Clamping yoke connection, Clamping range, max. : 25 mm ² , Box
Order No.	2283750000
Type	LX 15.00/09/90 4.5SN BK BX
GTIN (EAN)	4050118428728
Qty.	10 items
Product data	IEC: 1000 V / 101 A / 1.5 - 25 mm ² UL: 600 V / 85 A / AWG 16 - AWG 4
Packaging	Box

LX 15.00/09/90 4.5SN BK BX

Weidmüller Interface GmbH & Co. KG
Klingenbergsstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Approvals

RoHS	Conform
------	---------

Dimensions and weights

Depth	29.1 mm	Depth (inches)	1.1457 inch
Height	41.5 mm	Height (inches)	1.6339 inch
Height of lowest version	37 mm	Width	148 mm
Width (inches)	5.8268 inch	Net weight	146.57 g

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

System parameters

Product family	OMNIMATE Power - series LX	Wire connection method	Clamping yoke connection
Mounting onto the PCB	THT solder connection	Conductor outlet direction	90°
Pitch in mm (P)	15.00 mm	Pitch in inches (P)	0.591 "
Number of poles	9	Pin series quantity	1
Fitted by customer	No	Number of rows	1
Max. adjacent poles per row	10	Solder pin length (l)	4.5 mm
Solder pin dimensions	1.2 x 1.2 mm	Solder eyelet hole diameter (D)	1.6 mm
Solder eyelet hole diameter tolerance (D)+ 0,1 mm		Number of solder pins per pole	4
Screwdriver blade	1.0 x 5.5	Screwdriver blade standard	DIN 5264
Tightening torque, min.	2.4 Nm	Tightening torque, max.	4 Nm
Clamping screw	M 5	Stripping length	16 mm
L1 in mm	135.00 mm	L1 in inches	5.319 "
Touch-safe protection acc. to DIN VDE 0470	IP 10	Touch-safe protection acc. to DIN VDE 57 106	Safe from finger touch
Protection degree	IP20	Volume resistance	0.50 mΩ

Material data

Insulating material	Wemid (PA)	Colour	black
Colour chart (similar)	RAL 9011	Insulating material group	I
Comparative Tracking Index (CTI)	≥ 600	Moisture Level (MSL)	
UL 94 flammability rating	V-0	Contact material	Cu-alloy
Contact surface	tinned	Layer structure of solder connection	1.5...3 µm Ni / 4...6 µm Sn matt
Storage temperature, min.	-40 °C	Storage temperature, max.	70 °C
Operating temperature, min.	-50 °C	Operating temperature, max.	120 °C
Temperature range, installation, min.	-25 °C	Temperature range, installation, max.	120 °C

Conductors suitable for connection

Clamping range, min.	1.31 mm ²
Clamping range, max.	25 mm ²
Wire connection cross section AWG, min.	AWG 16
Wire connection cross section AWG, max.	AWG 4
Solid, min. H05(07) V-U	1.5 mm ²
Solid, max. H05(07) V-U	16 mm ²
Stranded, min. H07V-R	6 mm ²

LX 15.00/09/90 4.5SN BK BX

Weidmüller Interface GmbH & Co. KG
Klingenbergsstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Stranded, max. H07V-R	25 mm ²																																																
Flexible, min. H05(07) V-K	1.5 mm ²																																																
Flexible, max. H05(07) V-K	25 mm ²																																																
w. plastic collar ferrule, DIN 46228 pt 4, 1.5 mm ² min.																																																	
w. plastic collar ferrule, DIN 46228 pt 4, 16 mm ² max.																																																	
w. wire end ferrule, DIN 46228 pt 1, 1.5 mm ² min.																																																	
w. wire end ferrule, DIN 46228 pt 1, 16 mm ² max.																																																	
Plug gauge in accordance with EN 60999 a x b; ø	6.9 mm x 6.9 mm																																																
Clampable conductor	<table border="1"> <tr> <td>Cross-section for conductor connection</td> <td>Type</td> <td>fine-wired</td> </tr> <tr> <td></td> <td>nominal</td> <td>4 mm²</td> </tr> <tr> <td>wire end ferrule</td> <td>Stripping length</td> <td>nominal 15 mm</td> </tr> <tr> <td></td> <td>Recommended wire-end ferrule</td> <td>H4.0/15</td> </tr> <tr> <td>Cross-section for conductor connection</td> <td>Type</td> <td>fine-wired</td> </tr> <tr> <td></td> <td>nominal</td> <td>6 mm²</td> </tr> <tr> <td>wire end ferrule</td> <td>Stripping length</td> <td>nominal 15 mm</td> </tr> <tr> <td></td> <td>Recommended wire-end ferrule</td> <td>H6.0/15</td> </tr> <tr> <td>Cross-section for conductor connection</td> <td>Type</td> <td>fine-wired</td> </tr> <tr> <td></td> <td>nominal</td> <td>10 mm²</td> </tr> <tr> <td>wire end ferrule</td> <td>Stripping length</td> <td>nominal 15 mm</td> </tr> <tr> <td></td> <td>Recommended wire-end ferrule</td> <td>H10.0/15</td> </tr> <tr> <td>Cross-section for conductor connection</td> <td>Type</td> <td>fine-wired</td> </tr> <tr> <td></td> <td>nominal</td> <td>16 mm²</td> </tr> <tr> <td>wire end ferrule</td> <td>Stripping length</td> <td>nominal 15 mm</td> </tr> <tr> <td></td> <td>Recommended wire-end ferrule</td> <td>H16.0/15</td> </tr> </table>	Cross-section for conductor connection	Type	fine-wired		nominal	4 mm ²	wire end ferrule	Stripping length	nominal 15 mm		Recommended wire-end ferrule	H4.0/15	Cross-section for conductor connection	Type	fine-wired		nominal	6 mm ²	wire end ferrule	Stripping length	nominal 15 mm		Recommended wire-end ferrule	H6.0/15	Cross-section for conductor connection	Type	fine-wired		nominal	10 mm ²	wire end ferrule	Stripping length	nominal 15 mm		Recommended wire-end ferrule	H10.0/15	Cross-section for conductor connection	Type	fine-wired		nominal	16 mm ²	wire end ferrule	Stripping length	nominal 15 mm		Recommended wire-end ferrule	H16.0/15
Cross-section for conductor connection	Type	fine-wired																																															
	nominal	4 mm ²																																															
wire end ferrule	Stripping length	nominal 15 mm																																															
	Recommended wire-end ferrule	H4.0/15																																															
Cross-section for conductor connection	Type	fine-wired																																															
	nominal	6 mm ²																																															
wire end ferrule	Stripping length	nominal 15 mm																																															
	Recommended wire-end ferrule	H6.0/15																																															
Cross-section for conductor connection	Type	fine-wired																																															
	nominal	10 mm ²																																															
wire end ferrule	Stripping length	nominal 15 mm																																															
	Recommended wire-end ferrule	H10.0/15																																															
Cross-section for conductor connection	Type	fine-wired																																															
	nominal	16 mm ²																																															
wire end ferrule	Stripping length	nominal 15 mm																																															
	Recommended wire-end ferrule	H16.0/15																																															

Reference text	Length of ferrules is to be chosen depending on the product and the rated voltage., The outside diameter of the plastic collar should not be larger than the pitch (P)
----------------	--

Rated data acc. to IEC

tested acc. to standard	IEC 60664-1, IEC 61984	Rated current, min. number of poles (Tu=20°C)	101 A
Rated current, max. number of poles (Tu=20°C)	101 A	Rated current, min. number of poles (Tu=40°C)	101 A
Rated current, max. number of poles (Tu=40°C)	101 A	Rated voltage for surge voltage class / pollution degree II/2	1000 V
Rated voltage for surge voltage class / pollution degree III/2	1000 V	Rated voltage for surge voltage class / pollution degree III/3	1000 V
Rated impulse voltage for surge voltage class/ pollution degree II/2	6 kV	Rated impulse voltage for surge voltage class/ pollution degree III/2	8 kV
Rated impulse voltage for surge voltage class/ contamination degree III/3	8 kV	Short-time withstand current resistance	3 x 1 s mit 1000 A

Rated data acc. to CSA

Rated voltage (Use group B / CSA)	600 V	Rated voltage (Use group C / CSA)	600 V
Rated voltage (Use group D / CSA)	600 V	Rated current (Use group B / CSA)	85 A
Rated current (Use group C / CSA)	85 A	Rated current (Use group D / CSA)	5 A
Wire cross-section, AWG, min.	AWG 16	Wire cross-section, AWG, max.	AWG 4

LX 15.00/09/90 4.5SN BK BX

Weidmüller Interface GmbH & Co. KG
Klingenbergsstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Rated data acc. to UL 1059

Rated voltage (Use group B / UL 1059)	600 V	Rated voltage (Use group C / UL 1059)	600 V
Rated voltage (Use group D / UL 1059)	600 V	Rated current (Use group B / UL 1059)	85 A
Rated current (Use group C / UL 1059)	85 A	Rated current (Use group D / UL 1059)	5 A
Wire cross-section, AWG, min.	AWG 16	Wire cross-section, AWG, max.	AWG 4

Packing

Packaging	Box	VPE length	295.00 mm
VPE width	91.00 mm	VPE height	65.00 mm

Type tests

Test: Durability of markings	Standard	DIN EN 61984 section 7.3.2 / 09.02 taking pattern from DIN EN 60068-2-70 / 07.96
	Test	mark of origin, type identification, pitch, approval marking CSA, approval marking UL, type of material, durability
	Evaluation	available
Test: Clampable cross section	Standard	DIN EN 60999 section 6 and 8.1 / 04.94, DIN EN 60947-1 section 8.2.4.5.1 / 12.99
	Conductor type	Type of conductor solid 1.5 mm ² and conductor cross-section
		Type of conductor stranded 1.5 mm ² and conductor cross-section
		Type of conductor solid 16 mm ² and conductor cross-section
		Type of conductor stranded 25 mm ² and conductor cross-section
		Type of conductor AWG 16/1 and conductor cross-section
		Type of conductor AWG 16/ stranded and conductor cross-section
		Type of conductor AWG 4/1 and conductor cross-section
		Type of conductor AWG 4/ stranded and conductor cross-section
	Evaluation	passed
Test for damage to and accidental loosening of conductors	Standard	DIN EN 60999 section 8.4 / 04.94
	Requirement	0.4 kg
	Conductor type	Type of conductor solid 1.5 mm ² and conductor cross-section
		Type of conductor stranded 1.5 mm ² and conductor cross-section
		Type of conductor AWG 16/7 and conductor cross-section
		Type of conductor AWG 16/19 and conductor cross-section
	Evaluation	passed

LX 15.00/09/90 4.5SN BK BX

Weidmüller Interface GmbH & Co. KG
Klingenbergsstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

	Requirement	4,5 kg
	Conductor type	Type of conductor and conductor cross-section AWG 4/ stranded
	Evaluation	passed
Pull-out test	Standard	DIN EN 60999 section 8.5 / 04.94
	Requirement	≥40 N
	Conductor type	Type of conductor and conductor cross-section H05V-U1.5
		Type of conductor and conductor cross-section H05V-K1.5
		Type of conductor and conductor cross-section AWG 16/7
		Type of conductor and conductor cross-section AWG 16/19
	Evaluation	passed
	Requirement	≥ 135 N
	Conductor type	Type of conductor and conductor cross-section H05V-R25
		Type of conductor and conductor cross-section H05V-K25
		Type of conductor and conductor cross-section AWG 4/ stranded
	Evaluation	passed

Important note

IPC conformity Conformity: The products are developed, manufactured and delivered according international recognized standards and norms and comply with the assured properties in the data sheet resp. fulfill decorative properties in accordance with IPC-A-610 "Class 2". Further claims on the products can be evaluated on request.

Notes

- Additional variants on request
- Rated current related to rated cross-section & min. No. of poles
- Wire end ferrule without plastic collar to DIN 46228/1
- Wire end ferrule with plastic collar to DIN 46228/4
- P on drawing = pitch
- Rated data refer only to the component itself. Clearance and creepage distances to other components are to be designed in accordance with the relevant application standards.
- The test point can only be used as potential-pickup point.
- Long term storage of the product with average temperature of 50 °C and maximum humidity 70%, 36 months



Classifications

ETIM 8.0	EC002643	ETIM 9.0	EC002643
ETIM 10.0	EC002643	ECLASS 14.0	27-46-01-01
ECLASS 15.0	27-46-01-01		

LX 15.00/09/90 4.5SN BK BX

Weidmüller Interface GmbH & Co. KG
Klingenbergsstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings**Product image****Dimensional drawing****Graph****Graph**