

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

Similar to illustration





Weidmüller is one of the industry's leading international providers of connectors. An important mainstay in this product family are the circular connectors, which Weidmüller groups under the product name SAI. In the development of SAI products, Weidmüller engineers have always concentrated on achieving rational, cost-effective installation concepts, and – in cooperation with major users – have supplied the markets with well-conceived products which set standards in terms of functionality and quality across the globe. The best examples are the new power distributors with S and T coded M12. These modules are characterised by particularly high currents and voltages. This enables them to also be used, for example, with three-phase motors.

General ordering data

| Version | Built-in plugs, M12, Mounting thread: PG 9, Number of poles: 5, Strand / cable length: |
|------------|--|
| Order No. | <u>2421980000</u> |
| Туре | SAIE-M12B-5-H5.5TL-PG9 |
| GTIN (EAN) | 4050118430806 |
| Qty. | 10 items |

1

Catalogue status / Drawings





Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

Technical data

| Aр | pr | ov | a | s |
|----|----|----|---|---|
|----|----|----|---|---|

ROHS Conform

Dimensions and weights

Net weight 20 g

Environmental Product Compliance

| RoHS Compliance Status | Compliant with exemption |
|--------------------------------------|--------------------------------------|
| RoHS Exemption (if applicable/known) | 6c |
| REACH SVHC | Lead 7439-92-1 |
| SCIP | 0ea6d931-f9e9-40a6-89d9-8d67103189d3 |

Technical data of PCB plug-in connector

| Number of poles | 5 |
|--|--|
| Coding | A-coded |
| Type of mounting | Rear panel mounting |
| Housings | M12 socket |
| Installation height | 5.5 mm |
| Shield connection | No |
| Mounting thread | PG9 |
| Nominal voltage | 60 V |
| Rated voltage | 250 V (4-pole) / 60 V (5-pole) / 30 V (8-pole) |
| Nominal current | 4 A |
| Rated current | 4 A (4- and 5-pole) / 2 A (8-pole) |
| Temperature range | -3080 °C |
| Protection degree | IP67 |
| Contact surface | Au (Gold) |
| Housing main material | CuZn, nickel-plated |
| Connection thread | M12 |
| Tightening torque | M12: 0.8 Nm |
| Mounting thread | PG 9 |
| Mounting torque range | 1.2 Nm |
| Mounting torque | max. 1.2 Nm |
| Insulation resistance | 100 ΜΩ |
| Pollution severity | 3 (2 within the sealed area) |
| Plugging cycles | ≥ 100 |
| Contact material | Cu-alloy |
| Lock nut material | Nickel-plated CuZn |
| Material of the flange-mounted housing | Nickel-plated CuZn |

General Info

| Number of poles | 5 | Housing main material | CuZn, nickel-plated |
|-------------------|-----------|-----------------------|---------------------|
| Connection thread | M12 | Contact material | Cu-alloy |
| Contact surface | Au (Gold) | Type of mounting | Rear panel mounting |
| Protection degree | IP67 | Plugging cycles | ≥ 100 |

Material data

| Contact material | Cu-alloy | Contact surface | Au (Gold) |
|------------------|----------|-----------------|-----------|

Creation date 01.12.2025 01:52:12 MEZ

Catalogue status / Drawings 2





Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

Technical data

| System para | ameters |
|-------------|---------|
|-------------|---------|

| Number of poles | 5 | Pin series quantity | 1 | |
|-----------------------|--------|---------------------|------|--|
| Insulation resistance | 100 ΜΩ | Protection degree | IP67 | |
| Plugging cycles | ≥ 100 | | | |

Important note

Notes

Classifications

| ETIM 6.0 | EC002638 | ETIM 7.0 | EC003568 |
|-------------|-------------|-------------|-------------|
| ETIM 8.0 | EC003568 | ETIM 9.0 | EC003568 |
| ETIM 10.0 | EC003568 | ECLASS 9.0 | 27-44-03-09 |
| ECLASS 9.1 | 27-44-03-09 | ECLASS 10.0 | 27-44-03-09 |
| ECLASS 11.0 | 27-44-01-10 | ECLASS 12.0 | 27-44-01-10 |
| ECLASS 13.0 | 27-44-01-10 | ECLASS 14.0 | 27-44-01-10 |
| ECLASS 15.0 | 27-44-01-10 | | |
| | | | |

Catalogue status / Drawings 3




Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

Drawings

PCB design




L(board-to-board distance) = 5,5mm D1 = 5,0 mm D2 = 1,6 mm

Front panel section

Ø15,3^{+0,1}

Pole scheme



M12 = A-coded