

## PAC-HE40-F-HF-2M


**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)



Similar to illustration

### General ordering data

|            |                                  |
|------------|----------------------------------|
| Order No.  | 2425680020                       |
| Type       | <a href="#">PAC-HE40-F-HF-2M</a> |
| GTIN (EAN) | 4099986593060                    |
| Qty.       | 1 items                          |

## PAC-HE40-F-HF-2M

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Approvals

|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

## Dimensions and weights

|            |       |
|------------|-------|
| Net weight | 298 g |
|------------|-------|

## Temperatures

|                     |             |                       |             |
|---------------------|-------------|-----------------------|-------------|
| Storage temperature | -10...60 °C | Operating temperature | -10...50 °C |
|---------------------|-------------|-----------------------|-------------|

## Environmental Product Compliance

|                        |                       |
|------------------------|-----------------------|
| RoHS Compliance Status | Compliant             |
| REACH SVHC             | No SVHC above 0.1 wt% |

## General Data

|                       |                      |                     |                                          |
|-----------------------|----------------------|---------------------|------------------------------------------|
| Cable length          | 2 m                  | Suitable for        | Digital signals                          |
| Cable                 | Cable LIHH           | Interface connector | FLAT CABLE PLANO HE10 40P                |
| Number of poles, min. | 40-pole              | Connector PLC side  | H0.14/10 (FERRULES 0.14mm <sup>2</sup> ) |
| Wire cross-section    | 0.14 mm <sup>2</sup> |                     |                                          |

## Electrical Data

|                        |                     |                                             |            |
|------------------------|---------------------|---------------------------------------------|------------|
| Total current, max.    | 3 A                 | Permissible current strength per path, max. | 1 A        |
| Rated voltage          | ≤ 60 V DC ≤ 25 V AC | Resistance                                  | ≤ 150 mΩ/m |
| Operating voltage      | ≤ 60 V DC ≤ 25 V AC | Capacity wire / wires                       | 300 pF/m   |
| Capacity wire / shield | 300 pF/m            |                                             |            |

## Classifications

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 8.0    | EC000237    | ETIM 9.0    | EC000237    |
| ETIM 10.0   | EC000237    | ECLASS 14.0 | 27-24-22-20 |
| ECLASS 15.0 | 27-24-22-20 |             |             |