
Data sheet

# SAIE-M12B-5B-0.5U-M16

**Weidmüller Interface GmbH & Co. KG**
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



Various build-in connectors are required for the connections on the device side of the sensor/actuator cabling. These are available in the versions M12, M8 and M5.

## General ordering data

| | |
|---|---|
| Version | Built-in plugs, M12, Female socket, straight, Mounting thread: M 16 x 1.5, Number of poles: 5, Strand / cable length: 0.5 m, Front mounting |
| Order No. | 2434700000 |
| Type | SAIE-M12B-5B-0.5U-M16 |
| GTIN (EAN) | 4050118446524 |
| Qty. | 1 items |

# Data sheet

## SAIE-M12B-5B-0.5U-M16

**Weidmüller Interface GmbH & Co. KG**
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

# Technical data

### Approvals

| | |
|---|---|
| Approvals | |
| ROHS | Conform |
| UL File Number Search | UL Website |
| Certificate no. (cULus) | E307231 |

### Dimensions and weights

| | |
|---|---|
| Net weight | 30 g |

### Environmental Product Compliance

| | |
|---|---|
| RoHS Compliance Status | Compliant |
| REACH SVHC | Lead 7439-92-1 |
| SCIP | ebf89fc8-a87f-4691-b87a-dfb9921774b4 |

### Technical specifications for cable

| | | | |
|---|---|---|---|
| PE function | No | Core cross-section | 0.34 mm² |
| Strand / cable length | 0.5 m | Colour coding | brown, white, blue, black, grey |
| Number of poles | 5 | | |

### Technical data customisable plug-in connectors

| | | | |
|---|---|---|---|
| Number of poles | 5 | Coding | B-coded |
| Contact surface | Gold-plated | Housing main material | Zinc diecast |
| Nominal voltage | 60 V | Nominal current | 4 A |
| Protection degree | IP67, when screwed in | Plugging cycles | ≥ 100 |
| Temperature range of housing | -30...+90 °C | | |

### Standards

| | |
|---|---|
| Connector standard | IEC 61076-2-101 |

### General data

| | |
|---|---|
| Number of poles | 5 |
| Coding | B-coded |
| Connection thread | M12 |
| Contact surface | Gold-plated |
| Tightening torque | 1 Nm |
| Core cross-section | 0.34 mm² |
| Housing main material | Zinc diecast |
| Type of mounting | Front mounting |
| Nominal voltage | 60 V |
| Nominal current | 4 A |
| Protection degree | IP67, when screwed in |
| Plugging cycles | ≥ 100 |
| Rated voltage | 250 V (4-pole) / 125 V (5-pole) / 60 V (8-pole) |
| Connection 1 | M12 |
| Connection 2 | Flying wires |
| Strand / cable length | 0.5 m |

# Data sheet

## SAIE-M12B-5B-0.5U-M16

**Weidmüller Interface GmbH & Co. KG**
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

## Technical data

| | | |
|---|---|---|
| Mounting thread | M 16 x 1.5 | |
| Mounting torque range | 2 Nm | |
| Mounting torque | max. | 2 Nm |
| Temperature range of housing | -30...+90 °C | |
| Conductor O.D. | - | |

### Classifications

| | | | |
|---|---|---|---|
| ETIM 8.0 | EC003570 | ETIM 9.0 | EC003570 |
| ETIM 10.0 | EC003570 | ECLASS 14.0 | 27-44-01-03 |
| ECLASS 15.0 | 27-44-01-03 | | |


# SAIE-M12B-5B-0.5U-M16

**Weidmüller Interface GmbH & Co. KG**
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

## Drawings

### Wiring diagram




### Pole scheme

