

**PAC-RX3i-UNIS-V0-2M5****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

The pre-assembled PAC cables establish an electrical and logical connection between the PLC and the PLC interfaces. These cables consist of the following components:

- Manufacturer's PLC connector.
- Multi-pole LIYY or LY YCY cable (shielded) with a cross-section of 0.14 mm<sup>2</sup> or 0.25 mm<sup>2</sup>.
- Flat cable connector, SUB-D or RSV, for connection to the interface.

The cables are tested automatically for their continuity and insulation to guarantee the functionality for which they have been designed.

**General ordering data**

|            |                                      |
|------------|--------------------------------------|
|            |                                      |
| Order No.  | 2435780025                           |
| Type       | <a href="#">PAC-RX3i-UNIS-V0-2M5</a> |
| GTIN (EAN) | 4099986601055                        |
| Qty.       | 1 items                              |

## PAC-RX3i-UNIS-V0-2M5

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Approvals

|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

## Dimensions and weights

|            |       |
|------------|-------|
| Net weight | 710 g |
|------------|-------|

## General Data

|                     |                                       |                       |                         |
|---------------------|---------------------------------------|-----------------------|-------------------------|
| Cable length        | 2.5 m                                 | Suitable for          | Analogue signals        |
| Basic material      | PVC                                   | Cable                 | Cable LiYCY             |
| Interface connector | H0.25 (FERRULES 0.25mm <sup>2</sup> ) | Number of poles, min. | 36-pole                 |
| Outer diameter      | 12.4 ± 1 mm                           | Connector PLC side    | GEFANUC IC694TBS032 36P |
| Wire cross-section  | 0.25 mm <sup>2</sup>                  |                       |                         |

## Electrical Data

|                         |           |                          |                       |
|-------------------------|-----------|--------------------------|-----------------------|
| Total current, max.     | 0.125 A   | High voltage test        | 1 KV/1s               |
| Resistance              | ≤ 80 mΩ/m | Operating voltage        | ≤ 250 V DC ≤ 250 V AC |
| Capacity (wire / wires) | 300 pF/m  | Capacity (wire / shield) | 300 pF/m              |

## Rated data UL

|                     |         |
|---------------------|---------|
| Total current, max. | 0.125 A |
|---------------------|---------|

## Classifications

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 8.0    | EC000237    | ETIM 9.0    | EC000237    |
| ETIM 10.0   | EC000237    | ECLASS 14.0 | 27-24-22-20 |
| ECLASS 15.0 | 27-24-22-20 |             |             |