Data sheet

# HS-HF 6.4-12.7/25 MM B

**Weidmüller Interface GmbH & Co. KG**
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



The heat-shrinkable sleeve is printable on 2 sides and can be used for marking and insulating cables and wires. The flexible, heat-shrink material enables a firm, perfect fit around the conductor and therefore saves space.

## General ordering data

| | |
|---|---|
| Version | Conductor and cable markers, 6.4 - 12.7 mm, 25.4 x 20.9 mm, blue |
| Order No. | 2438130000 |
| Type | HS-HF 6.4-12.7/25 MM B |
| GTIN (EAN) | 4050118461220 |
| Qty. | 1000 items |
| Delivery status | This article will no longer be available in the future. |
| Available until | 2025-08-31T00:00:00+02:00 |

# Data sheet

## HS-HF 6.4-12.7/25 MM B

**Weidmüller Interface GmbH & Co. KG**
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

# Technical data

### Approvals

| | |
|---|---|
| ROHS | Conform |

### Dimensions and weights

| | | | |
|---|---|---|---|
| Depth | 0.77 mm | Depth (inches) | 0.0303 inch |
| Height | 25.4 mm | Height (inches) | 1 inch |
| Width | 20.9 mm | Width (inches) | 0.8228 inch |
| Net weight | 0.6 g | | |

### Temperatures

| | |
|---|---|
| Operating temperature range | -55…105 °C |

### Environmental Product Compliance

| | |
|---|---|
| RoHS Compliance Status | Compliant without exemption |
| REACH SVHC | No SVHC above 0.1 wt% |

### General data

| | | | |
|---|---|---|---|
| Type of printing | neutral | Width | 20.9 mm |
| Operating temperature range, max. | 105 °C | Operating temperature range, min. | -55 °C |
| Colour | blue | Halogen | No |
| Basic material | Polyolefine | Printed characters | without |
| compatible printer | THM MULTIMARK, THM MULTIMARK PLUS | Operating temperature range | -55…105 °C |
| Number per roll | 1000 | | |

### Conductor and cable markers

| | | | |
|---|---|---|---|
| Halogen | No | Conductor cross-section, max. | 35 mm² |
| Conductor cross-section, min. | 6 mm² | Conductor O.D., max. | 12.7 mm |
| Conductor O.D., min. | 6.4 mm | Rate of shrinkage | 2:1 |
| Recommended shrinking temperature | 90 °C | Conductor O.D. | 6.4 - 12.7 mm |
| Cross-section for connected wire | 6 - 35 mm² | | |

### Classifications


| | | | |
|---|---|---|---|
| ETIM 8.0 | EC001530 | ETIM 9.0 | EC001530 |
| ETIM 10.0 | EC001530 | ECLASS 14.0 | 27-28-11-02 |
| ECLASS 15.0 | 27-28-11-02 | | |

# HS-HF 6.4-12.7/25 MM B

**Weidmüller Interface GmbH & Co. KG**
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

## Drawings



Weidmüller

**Weidmüller Interface GmbH & Co. KG**
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

# Accessories

## Ink ribbons




These printers produce excellent printing results thanks to the thermal transfer technique. Different materials and the user-friendly printing system under Windows optimise marking efforts.

### General ordering data

| | | |
|---|---|---|
| Type | RIBBON MM-HS 60/300 SW | Version |
| Order No. | 2448880000 | Ink ribbon |
| GTIN (EAN) | 4050118462944 | |
| Qty. | 1 ST | |

## THM MULTIMARK




These printers produce excellent printing results thanks to the thermal transfer technique. Different materials and the user-friendly printing system under Windows optimise marking efforts.

### General ordering data

| | | |
|---|---|---|
| Type | MULTIMARK ROLLER 115 | Version |
| Order No. | 1357420000 | |
| GTIN (EAN) | 4050118160314 | |
| Qty. | 1 ST | |

## THM MULTIMARK PLUS



These printers produce excellent printing results thanks to the thermal transfer technique. Different materials and the user-friendly printing system under Windows optimise marking efforts.

### General ordering data

| | | |
|---|---|---|
| Type | MULTIMARK PLUS ROLLER 1... | Version |
| Order No. | 2672590000 | |
| GTIN (EAN) | 4050118708097 | |
| Qty. | 1 ST | |