

WB SI SL 1,0X5,5

Weidmüller Interface GmbH & Co. KG
Klingenbergsstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Similar to illustration



1000V
IEC 60900



If you demand effective and exact work, it is essential to use the precise torque. This also guarantees high repetition accuracy.

This is the perfect job for the new Weidmüller torque screwdriver with the ergonomic grip and the unique interchangeable bit system.

- Compact and especially light design
- Torque set with special tool (supplied); an unintended, incorrect setting is ruled out.
- Ergonomic handle sizes matched to the torque range.
- Tools subjected to routine testing and provided with an ID number; 100% quality control with verification and product reference.
- Clicking sound upon reaching the set torque, clearly audible and noticeable, no unnecessary tightening.
- Interchangeable blades made from high-quality wear-resistant tool steel.
- All tools fulfil the accuracy requirements of: EN ISO 6798, BS EN 26789, ASME B107.14M
- Trigger accuracy +/- 6% of the set scale value.

General ordering data

| | |
|------------|----------------------------|
| Version | Screwdriver insert |
| Order No. | 2433200000 |
| Type | WB SI SL 1,0X5,5 |
| GTIN (EAN) | 4050118443660 |
| Qty. | 1 items |

WB SI SL 1,0X5,5

Weidmüller Interface GmbH & Co. KG
Klingenbergsstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data**Dimensions and weights**

| | | | |
|------------|--------|-----------------|-------------|
| Depth | 7 mm | Depth (inches) | 0.2756 inch |
| Height | 75 mm | Height (inches) | 2.9527 inch |
| Width | 7 mm | Width (inches) | 0.2756 inch |
| Net weight | 9.68 g | | |

Environmental Product Compliance

| | |
|------------------------|-----------------------------|
| RoHS Compliance Status | Compliant without exemption |
| REACH SVHC | No SVHC above 0.1 wt% |

Technical data

| | |
|------------------------|--|
| Description of article | VDE-insulated interchangeable bit for slotted screws, size 1 x 5.5 |
|------------------------|--|

Screwing tools

| | | | |
|-----------------|---------|----------------------|--------|
| Blade width (B) | 5.5 mm | Blade thickness (A) | 1 mm |
| Form | Slotted | Torque setting, max. | 5.5 Nm |

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 8.0 | EC003864 | ETIM 9.0 | EC003864 |
| ETIM 10.0 | EC003864 | ECLASS 14.0 | 21-04-42-04 |
| ECLASS 15.0 | 21-04-42-04 | | |