


**SAIE-M12B-5B-0.5U-M16****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



Various build-in connectors are required for the connections on the device side of the sensor/actuator cabling. These are available in the versions M12, M8 and M5.

**General ordering data**

Version	Built-in plugs, M12, Female socket, straight, Mounting thread: M 16 x 1.5, Number of poles: 5, Strand / cable length: 0.5 m, Front mounting
Order No.	<a href="#">2434700000</a>
Type	SAIE-M12B-5B-0.5U-M16
GTIN (EAN)	4050118446524
Qty.	1 items

## SAIE-M12B-5B-0.5U-M16

Weidmüller Interface GmbH & Co. KG  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

www.weidmueller.com

## Technical data

## Approvals

Approvals



ROHS Conform

UL File Number Search [UL Website](#)

Certificate no. (cULus) E307231

## Dimensions and weights

Net weight 30 g

## Environmental Product Compliance

RoHS Compliance Status Compliant

REACH SVHC Lead 7439-92-1

SCIP ebf89fc8-a87f-4691-b87a-dfb9921774b4

## Technical specifications for cable

PE function	No	Core cross-section	0.34 mm <sup>2</sup>
Strand / cable length	0.5 m	Colour coding	brown, white, blue, black, grey
Number of poles	5		

## Technical data customisable plug-in connectors

Number of poles	5	Coding	B-coded
Contact surface	Gold-plated	Housing main material	Zinc diecast
Nominal voltage	60 V	Nominal current	4 A
Protection degree	IP67, when screwed in	Plugging cycles	≥ 100
Temperature range of housing	-30...+90 °C		

## Standards

Connector standard IEC 61076-2-101

## General data

Number of poles	5
Coding	B-coded
Connection thread	M12
Contact surface	Gold-plated
Tightening torque	1 Nm
Core cross-section	0.34 mm <sup>2</sup>
Housing main material	Zinc diecast
Type of mounting	Front mounting
Nominal voltage	60 V
Nominal current	4 A
Protection degree	IP67, when screwed in
Plugging cycles	≥ 100
Rated voltage	250 V (4-pole) / 125 V (5-pole) / 60 V (8-pole)
Connection 1	M12
Connection 2	Flying wires
Strand / cable length	0.5 m

**SAIE-M12B-5B-0.5U-M16**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Technical data**

Mounting thread	M 16 x 1.5
Mounting torque range	2 Nm
Mounting torque	max. 2 Nm
Temperature range of housing	-30...+90 °C
Conductor O.D.	-

**Classifications**

ETIM 8.0	EC003570	ETIM 9.0	EC003570
ETIM 10.0	EC003570	ECLASS 14.0	27-44-01-03
ECLASS 15.0	27-44-01-03		

**Wiring diagram**



**Pole scheme**

