

VT LCL

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



- Reacts from a distance of 4 mm
- No current flow necessary thanks to capacitive method
- Detects concealed broken wires with a tolerance of just a few millimetres
- Detects voltage-conducting wires in sockets, cable reels, distributors, etc.
- Display: visual or both visual and acoustic
- including a flashlight function with the VT LCL

General ordering data

Version	Testing tools, Cable detector
Order No.	2436670000
Type	VT LCL
GTIN (EAN)	4050118450033
Qty.	1 items

VT LCL

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

Approvals



ROHS Conform

Dimensions and weights

Depth	23 mm	Depth (inches)	0.9055 inch
Height	25 mm	Height (inches)	0.9842 inch
Width	155 mm	Width (inches)	6.1024 inch
Length	155 mm	Length (inches)	6.1024 inch
Net weight	181 g		

Environmental Product Compliance

RoHS Compliance Status	Compliant
RoHS Exemption (if applicable/known)	7cl
REACH SVHC	No SVHC above 0.1 wt%
SCIP	b05b5 122-6117-4cb0-b28c-df32f921fa36

Technical data

Description of article	Non-contact voltage tester
------------------------	----------------------------

Measuring and testing devices

Measuring range category	CAT IV 1000 V	Rated voltage, max.	1000 V AC
Rated voltage, min.	12 V AC	Display	Visual & acoustic
Protection degree	IP65	Battery type	1.5 V type AAA battery
Tested and approved according to	DIN EN 61010-1, DIN EN 61326		

Classifications

ETIM 8.0	EC000494	ETIM 9.0	EC000494
ETIM 10.0	EC000494	ECLASS 14.0	27-20-03-08
ECLASS 15.0	27-20-03-08		