

**HS-HF 3.2-6.4/50 MM Y****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



The heat-shrinkable sleeve is printable on 2 sides and can be used for marking and insulating cables and wires. The flexible, heat-shrink material enables a firm, perfect fit around the conductor and therefore saves space.

**General ordering data**

|            |  |
|------------|--|
| Version    | Conductor markers, Conductor and cable markers, 3.2 - 6.4 mm, 50.8 x 10.7 mm, yellow |
| Order No.  | <a href="#">2438070000</a>   |
| Type       | HS-HF 3.2-6.4/50 MM Y  |
| GTIN (EAN) | 4050118461145  |
| Qty.       | 1000 items   |

**HS-HF 3.2-6.4/50 MM Y**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

**Technical data**

**Approvals**

ROHS Conform

**Dimensions and weights**

|            |         |                 |             |
|------------|---------|-----------------|-------------|
| Depth      | 0.77 mm | Depth (inches)  | 0.0303 inch |
| Height     | 50.8 mm | Height (inches) | 2 inch      |
| Width      | 10.7 mm | Width (inches)  | 0.4213 inch |
| Net weight | 0.6 g   |                 |             |

**Temperatures**

Operating temperature range -55...105 °C

**Environmental Product Compliance**

RoHS Compliance Status Compliant without exemption  
 REACH SVHC No SVHC above 0.1 wt%

**General data**

|                                   |  |                                   |              |
|-----------------------------------|--|-----------------------------------|--------------|
| Type of printing                  | neutral  | Width                             | 10.7 mm      |
| Operating temperature range, max. | 105 °C   | Operating temperature range, min. | -55 °C       |
| Colour                            | yellow   | Halogen                           | No           |
| Basic material                    | Polyolefine  | Printed characters                | without      |
| compatible printer                | <a href="#">THM MULTIMARK</a> , <a href="#">THM MULTIMARK PLUS</a> | Operating temperature range       | -55...105 °C |
| Number per roll                   | 1000   |                                   |              |

**Conductor and cable markers**

|                                   |                         |                               |                   |
|-----------------------------------|-------------------------|-------------------------------|-------------------|
| Halogen                           | No                      | Conductor cross-section, max. | 6 mm <sup>2</sup> |
| Conductor cross-section, min.     | 1.5 mm <sup>2</sup>     | Conductor O.D., max.          | 6.4 mm            |
| Conductor O.D., min.              | 3.2 mm                  | Rate of shrinkage             | 2:1               |
| Recommended shrinking temperature | 90 °C                   | Conductor O.D.                | 3.2 - 6.4 mm      |
| Cross-section for connected wire  | 1.5 - 6 mm <sup>2</sup> |                               |                   |

**Classifications**

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 8.0    | EC001530    | ETIM 9.0    | EC001530    |
| ETIM 10.0   | EC001530    | ECLASS 14.0 | 27-28-11-02 |
| ECLASS 15.0 | 27-28-11-02 |             |             |

**HS-HF 3.2-6.4/50 MM Y**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Drawings**

