

SAIL-M8WM8W-4S7.5U

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



Sensor/actuator cables are used for wiring sensors and actuators and for transmitting data or power in various applications. The moulded cable offers connected and tested connection of the plug-in connector to the cable ex-works. The cables may be exposed to a wide range of conditions, such as humidity, dust, heat, cold, shock or vibration.

Our developers have focused specifically on this issue and designed a host of different M8 and M12 sensor-actuator cables so you are bound to find the solution you need for your application.

Is there something you have not managed to find or you feel needs explanation? Talk to us!

General ordering data

| | |
|------------|--|
| Version | Sensor/actuator line, M8, Number of poles : 4, 7.5 m, pin, 90° - socket 90°, Shielded: Yes, LED: No, Sheath material: PUR, Halogen: No |
| Order No. | 2443150750 |
| Type | SAIL-M8WM8W-4S7.5U |
| GTIN (EAN) | 4050118457094 |
| Qty. | 1 items |

SAIL-M8WM8W-4S7.5U

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

Approvals



| | |
|-------------------------|----------------------------|
| ROHS | Conform |
| UL File Number Search | UL Website |
| Certificate no. (cULus) | E307231 |

Dimensions and weights

| | |
|------------|-------|
| Net weight | 314 g |
|------------|-------|

Environmental Product Compliance

| | |
|--------------------------------------|--------------------------------------|
| RoHS Compliance Status | Compliant with exemption |
| RoHS Exemption (if applicable/known) | 6c |
| REACH SVHC | Lead 7439-92-1 |
| SCIP | e8d8af70-4c85-4483-bc8c-9bc5b598e2a9 |

Technical specifications for cable

| | | | |
|-------------------------------|------------------------------|--|--------------------------------|
| Cable length | 7.5 m | Sheathing colour | black |
| Suitable for cable carriers | Yes | Core cross-section | 0.34 mm ² |
| Shielded | Yes | Halogen | No |
| Insulation | PP | Acceleration | 5 m/s ² |
| Bending radius, min., moving | 12 x conductor cross-section | Bending radius, min., stationary | 5 x cable diameter |
| Bending cycles | 2 Mio | Resistance to spread of flame | in accordance with IEC 60332-2 |
| Speed | 100 m/s | Sheath material | PUR |
| Configurable cable length | No | Outer cladding in accordance with UL AWM style | 20549 (80 °C / 300 V) |
| Irradiation crosslinked | No | Welding spark resistance | No |
| Colour coding | brown, black, blue, white | Torsion resistance | 0 °/m |
| Temperature range, stationary | -40...80 °C | Resistant to welding beads | No |
| Temperature range, moving | -25...80 °C | Number of poles | 4 |
| Outside diameter | 5.1 mm ± 0.2 mm | | |

General technical data

| | | | |
|------------------------------|-------------------------------|------------------------|---|
| Coding | A-coded | Connection thread | M8 |
| Contact surface | Gold-plated | LED | No |
| Version | pin, 90° - socket 90° | Housing main material | PUR |
| Insulation resistance | 108 Ω | Nominal voltage | 30 V |
| Nominal current | 4 A | Protection degree | IP65, IP66, IP67, IP68, when screwed in |
| Plugging cycles jumpered | ≥ 100 | Pollution severity | 3 |
| Temperature range of housing | -25...+85 °C | Threaded ring material | Diecast zinc |
| | | Tightening torque | M8: 0.6 Nm |

Electrical properties

| | | | |
|-----------------------|-------|-----------------|------|
| Insulation resistance | 108 Ω | Nominal voltage | 30 V |
|-----------------------|-------|-----------------|------|

SAIL-M8WM8W-4S7.5U

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

General standards

Certificate no. (cULus) E307231

Plug, left

Plug left M8, IP69, male contact, angled 90°, Plastic, shielded

Plug, right

Plug right M8, IP69, female contact, angled 90°, Plastic, shielded

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 8.0 | EC001855 | ETIM 9.0 | EC001855 |
| ETIM 10.0 | EC001855 | ECLASS 14.0 | 27-06-03-11 |
| ECLASS 15.0 | 27-06-03-11 | | |

SAIL-M8WM8W-4S7.5U

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany


www.weidmueller.com

Drawings

Dimensioned drawing



Dimensioned drawing



Pole scheme



Pole scheme



SAIL-M8WM8W-4S7.5U

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

Drawings

www.weidmueller.com

Wiring diagram



The ideal tool: Screwty® with torque function



Light, securely screwed-in round plug-in connectors. Screwty set DM / VPE: 1 / Order No.: 1920000000 Adapters: M12, M12 F, M8, M8 F