

**IE-CD-V14SCRJ/VAPM24V-C**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

www.weidmueller.com



Coupling FreeCon design for Fibre-optic plug-in connectors PushPull Var.14 according to IEC 61076-3-117, metal

**General ordering data**

Version	Junction box, FreeCon, Plug-in connector, SCRJ, Supply, IP65
Order No.	<a href="#">2448840000</a>
Type	IE-CD-V14SCRJ/VAPM24V-C
GTIN (EAN)	4050118462685
Qty.	1 items

## IE-CD-V14SCRJ/VAPM24V-C

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technical data

### Approvals

ROHS	Conform
------	---------

### Dimensions and weights

Depth	130.4 mm	Depth (inches)	5.1338 inch
Height	53 mm	Height (inches)	2.0866 inch
Width	100 mm	Width (inches)	3.937 inch
Net weight	804.65 g		

### Temperatures

Storage temperature	Operating temperature	-20 °C...55 °C
Installation temperature		

### Environmental Product Compliance

RoHS Compliance Status	Compliant
REACH SVHC	Lead 7439-92-1
SCIP	67cf1078-beca-4687-860b-dc475a6ec24a

### General data

UL 94 flammability rating	V-0	Colour	silver
Housing main material	Aluminium profile, Cover: die-cast zinc, painted	Type of mounting	Screw mounting
Protection degree	IP65	Plugging cycles	≥ 100
Power interface	PROFINET PushPull Power	Data interface	PROFINET PushPull SCRJ POF (V14)

### General standards

Connector standard	IEC 61076-3-117 Var. 14, IEC 61754-24
--------------------	--

### Optical properties of fibre-optic coupling

Insertion attenuation (fibre-optic coupling)	≤ 3.5 dB
--	----------

### Technical specifications for power connector

Wire connection cross section, finely stranded, max. (power connector)	2.5 mm <sup>2</sup>	Connection cross-section AWG, min. (power connector)	18.00
Contact material (power connector)	Copper alloy	Wire connection cross section, finely stranded, min. (power connector)	0.75 mm <sup>2</sup>
Pollution degree (power connector)	2	Interlock type (power connector)	Push Pull
Connection cross-section AWG, max. (power connector)	13.00	Housing base material (power connector)	Zinc diecast, nickel-plated
Connection 2 (power connector)	Tension clamp	Plugging cycles (power connector)	≤ 100
Seal material (power connector)	NBR	Contact carrier material (power connector)	PA
Nominal voltage (power connector)	24 V		

**Technical data**

**Classifications**

ETIM 8.0	EC002597	ETIM 9.0	EC002597
ETIM 10.0	EC002597	ECLASS 14.0	27-44-03-18
ECLASS 15.0	27-44-03-18		


**IE-CD-V14SCRJ/VAPM24V-C**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

**Drawings**

[www.weidmueller.com](http://www.weidmueller.com)

**Dimensioned drawing**



**Dimensioned drawing**

