

**SAIL-M12BG-L-40PGR****Weidmüller Interface GmbH & Co. KG**Klingenbergstraße 26  
D-32758 Detmold  
Germany

www.weidmueller.com



Your peripheral devices should be supplied with greater power. With our new M12 plug-in connector, more than 250 V and 2 A is possible without problems. The compact A-, K-, L-, S- and T-coded M12 plug-in connectors are designed for the transmission of up to 630 V AC or 60 V DC and 12 A.

**General ordering data**

Version	Sensor/actuator line, One end without connector, M12, Number of poles : 5, 40 m, Female socket, straight, Shielded: No, LED: No, Sheath material: PUR, Halogen: No
Order No.	<a href="#">2455334000</a>
Type	SAIL-M12BG-L-40PGR
GTIN (EAN)	4099986897953
Qty.	1 items

## SAIL-M12BG-L-40PGR

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technical data

### Dimensions and weights

Net weight	3000 g
------------	--------

### Technical specifications for cable

Cable length	40 m	Sheathing colour	grey
Suitable for cable carriers	Yes	Core cross-section	1.5 mm <sup>2</sup>
Number of wires	5	Shielded	No
Halogen	No	Insulation	PP
Acceleration	5 m/s <sup>2</sup>	Bending radius, min., moving	7.5 x cable diameter
Bending radius, min., stationary	4 x cable diameter	Bending cycles	10 Mio
Speed	5 m/s	Sheath material	PUR
Cable length configurable	No	Outer cladding in accordance with UL AWM style	20939 (80 °C / 600 V)
Hybrid cable	No	Irradiation crosslinked	No
Welding spark resistance	No	Colour coding	brown, white, blue, black, pink
Temperature range, stationary	-40...80 °C	Resistant to welding beads	No
Temperature range, moving	-30...80 °C	Number of poles	5

### General technical data

Coding	L-coded	Connection thread	M12
Contact surface	Gold-plated	LED	No
Version	Female socket, straight	Housing main material	PUR
Insulation resistance	108 Ω	Contact material	Copper alloy
Nominal voltage	50 V	Nominal current	16 A
Protection degree	IP65, IP67, when screwed in	Plugging cycles	≤ 100
Pollution severity	3	Threaded ring material	Cu Zn
Temperature range of housing	-40 ... +85 °C	Tightening torque	M12: 0.8 - 1.2 Nm

### Electrical properties

Insulation resistance	108 Ω	Nominal voltage	50 V
-----------------------	-------	-----------------	------

### General standards

Connector standard	IEC 61076-2-111
--------------------	-----------------

### Standards

Connector standard	IEC 61076-2-111
--------------------	-----------------

### Plug, left

Plug left	M12, L-coded, Number of poles: 5, female contact, straight, plug, unshielded
-----------	--

### Plug, right

Plug right	Free conductor end
------------	--------------------

**SAIL-M12BG-L-40PGR**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Technical data**

**Classifications**

ETIM 8.0	EC001855	ETIM 9.0	EC001855
ETIM 10.0	EC001855	ECLASS 14.0	27-06-03-11
ECLASS 15.0	27-06-03-11		

SAIL-M12BG-L-40PGR

Weidmüller Interface GmbH & Co. KG  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

www.weidmueller.com

Drawings


Dimensioned drawing



Pole scheme



Wiring diagram



The ideal tool: Screwty® with torque function

