

## UR20-8DIO-P-3W-DIAG

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

[www.weidmueller.com](http://www.weidmueller.com)



Digital input and output modules More performance. Simplified. u-remote. Weidmüller u-remote – our innovative remote I/O concept with IP 20 which focuses purely on user benefits: tailored planning, faster installation, safer start-up, no more downtime. For considerably improved performance and greater productivity. Reduce the size of your cabinets with u-remote, thanks to the narrowest modular design on the market and the need for fewer power-feed modules. Our u-remote technology also offers tool-free assembly, while the modular "sandwich" design and integrated web server speed up installation, both in the cabinet and machine. Status LEDs on the channel and each u-remote module enable reliable diagnosis and rapid service. This and many other amazing ideas boost the availability of your machines and systems. And ensure smooth processes too. From planning to operation. u-remote stands for "More Performance". Simplified

### General ordering data

Version	Remote I/O module, IP20, Digital signals, Input, Output, 8-channel
Order No.	<a href="#">2456530000</a>
Type	UR20-8DIO-P-3W-DIAG
GTIN (EAN)	4050118471694
Qty.	1 items

## UR20-8DIO-P-3W-DIAG

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technical data

### Approvals

Approvals



ROHS	Conform
UL File Number Search	<a href="#">UL Website</a>
Certificate no. (cULus)	E141197
Certificate no. (cULusEX)	E223527

### Dimensions and weights

Depth	76 mm	Depth (inches)	2.9921 inch
Height	120 mm	Height (inches)	4.7244 inch
Width	11.5 mm	Width (inches)	0.4528 inch
Mounting dimension - height	128 mm	Net weight	83 g

### Temperatures

Storage temperature	-40 °C ... +85 °C	Operating temperature	-20 °C...60 °C
---------------------	-------------------	-----------------------	----------------

### Environmental Product Compliance

RoHS Compliance Status	Compliant with exemption		
RoHS Exemption (if applicable/known)	7a, 7cI		
REACH SVHC	Lead 7439-92-1, Diboron trioxide 1303-86-2, Lead monoxide 1317-36-8		
SCIP	b5ed5bad-cbfe-4ad3-903c-fc3d1093a415		
Product Carbon Footprint	Cradle to gate	8,704 kg CO2 eq.	

### digital inputs

Short-circuit-proof	Yes	Reverse polarity protection	No, Input voltage below -10 V can destroy the module
Number of digital inputs	8	Type	PNP switched
Sensor supply	≥ 0.3 A per connector, limited electronically	Input filter	Input delay adjustable from 0 to 40 ms
Input type	P-switching, for Type 1 and Type 3 sensors as per IEC 61131-2	Protective circuit	Constant current with thermal switch-off and automatic restart
Input voltage, high	> + 11 V referred to 0 V of the output power supply UOUT	Module diagnosis	Yes
Input voltage, low	<+ 5 V referred to 0 V of the output power supply UOUT	Individual channel diagnosis	only auxiliary voltage output
Sensor connection	2-wire, 3-wire		

## UR20-8DIO-P-3W-DIAG

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technical data

### digital outputs

Short-circuit-proof	Yes	Number of digital outputs	8
Type	PNP switched	Feedback-free	Yes
Resistive load (min. 47 Ω)	1 kHz	Output current per channel, max.	0.5 A
Individual channel diagnosis	Yes, Overcurrent monitoring > 0.5 A, line break detection	Actuator supply	≤ 0.3 A per connector; limited electronically
Protective circuit	Constant current with thermal switch-off and automatic restart	Module diagnosis	Yes
Switch-off energy (inductive)	<150 mJ / channel	Response time of the protective circuit (current limiting)	<100μs
Actuator connection	2-wire, 3-wire	Lamp load (12 W)	10 Hz
Inductive load (DC13)	0.2 Hz	Output current per module, max.	4 A
Sensor connection	2-wire, 3-wire		

### Connection data

Wire cross-section, finely stranded, max. (AWG)	AWG 16	Wire cross-section, finely stranded, min. (AWG)	AWG 26
Wire cross-section, solid, max. (AWG)	AWG 16	Wire cross-section, solid, min. (AWG)	AWG 26
Type of connection	PUSH IN	Wire cross-section, solid, max.	1.5 mm <sup>2</sup>
Wire cross-section, solid, min.	0.14 mm <sup>2</sup>	Wire connection cross section, finely stranded, max.	1.5 mm <sup>2</sup>
Wire connection cross section, finely stranded, min.	0.14 mm <sup>2</sup>		

### General data

Vibration resistance	5 Hz ≤ f ≤ 8.4 Hz: 3.5-mm amplitude as per IEC 60068-2-6, 8.4 Hz ≤ f ≤ 150 Hz: 1 g acceleration as per IEC 60068-2-6	UL 94 flammability rating	V-0
Test voltage	500 V	Surge voltage category	II
Pollution severity	2	Mounting rail	TS 35
Air pressure (operation)	≥ 795 hPa (height ≤ 2000 m) as per DIN EN 61131-2	Air humidity (transport)	10% to 95%, non-condensing as per DIN EN 61131-2
Air pressure (transport)	1013 hPa (height 0 m) to 700 hPa (height 3000 m) as per DIN EN 61131-2	Air pressure (storage)	1013 hPa (height 0 m) to 700 hPa (height 3000 m) as per DIN EN 61131-2
Air humidity (operation)	10% to 95%, non-condensing as per DIN EN 61131-2	Air humidity (storage)	10% to 95%, non-condensing as per DIN EN 61131-2
Shock	15 g over 11 ms, half sinus wave, acc. to IEC 60068-2-27		

### Power supply

Reverse polarity protection	No, Input voltage below -10 V can destroy the module	Supply voltage	24 V DC +20 %/ -15 %, via the system bus
Current consumption from IIN (the respective power segment)	8 mA	Current consumption from I <sub>sys</sub> , typ.	8 mA
Current consumption from IOUT (the respective power segment)	32 mA + I-Last		

**UR20-8DIO-P-3W-DIAG**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Technical data**

**System data**

Module type	Digital input module, Digital output module	Interface	u-remote system bus
Galvanic isolation	500 V DC between the current paths	Field bus protocol	PROFINET IRT, PROFINET RT, PROFIBUS DP-V1, EtherCAT, Modbus/TCP, EtherNet/IP, CANopen, DeviceNet, POWERLINK, CC-Link, CC-Link IE TSN
Possible connection	2-wire, 3-wire	Transmission speed of system bus, max.	48 MBit/s

**Classifications**

ETIM 8.0	EC001599	ETIM 9.0	EC001599
ETIM 10.0	EC001599	ECLASS 14.0	27-24-26-04
ECLASS 15.0	27-24-26-04		


**UR20-8DIO-P-3W-DIAG**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany


www.weidmueller.com

**Drawings**

**Block diagram**



**Connection diagram**



**Explanation of abbreviations**

**Digital input and output modules**

