

**ZQV 4N/3 RD****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Product image**

The distribution or multiplication of a potential to adjoining terminal blocks is realized via a cross-connection. Additional wiring effort can be easily avoided. Even if the poles are broken out, contact reliability in the terminal blocks is still ensured. Our portfolio offers pluggable and screwable cross-connection systems for modular terminal blocks.

**General ordering data**

Version	Cross-connector (terminal), Plugged, red, 32 A, Number of poles: 3, Pitch in mm (P): 6.10, Insulated: Yes, Width: 16 mm
Order No.	<a href="#">2460810000</a>
Type	ZQV 4N/3 RD
GTIN (EAN)	4050118476231
Qty.	60 items

## Technical data

### Approvals

Approvals



ROHS Conform

### Dimensions and weights

Depth	27.95 mm	Depth (inches)	1.1004 inch
Height	2.8 mm	Height (inches)	0.1102 inch
Width	16 mm	Width (inches)	0.6299 inch
Net weight	2.11 g		

### Temperatures

Storage temperature	-25 °C...55 °C	Ambient temperature	-5 °C...40 °C
Operating temperature	-60 °C...130 °C	Continuous operating temp., min.	-60 °C
Continuous operating temp., max.	130 °C		

### Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

### Material data

Basic material	Wemid	Colour	red
UL 94 flammability rating	V-0		

### Additional technical data

Type of fixing	Plugged	Explosion-tested version	Yes
----------------	---------	--------------------------	-----

### Dimensions

Pitch in mm (P)	6.10 mm
-----------------	---------

### General

Number of poles	3
-----------------	---

### Rating data

Rated voltage	400 V	Nominal current	32 A
---------------	-------	-----------------	------

### Important note

Product information Due to stability and temperature reasons It is only possible to break out 60% of contact elements. The usage of cross connectors reduces the rated voltage to 400 V.The voltage reduced to 25 V if cut cross connection with blank cut edges are used.

### Classifications

ETIM 8.0	EC000489	ETIM 9.0	EC000489
ETIM 10.0	EC000489	ECLASS 14.0	27-25-03-03

**Technical data**

---

ECLASS 15.0

27-25-03-03

---