

JPO 24VDC 0.2A M12S**Weidmüller Interface GmbH & Co. KG**Klingenbergsstraße 26
D-32758 Detmold
Germanywww.weidmueller.com

Weidmüller is now one of the industry's leading international providers of connectors. An important mainstay in this product family are the circular connectors, which Weidmüller groups under the product name SAI. In the development of SAI products, Weidmüller engineers have always concentrated on achieving rational, cost-effective installation concepts, and – in cooperation with major users – have supplied the markets with well-conceived products which set standards in terms of functionality and quality across the globe. An example is the Jackpac® product family. These modules are waterproof signal converters.

General ordering data

Version	JACKPAC, Optos, Rated control voltage: 18...24...30 V DC, Rated switching voltage: 3...33 V DC, M12 plug / plug, A-coded
Order No.	2465830000
Type	JPO 24VDC 0.2A M12S
GTIN (EAN)	4050118482522
Qty.	1 items

JPO 24VDC 0.2A M12S

Weidmüller Interface GmbH & Co. KG
Klingenbergsstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Approvals

Approvals



RoHS Conform

Dimensions and weights

Height	14.4 mm	Height (inches)	0.5669 inch
Width	36 mm	Width (inches)	1.4173 inch
Length	83 mm	Length (inches)	3.2677 inch
Net weight	54.03 g		

Temperatures

Storage temperature -20 °C...60 °C Operating temperature -20 °C...60 °C

Environmental Product Compliance

RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	6c
REACH SVHC	Lead 7439-92-1
SCIP	1b05ef5c-aeab-43a7-8ce0-9a79e97b9996

Input

Rated control voltage 18...24...30 V DC Rated control voltage 18 V...24 V...30 V DC

Control side

Rated control voltage 18...24...30 V DC Nominal control current 0.01 A DC
Input current for sensor 10 mA

Output

Rated switching voltage	min.	3 V
	Voltage type	DC
	max.	33 V

Rated switching voltage 3...33 V DC

Load side

Rated switching voltage 3...33 V DC Rated switching current 200 mA
Voltage drop at max. load ≤ 1 V

Insulation coordination

Rated voltage 32 V Surge voltage category I
Pollution severity 2 Protection degree IP67

Insulation coordination

Rated voltage 32 V Pollution severity 2
Surge voltage category I Protection degree IP67

JPO 24VDC 0.2A M12S

Weidmüller Interface GmbH & Co. KG
Klingenbergsstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data**output**

Switching voltage, max. 3...33 V DC

Technical specifications for cable

Shielded	No	Number of poles	4
----------	----	-----------------	---

Important note

Product information Length of connected cable smaller than 30m

Classifications

ETIM 8.0	EC001134	ETIM 9.0	EC001134
ETIM 10.0	EC001134	ECLASS 14.0	19-17-90-90
ECLASS 15.0	19-17-90-90		

JPO 24VDC 0.2A M12S

Weidmüller Interface GmbH & Co. KG
Klingenbergsstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings



Wiring diagram

