

ES EPG/HPG 60 WM 16

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Similar to illustration



Crimping tools for cable lugs, connectors and wire-end ferrules with interchangeable inserts

- extremely fast processing thanks to hydraulic support
- large processing range up to 300 mm²
- 270° revolving quick-action crimping head
- automatic pressure limitation and monitoring via pressure sensor
- electronic control and monitoring of the crimping process
- Saving of all crimping cycles and error messages to internal memory
- Reading of all cycles and error messages via USB
- Li-ion rechargeable battery with charge status indicator: 18 V, 2 Ah

General ordering data

Version	Crimping tool insert, 16mm ² , WM crimp
Order No.	2469550000
Type	ES EPG/HPG 60 WM 16
GTIN (EAN)	4050118483833
Qty.	1 items

ES EPG/HPG 60 WM 16

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	22 mm	Depth (inches)	0.8661 inch
Height	42 mm	Height (inches)	1.6535 inch
Width	42 mm	Width (inches)	1.6535 inch
Net weight	131.12 g		

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

Crimp inserts

Crimping width	7 mm	Crimp cross-section copper	16
Crimping width in mm	7		

Description of contact

Type of contact	Euro series cable lug	Conductor cross-section, max. AWG	6
Conductor cross-section, min. AWG	6	Crimping range, max.	16 mm ²

tool data crimping

Crimping type/profile	WM crimp
Cable lug cross section	nominal 16 mm ²

Classifications

ETIM 8.0	EC001282	ETIM 9.0	EC001282
ETIM 10.0	EC001282	ECLASS 14.0	21-04-90-90
ECLASS 15.0	21-04-90-90		

ES EPG/HPG 60 WM 16

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Accessories

Tools



Crimping tools for cable lugs, connectors and wire-end ferrules with interchangeable inserts

- extremely fast processing thanks to hydraulic support
- large processing range up to 300 mm²
- 270° revolving quick-action crimping head
- automatic pressure limitation and monitoring via pressure sensor
- electronic control and monitoring of the crimping process
- Saving of all crimping cycles and error messages to internal memory
- Reading of all cycles and error messages via USB
- Li-ion rechargeable battery with charge status indicator: 18 V, 2 Ah

General ordering data

Type	EPG 60	Version
Order No.	2453810000	Pressing tools, Tools, Pressing tool, 6mm ² , 300mm ² , Hexagonal crimp, WM crimp, Indent crimp, Trapezoidal crimp, Oval crimping
GTIN (EAN)	4050118468434	
Qty.	1 ST	
Type	HPG 60	Version
Order No.	2453820000	6mm ² , 300mm ² , Hexagonal crimp, WM crimp, Indent crimp, Trapezoidal crimp, Oval crimping
GTIN (EAN)	4050118468427	
Qty.	1 ST	

16 mm²

The use of insulated connectors guarantees users consistent electrical connection quality in the long term.

- Wide range of insulated and non-insulated cable lugs and connectors
- Tubular cable lugs according to current market standards (Euroseries)
- Compression cable lugs acc. to DIN 46235
- Sheet metal cable lugs acc. to DIN 46234
- Insulated ring cable lugs to DIN 46237
- Insulated pin cable lugs to DIN 46231

General ordering data

Type	KRN-M5/-16	Version
Order No.	1496970000	cable lug, terminal end, 16 mm ² , 16 mm ² - 16 mm ²
GTIN (EAN)	4050118306569	
Qty.	100 ST	
Type	KRN-M6/-16	Version
Order No.	1496980000	cable lug, terminal end, 16 mm ² , 16 mm ² - 16 mm ²
GTIN (EAN)	4050118306583	
Qty.	100 ST	
Type	KRN-M8/-16	Version
Order No.	1496990000	cable lug, terminal end, 16 mm ² , 16 mm ² - 16 mm ²
GTIN (EAN)	4050118306514	
Qty.	100 ST	

ES EPG/HPG 60 WM 16

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Accessories

Type	KRN-M10/-16	Version
Order No.	1497000000	cable lug, terminal end,16 mm ² ,16 mm ² - 16 mm ²
GTIN (EAN)	4050118306460	
Qty.	100 ST	
Type	KRN-M12/-16	Version
Order No.	1497010000	cable lug, terminal end,16 mm ² ,16 mm ² - 16 mm ²
GTIN (EAN)	4050118306538	
Qty.	100 ST	
Type	KWN-M5/-16 90	Version
Order No.	1497080000	cable lug, terminal end,16 mm ² ,16 mm ² - 16 mm ²
GTIN (EAN)	4050118306392	
Qty.	100 ST	
Type	KWN-M6/16 90	Version
Order No.	1497090000	cable lug, terminal end,16 mm ² ,16 mm ² - 16 mm ²
GTIN (EAN)	4050118306743	
Qty.	100 ST	
Type	KWN-M8/-16 90	Version
Order No.	1497100000	cable lug, terminal end,16 mm ² ,16 mm ² - 16 mm ²
GTIN (EAN)	4050118306804	
Qty.	100 ST	
Type	KWN-M10/-16 90	Version
Order No.	1497110000	cable lug, terminal end,16 mm ² ,16 mm ² - 16 mm ²
GTIN (EAN)	4050118306705	
Qty.	100 ST	
Type	KWN-M12/-16 90	Version
Order No.	1497120000	cable lug, terminal end,16 mm ² ,16 mm ² - 16 mm ²
GTIN (EAN)	4050118306736	
Qty.	100 ST	
Type	KWN-M5/-16 45	Version
Order No.	1496850000	cable lug, terminal end,16 mm ² ,16 mm ² - 16 mm ²
GTIN (EAN)	4050118306408	
Qty.	100 ST	
Type	KWN-M6/-16 45	Version
Order No.	1496870000	cable lug, terminal end,16 mm ² ,16 mm ² - 16 mm ²
GTIN (EAN)	4050118306446	
Qty.	100 ST	
Type	KWN-M8/-16 45	Version
Order No.	1496880000	cable lug, terminal end,16 mm ² ,16 mm ² - 16 mm ²
GTIN (EAN)	4050118306422	
Qty.	100 ST	
Type	KWN-M10/-16 45	Version
Order No.	1496890000	cable lug, terminal end,16 mm ² ,16 mm ² - 16 mm ²
GTIN (EAN)	4050118306194	
Qty.	100 ST	
Type	VSTN/-16	Version
Order No.	1497140000	cable lug, terminal end,16 mm ² ,16 mm ² ,None
GTIN (EAN)	4050118306620	
Qty.	50 ST	
Type	KP-M5/-16	Version
Order No.	1497920000	cable lug, terminal end,16 mm ²
GTIN (EAN)	4050118307542	
Qty.	100 ST	

ES EPG/HPG 60 WM 16

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Accessories

Type	KP-M6/-16	Version
Order No.	1497930000	cable lug, terminal end,16 mm ²
GTIN (EAN)	4050118307290	
Qty.	100 ST	
Type	KP-M8/-16	Version
Order No.	1497940000	cable lug, terminal end,16 mm ²
GTIN (EAN)	4050118307269	
Qty.	100 ST	
Type	KP-M10/-16	Version
Order No.	1497950000	cable lug, terminal end,16 mm ²
GTIN (EAN)	4050118307450	
Qty.	100 ST	
Type	KP-M12/-16	Version
Order No.	1497960000	cable lug, terminal end,16 mm ²
GTIN (EAN)	4050118307436	
Qty.	100 ST	
Type	KWPN-M6/-16 90	Version
Order No.	1497440000	cable lug, terminal end,16 mm ²
GTIN (EAN)	4050118306644	
Qty.	100 ST	
Type	KWPN-M8/-16 90	Version
Order No.	1497450000	cable lug, terminal end,16 mm ²
GTIN (EAN)	4050118306873	
Qty.	100 ST	
Type	KWPN-M10/-16 90	Version
Order No.	1497470000	cable lug, terminal end,16 mm ²
GTIN (EAN)	4050118307016	
Qty.	100 ST	
Type	KWPN-M12/-16 90	Version
Order No.	1497480000	cable lug, terminal end,16 mm ²
GTIN (EAN)	4050118306866	
Qty.	100 ST	
Type	VPN/-16	Version
Order No.	1498630000	cable lug, terminal end,16 mm ² ,16 mm ² ,None
GTIN (EAN)	4050118307856	
Qty.	100 ST	
Type	KQN-M5/-16	Version
Order No.	1494070000	cable lug, terminal end,16 mm ²
GTIN (EAN)	4050118303650	
Qty.	100 ST	
Type	KQN-M6/-16	Version
Order No.	1494080000	cable lug, terminal end,16 mm ²
GTIN (EAN)	4050118303636	
Qty.	100 ST	
Type	KQN-M8/-16	Version
Order No.	1494090000	cable lug, terminal end,16 mm ²
GTIN (EAN)	4050118303742	
Qty.	100 ST	
Type	KQN-M10/-16	Version
Order No.	1494100000	cable lug, terminal end,16 mm ²
GTIN (EAN)	4050118303728	
Qty.	100 ST	

ES EPG/HPG 60 WM 16

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Accessories

Type	KQN-M12/-16	Version
Order No.	1494110000	cable lug, terminal end,16 mm ²
GTIN (EAN)	4050118303773	
Qty.	100 ST	
Type	KQNG-M6/-16	Version
Order No.	1492700000	cable lug, terminal end,16 mm ² ,16 mm ²
GTIN (EAN)	4050118302493	
Qty.	50 ST	
Type	KQNG-M8/-16	Version
Order No.	1492710000	cable lug, terminal end,16 mm ² ,16 mm ²
GTIN (EAN)	4050118302677	
Qty.	50 ST	
Type	KSN/-16	Version
Order No.	1492790000	cable lug, terminal end,16 mm ² ,16 mm ²
GTIN (EAN)	4050118302745	
Qty.	100 ST	
Type	VPLN/-16	Version
Order No.	1492900000	cable lug, terminal end,16 mm ² ,16 mm ² ,None
GTIN (EAN)	4050118302714	
Qty.	100 ST	
Type	VSTN/16	Version
Order No.	1493040000	cable lug, terminal end,16 mm ² ,16 mm ² ,None
GTIN (EAN)	4050118302981	
Qty.	100 ST	