


LLF 7.50/02/90V 5.0SN BK BX

Weidmüller Interface GmbH & Co. KG
Klingenbergsstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Product image

The sturdy, direct connection for extreme current and voltage requirements in all power electronics applications such as solar inverters, frequency converters, servo-controllers and power supplies.

General ordering data

Version	Printed circuit board terminals, 7.50 mm, Number of poles: 2, 90°, Solder pin length (l): 5 mm, tinned, black, PUSH IN with lever, Clamping range, max. : 6 mm ² , Box
Order No.	2471530000
Type	LLF 7.50/02/90V 5.0SN BK BX
GTIN (EAN)	4050118550139
Qty.	100 items
Product data	IEC: 1000 V / 41 A / 0.5 - 6 mm ² UL: 600 V / 35 A / AWG 24 - AWG 8
Packaging	Box

LLF 7.50/02/90V 5.0SN BK BX

Weidmüller Interface GmbH & Co. KG
Klingenbergsstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Approvals

Approvals



ROHS Conform
UL File Number Search [UL Website](#)
Certificate No. (cURus) E60693

Dimensions and weights

Depth	22.07 mm	Depth (inches)	0.8689 inch
Height	36.55 mm	Height (inches)	1.439 inch
Height of lowest version	31.55 mm	Width	16.8 mm
Width (inches)	0.6614 inch	Net weight	7.36 g

Environmental Product Compliance

RoHS Compliance Status Compliant without exemption
REACH SVHC No SVHC above 0.1 wt%

System parameters

Product family	OMNIMATE Power - series LL	Wire connection method	PUSH IN with lever
Mounting onto the PCB	THT solder connection	Conductor outlet direction	90°
Pitch in mm (P)	7.50 mm	Pitch in inches (P)	0.295 "
Number of poles	2	Pin series quantity	1
Fitted by customer	No	Number of rows	1
Solder pin length (l)	5 mm	Solder pin dimensions	d = 1.5 mm
Solder eyelet hole diameter (D)	2 mm	Solder eyelet hole diameter tolerance (D)+ 0.1 mm	
Number of solder pins per pole	1	Stripping length	12 mm
L1 in mm	7.50 mm	L1 in inches	0.295 "
Touch-safe protection acc. to DIN VDE 0470	IP 20	Touch-safe protection acc. to DIN VDE 57 106	Safe from finger touch
Protection degree	IP20		

Material data

Insulating material	Wemid (PA)	Colour	black
Colour chart (similar)	RAL 9011	Insulating material group	I
Moisture Level (MSL)		UL 94 flammability rating	V-0
Contact material	Cu-alloy	Contact surface	tinned
Layer structure of solder connection	4...10 µm Sn matt	Storage temperature, min.	-40 °C
Storage temperature, max.	70 °C	Operating temperature, min.	-40 °C
Operating temperature, max.	120 °C		

Conductors suitable for connection

Clamping range, min.	0.25 mm ²
Clamping range, max.	6 mm ²
Wire connection cross section AWG, min.	AWG 24
Wire connection cross section AWG, max.	AWG 8
Solid, min. H05(07) V-U	0.5 mm ²
Solid, max. H05(07) V-U	6 mm ²
Stranded, min. H07V-R	0.5 mm ²

LLF 7.50/02/90V 5.0SN BK BX

Weidmüller Interface GmbH & Co. KG
Klingenbergsstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Flexible, min. H05(07) V-K	0.5 mm ²																																																																																																												
Flexible, max. H05(07) V-K	6 mm ²																																																																																																												
w. plastic collar ferrule, DIN 46228 pt 4, 0.25 mm ² min.																																																																																																													
w. plastic collar ferrule, DIN 46228 pt 4, 6 mm ² max.																																																																																																													
w. wire end ferrule, DIN 46228 pt 1, 0.25 mm ² min.																																																																																																													
w. wire end ferrule, DIN 46228 pt 1, 6 mm ² max.																																																																																																													
Clampable conductor	<table border="1"> <tbody> <tr> <td>Cross-section for conductor connection</td><td>Type</td><td>fine-wired</td></tr> <tr> <td></td><td>nominal</td><td>0.5 mm²</td></tr> <tr> <td>wire end ferrule</td><td>Stripping length</td><td>nominal 14 mm</td></tr> <tr> <td></td><td>Recommended wire-end ferrule</td><td>H0,5/18 OR</td></tr> <tr> <td>Cross-section for conductor connection</td><td>Type</td><td>fine-wired</td></tr> <tr> <td></td><td>nominal</td><td>1 mm²</td></tr> <tr> <td>wire end ferrule</td><td>Stripping length</td><td>nominal 15 mm</td></tr> <tr> <td></td><td>Recommended wire-end ferrule</td><td>H1,0/18 GE</td></tr> <tr> <td>Cross-section for conductor connection</td><td>Type</td><td>fine-wired</td></tr> <tr> <td></td><td>nominal</td><td>1.5 mm²</td></tr> <tr> <td>wire end ferrule</td><td>Stripping length</td><td>nominal 15 mm</td></tr> <tr> <td></td><td>Recommended wire-end ferrule</td><td>H1,5/18D SW</td></tr> <tr> <td></td><td>Stripping length</td><td>nominal 12 mm</td></tr> <tr> <td></td><td>Recommended wire-end ferrule</td><td>H1,5/12</td></tr> <tr> <td>Cross-section for conductor connection</td><td>Type</td><td>fine-wired</td></tr> <tr> <td></td><td>nominal</td><td>0.75 mm²</td></tr> <tr> <td>wire end ferrule</td><td>Stripping length</td><td>nominal 14 mm</td></tr> <tr> <td></td><td>Recommended wire-end ferrule</td><td>H0,75/18 W</td></tr> <tr> <td>Cross-section for conductor connection</td><td>Type</td><td>fine-wired</td></tr> <tr> <td></td><td>nominal</td><td>2.5 mm²</td></tr> <tr> <td>wire end ferrule</td><td>Stripping length</td><td>nominal 14 mm</td></tr> <tr> <td></td><td>Recommended wire-end ferrule</td><td>H2,5/19D BL</td></tr> <tr> <td></td><td>Stripping length</td><td>nominal 12 mm</td></tr> <tr> <td></td><td>Recommended wire-end ferrule</td><td>H2,5/12</td></tr> <tr> <td>Cross-section for conductor connection</td><td>Type</td><td>fine-wired</td></tr> <tr> <td></td><td>nominal</td><td>4 mm²</td></tr> <tr> <td>wire end ferrule</td><td>Stripping length</td><td>nominal 12 mm</td></tr> <tr> <td></td><td>Recommended wire-end ferrule</td><td>H4,0/12</td></tr> <tr> <td></td><td>Stripping length</td><td>nominal 14 mm</td></tr> <tr> <td></td><td>Recommended wire-end ferrule</td><td>H4,0/20D GR</td></tr> <tr> <td>Cross-section for conductor connection</td><td>Type</td><td>fine-wired</td></tr> <tr> <td></td><td>nominal</td><td>6 mm²</td></tr> <tr> <td>wire end ferrule</td><td>Stripping length</td><td>nominal 14 mm</td></tr> <tr> <td></td><td>Recommended wire-end ferrule</td><td>H6,0/20 SW</td></tr> <tr> <td></td><td>Stripping length</td><td>nominal 12 mm</td></tr> <tr> <td></td><td>Recommended wire-end ferrule</td><td>H6,0/12</td></tr> </tbody> </table>	Cross-section for conductor connection	Type	fine-wired		nominal	0.5 mm ²	wire end ferrule	Stripping length	nominal 14 mm		Recommended wire-end ferrule	H0,5/18 OR	Cross-section for conductor connection	Type	fine-wired		nominal	1 mm ²	wire end ferrule	Stripping length	nominal 15 mm		Recommended wire-end ferrule	H1,0/18 GE	Cross-section for conductor connection	Type	fine-wired		nominal	1.5 mm ²	wire end ferrule	Stripping length	nominal 15 mm		Recommended wire-end ferrule	H1,5/18D SW		Stripping length	nominal 12 mm		Recommended wire-end ferrule	H1,5/12	Cross-section for conductor connection	Type	fine-wired		nominal	0.75 mm ²	wire end ferrule	Stripping length	nominal 14 mm		Recommended wire-end ferrule	H0,75/18 W	Cross-section for conductor connection	Type	fine-wired		nominal	2.5 mm ²	wire end ferrule	Stripping length	nominal 14 mm		Recommended wire-end ferrule	H2,5/19D BL		Stripping length	nominal 12 mm		Recommended wire-end ferrule	H2,5/12	Cross-section for conductor connection	Type	fine-wired		nominal	4 mm ²	wire end ferrule	Stripping length	nominal 12 mm		Recommended wire-end ferrule	H4,0/12		Stripping length	nominal 14 mm		Recommended wire-end ferrule	H4,0/20D GR	Cross-section for conductor connection	Type	fine-wired		nominal	6 mm ²	wire end ferrule	Stripping length	nominal 14 mm		Recommended wire-end ferrule	H6,0/20 SW		Stripping length	nominal 12 mm		Recommended wire-end ferrule	H6,0/12
Cross-section for conductor connection	Type	fine-wired																																																																																																											
	nominal	0.5 mm ²																																																																																																											
wire end ferrule	Stripping length	nominal 14 mm																																																																																																											
	Recommended wire-end ferrule	H0,5/18 OR																																																																																																											
Cross-section for conductor connection	Type	fine-wired																																																																																																											
	nominal	1 mm ²																																																																																																											
wire end ferrule	Stripping length	nominal 15 mm																																																																																																											
	Recommended wire-end ferrule	H1,0/18 GE																																																																																																											
Cross-section for conductor connection	Type	fine-wired																																																																																																											
	nominal	1.5 mm ²																																																																																																											
wire end ferrule	Stripping length	nominal 15 mm																																																																																																											
	Recommended wire-end ferrule	H1,5/18D SW																																																																																																											
	Stripping length	nominal 12 mm																																																																																																											
	Recommended wire-end ferrule	H1,5/12																																																																																																											
Cross-section for conductor connection	Type	fine-wired																																																																																																											
	nominal	0.75 mm ²																																																																																																											
wire end ferrule	Stripping length	nominal 14 mm																																																																																																											
	Recommended wire-end ferrule	H0,75/18 W																																																																																																											
Cross-section for conductor connection	Type	fine-wired																																																																																																											
	nominal	2.5 mm ²																																																																																																											
wire end ferrule	Stripping length	nominal 14 mm																																																																																																											
	Recommended wire-end ferrule	H2,5/19D BL																																																																																																											
	Stripping length	nominal 12 mm																																																																																																											
	Recommended wire-end ferrule	H2,5/12																																																																																																											
Cross-section for conductor connection	Type	fine-wired																																																																																																											
	nominal	4 mm ²																																																																																																											
wire end ferrule	Stripping length	nominal 12 mm																																																																																																											
	Recommended wire-end ferrule	H4,0/12																																																																																																											
	Stripping length	nominal 14 mm																																																																																																											
	Recommended wire-end ferrule	H4,0/20D GR																																																																																																											
Cross-section for conductor connection	Type	fine-wired																																																																																																											
	nominal	6 mm ²																																																																																																											
wire end ferrule	Stripping length	nominal 14 mm																																																																																																											
	Recommended wire-end ferrule	H6,0/20 SW																																																																																																											
	Stripping length	nominal 12 mm																																																																																																											
	Recommended wire-end ferrule	H6,0/12																																																																																																											
Reference text	Length of ferrules is to be chosen depending on the product and the rated voltage., The outside diameter of the plastic collar should not be larger than the pitch (P)																																																																																																												

LLF 7.50/02/90V 5.0SN BK BX

Weidmüller Interface GmbH & Co. KG
Klingenbergsstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Rated data acc. to IEC

tested acc. to standard	In accordance with IEC 60947-7-1	Rated current, min. number of poles (Tu=20°C)	41 A
Rated current, max. number of poles (Tu=20°C)	35 A	Rated current, min. number of poles (Tu=40°C)	41 A
Rated current, max. number of poles (Tu=40°C)	30 A	Rated voltage for surge voltage class / pollution degree II/2	1000 V
Rated voltage for surge voltage class / pollution degree III/2	1000 V	Rated voltage for surge voltage class / pollution degree III/3	1000 V
Rated impulse voltage for surge voltage class/ pollution degree II/2	8 kV	Rated impulse voltage for surge voltage class/ pollution degree III/2	8 kV
Rated impulse voltage for surge voltage class/ contamination degree III/3	8 kV		

Rated data acc. to CSA

Rated voltage (Use group B / CSA)	600 V	Rated voltage (Use group C / CSA)	600 V
Rated voltage (Use group D / CSA)	600 V	Rated current (Use group B / CSA)	35 A
Rated current (Use group C / CSA)	35 A	Rated current (Use group D / CSA)	5 A
Wire cross-section, AWG, min.	AWG 24	Wire cross-section, AWG, max.	AWG 8

Rated data acc. to UL 1059

Institute (cURus)	CURUS	Certificate No. (cURus)	E60693
Rated voltage (Use group B / UL 1059)	600 V	Rated voltage (Use group C / UL 1059)	600 V
Rated voltage (Use group D / UL 1059)	600 V	Rated current (Use group B / UL 1059)	35 A
Rated current (Use group C / UL 1059)	35 A	Rated current (Use group D / UL 1059)	5 A
Wire cross-section, AWG, min.	AWG 24	Wire cross-section, AWG, max.	AWG 8
Reference to approval values	Specifications are maximum values, details - see approval certificate.		

Packing

Packaging	Box	VPE length	219.00 mm
VPE width	213.00 mm	VPE height	48.00 mm

Type tests

Test: Durability of markings	Standard	IEC 60947-7-4 section 7.1.4 / 08.13
	Test	mark of origin, type identification, type of material, pitch, durability, stripping length
	Evaluation	available
Test: Clampable cross section	Standard	IEC 60999-1 section 7 and 9.1 / 11.99, IEC 60947-1 section 8.2.4.5.1 / 03.11
	Conductor type	Type of conductor solid 0.5 mm ² and conductor cross-section
		Type of conductor stranded 0.5 mm ² and conductor cross-section
		Type of conductor solid 6 mm ² and conductor cross-section
		Type of conductor stranded 6 mm ² and conductor cross-section
		Type of conductor AWG 24/19 and conductor cross-section

LLF 7.50/02/90V 5.0SN BK BX

Weidmüller Interface GmbH & Co. KG
Klingenbergsstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Test for damage to and accidental loosening of conductors	Type of conductor and conductor cross-section	AWG 24/1
	Type of conductor and conductor cross-section	AWG 10/1
	Type of conductor and conductor cross-section	AWG 10/19
	Type of conductor and conductor cross-section	H07V-K10
	Evaluation	passed
	Standard	IEC 60999-1 section 9.4 / 11.99, IEC 60999-1 section 9.5 / 11.99
	Requirement	0.3 kg
	Conductor type	Type of conductor and conductor cross-section
		H05V-K0.5
		Type of conductor and conductor cross-section
Pull-out test	Evaluation	passed
	Requirement	0.4 kg
	Conductor type	Type of conductor and conductor cross-section
		H07V-K1
		Type of conductor and conductor cross-section
	Evaluation	passed
	Requirement	0.7 kg
	Conductor type	Type of conductor and conductor cross-section
		H07V-K2.5
		Type of conductor and conductor cross-section
Pull-out test	Evaluation	passed
	Requirement	0.9 kg
	Conductor type	Type of conductor and conductor cross-section
		H07V-K4
		Type of conductor and conductor cross-section
	Evaluation	passed
	Requirement	1.4 kg
	Conductor type	Type of conductor and conductor cross-section
		H07V-K6
		Type of conductor and conductor cross-section
Pull-out test	Evaluation	passed
	Standard	DIN EN 60999-1 section 9.5 / 12.00
	Requirement	≥20 N
	Conductor type	Type of conductor and conductor cross-section
Pull-out test		H05V-K0.5
		Type of conductor and conductor cross-section

LLF 7.50/02/90V 5.0SN BK BX

Weidmüller Interface GmbH & Co. KG
Klingenbergsstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Evaluation	passed	
Requirement	≥ 50 N	
Conductor type	Type of conductor and conductor cross-section	H07V-K2.5
	Type of conductor and conductor cross-section	H07V-U2.5
Evaluation	passed	
Requirement	≥ 60 N	
Conductor type	Type of conductor and conductor cross-section	H07V-K4
	Type of conductor and conductor cross-section	H07V-U4.0
Evaluation	passed	
Requirement	≥ 80 N	
Conductor type	Type of conductor and conductor cross-section	H07V-K6
	Type of conductor and conductor cross-section	H07V-U6
Evaluation	passed	
Requirement	≥ 35 N	
Conductor type	Type of conductor and conductor cross-section	H07V-K1
	Type of conductor and conductor cross-section	H07V-U1
Evaluation	passed	

Important note

IPC conformity Conformity: The products are developed, manufactured and delivered according international recognized standards and norms and comply with the assured properties in the data sheet resp. fulfill decorative properties in accordance with IPC-A-610 "Class 2". Further claims on the products can be evaluated on request.

Notes

- Additional variants on request
- Rated current related to rated cross-section & min. No. of poles.
- Wire end ferrule without plastic collar to DIN 46228/1
- Wire end ferrule with plastic collar to DIN 46228/4
- P on drawing = pitch
- Rated data refer only to the component itself. Clearance and creepage distances to other components are to be designed in accordance with the relevant application standards.
- The test point can only be used as potential-pickup point.
- The single-position PCB terminal block can be used for voltages up to 1500 V (DC) and 1000 V (AC). The relevant device standard and the appropriate required clearances and creepage distances should be observed in the application
- Long term storage of the product with average temperature of 50 °C and maximum humidity 70%, 36 months

Classifications

ETIM 8.0	EC002643	ETIM 9.0	EC002643
ETIM 10.0	EC002643	ECLASS 14.0	27-46-01-01
ECLASS 15.0	27-46-01-01		


LLF 7.50/02/90V 5.0SN BK BX

Weidmüller Interface GmbH & Co. KG
Klingenbergsstraße 26
D-32758 Detmold
Germany


www.weidmueller.com

Drawings


Product image




Dimensional drawing



Derating curve



Derating curve



Product benefits



Power up to UL 600 VOffset solder pins

Product benefits



Tool-free wiringTop contact security


LLF 7.50/02/90V 5.0SN BK BX

Weidmüller Interface GmbH & Co. KG
Klingenbergsstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

Product benefits



Maximum diagnosis flexibility Easily accessible test point

LLF 7.50/02/90V 5.0SN BK BX

Weidmüller Interface GmbH & Co. KG
Klingenbergsstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Accessories

Slotted screwdriver



VDE insulated slot-head screwdriver, SDI DIN 7437, ISO 2380/2, drive output acc. to DIN 5264, ISO 2380/1.
SoftFinish grip

General ordering data

Type	SDIS 0.5X3.0X100	Version
Order No.	9008380000	Screwdriver, Screwdriver
GTIN (EAN)	4032248056347	
Qty.	1 ST	
Type	SDS 0.5X3.0X80	Version
Order No.	9008320000	Screwdriver, Screwdriver
GTIN (EAN)	4032248056262	
Qty.	1 ST	

Additional accessories



No task is too small when creating the perfect solution. Connections form just one part of the overall process. Small details are often the key to the perfect solution in applications where potentials are tested, grouped or even isolated.

A system is not a system without small but essential details:

- Test plugs ensure reliable pick-up from diagnostic sockets

In tandem with the manufacturing process and application.

General ordering data

Type	PS 2.0 MC	Version
Order No.	0310000000	PCB plug-in connector, Accessories, Test plug, red, Number of poles:
GTIN (EAN)	4008190000059	1
Qty.	20 ST	

LLF 7.50/02/90V 5.0SN BK BX

Weidmüller Interface GmbH & Co. KG
Klingenbergsstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Accessories

Tools



- Stripping tools with automatic self-adjustment
- For flexible and solid conductors
- Ideally suitable for mechanical and plant engineering, railway and rail traffic, wind energy, robot technology, explosion protection as well as marine, offshore and ship building sectors
- Stripping length adjustable via end stop
- Automatic opening of clamping jaws after stripping
- No fanning-out of individual conductors
- Adjustable to diverse insulation thicknesses
- Double-insulated cables in two process steps without special adjustment
- No play in self-adjusting cutting unit
- Long service life
- Optimised ergonomic design

General ordering data

Type	STRIPAX	Version
Order No.	9005000000	Tools, Stripping and cutting tool
GTIN (EAN)	4008190072506	
Qty.	1 ST	