



**HDC AOC 6 FS****Weidmüller Interface GmbH & Co. KG**Klingenbergstraße 26  
D-32758 Detmold  
Germany

www.weidmueller.com



The AOC series ensures safe operation of current transformer secondary circuits by reliably preventing open circuit conditions.

Its integrated short circuit mechanism protects both personnel and equipment from dangerous induced voltages. The compact design combined with robust HDC technology delivers dependable performance in demanding energy and automation environments.

**General ordering data**

Version	HDC insert, Female, 500 V, 40 A, Number of poles: 6, Screw connection, Installation size: 3
Order No.	<a href="#">2466800000</a>
Type	HDC AOC 6 FS
GTIN (EAN)	4050118501568
Qty.	1 items

## HDC AOC 6 FS

Weidmüller Interface GmbH & Co. KG  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

www.weidmueller.com

## Technical data

## Approvals

ROHS	Conform
------	---------

## Dimensions and weights

Depth	34.8 mm	Depth (inches)	1.3701 inch
Height	41.7 mm	Height (inches)	1.6417 inch
Width	51 mm	Width (inches)	2.0079 inch
Net weight	66 g		

## Temperatures

Limit temperature	-40 °C ... 125 °C
-------------------	-------------------

## Environmental Product Compliance

RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	6c
REACH SVHC	Lead 7439-92-1, Potassium perfluorobutane sulfonate 29420-49-3
SCIP	b67daa31-7dca-434d-8290-da7fb52f83a2

## Dimensions

Width	51 mm	Total length base	34.8 mm
Height of socket	41.7 mm		

## General data

Number of poles	6	Plugging cycles, silver	≥ 500
Plugging cycles, gold	≥ 500	Type of connection	Screw connection
Installation size	3	UL 94 flammability rating	V-0
Volume resistance	2.00 mΩ	Colour	Light Grey
Insulation resistance	≥ 10 <sup>10</sup> Ω	Insulating material	Polyester glass-fibre reinforced, Polycarbonate
Conductor cross-section	3 mm <sup>2</sup>	Tightening torque, max. PE connection	1.5 Nm
Type	Female	Pollution severity	3
Tightening torque, min. PE connection	1.2 Nm	Basic material	Polycarbonate, glass fibre reinforced
Series	AOC	Rated voltage (DIN EN 61984)	500 V
Rated impulse voltage (DIN EN 61984)	6 kV	Rated current (DIN EN 61984)	40 A
Free from halogens	false	Low smoke acc. DIN EN 45545-2	Yes
BG	3		

## Connection data PE

Connection type PE	Screw connection	Stripping length PE connection	11 mm
Blade size, crosshead	0.6 x 3.5 mm	Tightening torque, max. PE connection	1.5 Nm
Tightening torque, min. PE connection	1.2 Nm	Fixing screw	M 4
Rated cross-section	4 mm <sup>2</sup>	Wire cross section, AWG (PE), min.	AWG 16
Wire cross section, AWG (PE), max.	AWG 12		

## Signal contact

Tightening torque, signal contact, max.	1.5 Nm	Tightening torque, signal contact, min.	1.2 Nm
---	--------	---	--------

## Technical data



### Version

Wire connection cross section AWG, max.	AWG 12	Stripping length, rated connection	11 mm
Type of connection	Screw connection	Installation size	3
Volume resistance	2.00 mΩ	Wire connection cross section AWG, min.	AWG 16
Wire cross-section, solid, max.	4 mm <sup>2</sup>	Wire cross-section, solid, min.	1.5 mm <sup>2</sup>
Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/4, max.	4 mm <sup>2</sup>	Wire connection cross section, finely stranded, max.	4 mm <sup>2</sup>
Wire connection cross section, finely stranded, min.	1.5 mm <sup>2</sup>	Conductor cross-section, max.	4 mm <sup>2</sup>
Conductor cross-section, min.	1.5 mm <sup>2</sup>	Basic material	Polycarbonate, glass fibre reinforced
BG	3		

### Classifications

ETIM 8.0	EC000438	ETIM 9.0	EC000438
ETIM 10.0	EC000438	ECLASS 14.0	27-44-02-05
ECLASS 15.0	27-44-02-05		

Connection diagram



Three-phase Anti-open Circuit Diagram