

FAD BLK4 2XSL20

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



The FAD TSX front adapters with pre-assembled cables provide safe migration from the TSX cards to other PLC systems or to the u-remote modules from Weidmüller.

- Can be plugged into TS35 terminal rail

General ordering data

Order No.	2494590000
Type	FAD BLK4 2XSL20
GTIN (EAN)	8430243373029
Qty.	1 items

FAD BLK4 2XSL20

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Approvals

Approvals



ROHS Conform

Dimensions and weights

Depth	24 mm	Depth (inches)	0.9449 inch
Height	218 mm	Height (inches)	8.5827 inch
Width	54 mm	Width (inches)	2.126 inch
Net weight	237.91 g		

Temperatures

Storage temperature	-40...60 °C	Operating temperature	-25...50 °C
---------------------	-------------	-----------------------	-------------

Environmental Product Compliance

RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	6c
REACH SVHC	Lead 7439-92-1
SCIP	348848c5-21ff-4d79-b541-7c34c4908172

Connection data

Connection (field side)	2 x Connector according IEC60603-13/DIN41651 20 p
-------------------------	---------------------------------------------------------

Connection data

Connection (field side)	2 x Connector according IEC60603-13/DIN41651 20 p
-------------------------	---------------------------------------------------------

Ratings data

Operating voltage	30 V AC / 60 V DC	Max. current per channel	3 A
Max. current per byte	2 A	Total operating current	6 A

Insulation coordination (EN50178)

According to	DIN EN 50178	Rated insulation voltage	50 V AC / 71 V DC
Surge voltage category	III	Pollution severity level	2
Insulation test voltage AC	0.56 kV		

Classifications

ETIM 8.0	EC002584	ETIM 9.0	EC002584
ETIM 10.0	EC002584	ECLASS 14.0	27-33-02-92
ECLASS 15.0	27-33-02-92		

FAD BLK4 2XSL20

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

Drawings

www.weidmueller.com

