


**APGTB 1.5 PE 3C/1****Weidmüller Interface GmbH & Co. KG**Klingenbergstraße 26  
D-32758 Detmold  
Germany

www.weidmueller.com

**Product image**

Some applications demand for a pluggable, modular solution to be more flexible or to facilitate the installation. Where complete functional units have to be prefabricated or replaced, modular and flexible connection systems are required. Our pluggable terminal blocks can be quickly assembled and are completely factory tested.

**General ordering data**

|            |   |
|------------|---|
| Version    | Plug-in modular terminals, PUSH IN, 1.5 mm <sup>2</sup> , 500 V, Green/yellow |
| Order No.  | <a href="#">2482230000</a>  |
| Type       | APGTB 1.5 PE 3C/1   |
| GTIN (EAN) | 4050118493955   |
| Qty.       | 50 items  |

## APGTB 1.5 PE 3C/1

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technical data

### Approvals

Approvals



|                         |                            |
|-------------------------|----------------------------|
| ROHS                    | Conform                    |
| UL File Number Search   | <a href="#">UL Website</a> |
| Certificate No. (cURus) | E60693                     |

### Dimensions and weights

|                          |             |                |             |
|--------------------------|-------------|----------------|-------------|
| Depth                    | 33.5 mm     | Depth (inches) | 1.3189 inch |
| Depth including DIN rail | 34.5 mm     | Height         | 62 mm       |
| Height (inches)          | 2.4409 inch | Width          | 3.5 mm      |
| Width (inches)           | 0.1378 inch | Net weight     | 7.33 g      |

### Temperatures

|                                  |                |                                  |               |
|----------------------------------|----------------|----------------------------------|---------------|
| Storage temperature              | -25 °C...55 °C | Ambient temperature              | -5 °C...40 °C |
| Continuous operating temp., min. | -60 °C         | Continuous operating temp., max. | 130 °C        |

### Environmental Product Compliance

|                        |                             |
|------------------------|-----------------------------|
| RoHS Compliance Status | Compliant without exemption |
| REACH SVHC             | No SVHC above 0.1 wt%       |

### Material data

|                                |        |                           |              |
|--------------------------------|--------|---------------------------|--------------|
| Basic material                 | Wemid  | Colour                    | Green/yellow |
| Colour of operational elements | orange | UL 94 flammability rating | V-0          |

### Rating data IECEx/ATEX

|                                |                     |                                 |                     |
|--------------------------------|---------------------|---------------------------------|---------------------|
| Certificate No. (ATEX)         | TUEV16ATEX7940U     | Certificate No. (IECEX)         | IECEXTUR16.0046U    |
| Wire cross section max. (ATEX) | 1.5 mm <sup>2</sup> | Wire cross section max. (IECEX) | 1.5 mm <sup>2</sup> |
| Marking EN 60079-7             | Ex ec II C Gc       | Ex 2014/34/EU label             | II 3 G D            |

### System specifications

|                               |     |                                     |       |
|-------------------------------|-----|-------------------------------------|-------|
| End cover plate required      | Yes | Number of potentials                | 1     |
| Number of levels              | 1   | Number of clamping points per level | 3     |
| Number of potentials per tier | 1   | Levels cross-connected internally   | No    |
| PE connection                 | Yes | Mounting rail                       | TS 35 |
| N-function                    | No  | PE function                         | Yes   |
| PEN function                  | No  |                                     |       |

### Additional technical data

|                   |    |                |         |
|-------------------|----|----------------|---------|
| With snap-in pegs | No | Open sides     | right   |
| Snap-on           | No | Type of fixing | Snap-on |

## APGTB 1.5 PE 3C/1

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technical data

|                     |       |                          |     |
|---------------------|-------|--------------------------|-----|
| Installation advice | Rail  | Explosion-tested version | Yes |
| Type of mounting    | TS 35 |                          |     |

### CSA rating data

|                               |                 |                               |        |
|-------------------------------|-----------------|-------------------------------|--------|
| Wire cross section max. (CSA) | 14 AWG          | Voltage size C (CSA)          | 300 V  |
| Certificate No. (CSA)         | 200039-70089609 | Voltage size B (CSA)          | 300 V  |
| Voltage size D (CSA)          | 600 V           | Wire cross section min. (CSA) | 26 AWG |

### Conductors for clamping (additional connection)

Connection type, additional connection pluggable

### Conductors for clamping (rated connection)

|   |                      |   |                     |
|---|----------------------|---|---------------------|
| Gauge to IEC 60947-1  | A1                   | Wire connection cross section AWG, max.   | AWG 14              |
| Connection direction  | top                  | Stripping length  | 8 mm                |
| Type of connection 2  | Plug-in connection   | Type of connection  | PUSH IN             |
| Number of connections   | 3                    | Clamping range, max.  | 1.5 mm <sup>2</sup> |
| Clamping range, min.  | 0.14 mm <sup>2</sup> | Blade size  | 0.4 x 2.0 mm        |
| Wire connection cross section AWG, min.   | AWG 26               | Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/4, max. | 1 mm <sup>2</sup>   |
| Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/4, min. | 0.14 mm <sup>2</sup> | Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/1, max. | 1.5 mm <sup>2</sup> |
| Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/1, min. | 0.14 mm <sup>2</sup> | Wire connection cross section, finely stranded, max.                                    | 1.5 mm <sup>2</sup> |
| Wire connection cross section, finely stranded, min.                                    | 0.14 mm <sup>2</sup> | Connection cross-section, stranded, max.  | 1.5 mm <sup>2</sup> |
| Connection cross-section, stranded, min.  | 0.14 mm <sup>2</sup> | Wire connection cross-section, solid core, max.   | 1.5 mm <sup>2</sup> |
| Wire connection cross-section, solid core, min.   | 0.14 mm <sup>2</sup> |   |                     |

### General

|   |        |                     |       |
|---|--------|---------------------|-------|
| Wire connection cross section AWG, max. | AWG 14 | Installation advice | Rail  |
| Wire connection cross section AWG, min. | AWG 26 | Mounting rail       | TS 35 |

### Rating data

|  |                     |                                 |       |
|--|---------------------|---------------------------------|-------|
| Rated cross-section                          | 1.5 mm <sup>2</sup> | Rated voltage                   | 500 V |
| Rated voltage to adjoining terminal          | 500 V               | Rated DC voltage                | 500 V |
| Volume resistance according to IEC 60947-7-x | 1.83 mΩ             | Rated impulse withstand voltage | 6 kV  |
| Power loss in accordance with IEC 60947-7-x  | 0.56 W              | Surge voltage category          | III   |
| Pollution severity                           | 3                   |                                 |       |

### UL rating data

|  |        |                         |        |
|--|--------|-------------------------|--------|
| Conductor size Factory wiring max. (cURus) | 14 AWG | Voltage size B (cURus)  | 300 V  |
| Voltage size D (cURus)                     | 600 V  | Certificate No. (cURus) | E60693 |

## APGTB 1.5 PE 3C/1

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Technical data

|   |   |
|---|---|
| Conductor size Field wiring min. (cURus) 26 AWG | Conductor size Factory wiring min. (cURus) 26 AWG |
| Voltage size C (cURus) 300 V                    | Conductor size Field wiring max. (cURus) 14 AWG   |

### Classifications

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 8.0    | EC000897    | ETIM 9.0    | EC000897    |
| ETIM 10.0   | EC000897    | ECLASS 14.0 | 27-25-01-17 |
| ECLASS 15.0 | 27-25-01-17 |             |             |

**Drawings**



## APGTB 1.5 PE 3C/1

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Accessories

### Plugs




The plugs for our WeiCoS-System are available for all different connection systems. The product range includes preassembled connectors from 1 to 10 poles and the possibility of an individual assembly. This ensures maximum flexibility for every application. The customized accessories increase the safety and protection against environmental influences.

### General ordering data

|            |                            |  |
|------------|----------------------------|--|
| Type       | APG 1.5 L GN               | Version  |
| Order No.  | <a href="#">2482270000</a> | Plug, 1.5 mm <sup>2</sup> , 500 V, 17.5 A, Number of poles: 1, green |
| GTIN (EAN) | 4050118494303              |  |
| Qty.       | 50 ST                      |  |
| Type       | APG 1.5 MI GN              | Version  |
| Order No.  | <a href="#">2482300000</a> | Plug, 1.5 mm <sup>2</sup> , 500 V, 17.5 A, Number of poles: 1, green |
| GTIN (EAN) | 4050118494365              |  |
| Qty.       | 50 ST                      |  |
| Type       | APG 1.5 R GN               | Version  |
| Order No.  | <a href="#">2482330000</a> | Plug, 1.5 mm <sup>2</sup> , 500 V, 17.5 A, Number of poles: 1, green |
| GTIN (EAN) | 4050118494396              |  |
| Qty.       | 50 ST                      |  |

### End bracket



Weidmüller's range of products includes end brackets that guarantee a permanent, reliable mounting on the terminal rail and prevent sliding. Versions with and without screws are available. The end brackets include marking options, also for group markers, and also a test plug holder.

### General ordering data

|            |                            |                       |
|------------|----------------------------|-----------------------|
| Type       | AEB 35 SC/1                | Version               |
| Order No.  | <a href="#">1991920000</a> | A-series, End bracket |
| GTIN (EAN) | 4050118376722              |                       |
| Qty.       | 50 ST                      |                       |
| Type       | AEB 35 SC/1 BK             | Version               |
| Order No.  | <a href="#">2475310000</a> | A-series, End bracket |
| GTIN (EAN) | 4050118487114              |                       |
| Qty.       | 50 ST                      |                       |

## APGTB 1.5 PE 3C/1

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

## Accessories

www.weidmueller.com

## End plates and partition plates




Partition plates and end plates are essential accessories for terminal blocks. Partition plates provide optical and electrical separation of different potentials and functional groups, increasing safety and ensuring a clear structure inside the control cabinet. End plates close the terminal block row on the sides, protect against contact with live parts, and ensure a clean, stable finish. Both components are precisely matched to the respective Weidmüller terminal block series, contributing to safe, compliant, and professional wiring.

## General ordering data

|            |                            |                     |
|------------|----------------------------|---------------------|
| Type       | AEP 2C 1.5                 | Version             |
| Order No.  | <a href="#">1552600000</a> | A-series, End plate |
| GTIN (EAN) | 4050118359602              |                     |
| Qty.       | 50 ST                      |                     |
| Type       | AEP 2C 1.5 BL              | Version             |
| Order No.  | <a href="#">1552610000</a> | A-series, End plate |
| GTIN (EAN) | 4050118359701              |                     |
| Qty.       | 50 ST                      |                     |
| Type       | AEP 2C 1.5 OR              | Version             |
| Order No.  | <a href="#">2052350000</a> | A-series, End plate |
| GTIN (EAN) | 4050118411980              |                     |
| Qty.       | 50 ST                      |                     |

## Cross-connections



The distribution or multiplication of a potential to adjoining terminal blocks is realized via a cross-connection. Additional wiring effort can be easily avoided. Even if the poles are broken out, contact reliability in the terminal blocks is still ensured. Our portfolio offers pluggable and screwable cross-connection systems for modular terminal blocks.

## General ordering data

|            |                            |   |
|------------|----------------------------|---|
| Type       | ZQV 1.5N/10                | Version   |
| Order No.  | <a href="#">1985580000</a> | Cross-connector (terminal), Plugged, orange, 17.5 A, Number of poles: 10, Pitch in mm (P): 3.50, Insulated: Yes, Width: 33.5 mm |
| GTIN (EAN) | 4050118370416              |   |
| Qty.       | 20 ST                      |   |
| Type       | ZQV 1.5N/10 BL             | Version   |
| Order No.  | <a href="#">1985680000</a> | Cross-connector (terminal), Plugged, blue, 17.5 A, Number of poles: 10, Pitch in mm (P): 3.50, Insulated: Yes, Width: 33.5 mm   |
| GTIN (EAN) | 4050118370539              |   |
| Qty.       | 20 ST                      |   |
| Type       | ZQV 1.5N/10 RD             | Version   |
| Order No.  | <a href="#">1985800000</a> | Cross-connector (terminal), Plugged, red, 17.5 A, Number of poles: 10, Pitch in mm (P): 3.50, Insulated: Yes, Width: 33.5 mm    |
| GTIN (EAN) | 4050118370393              |   |
| Qty.       | 20 ST                      |   |

## APGTB 1.5 PE 3C/1

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Accessories

|            |                            |  |
|------------|----------------------------|--|
| Type       | ZQV 1.5N/2                 | Version  |
| Order No.  | <a href="#">1985410000</a> | Cross-connector (terminal), Plugged, orange, 17.5 A, Number of         |
| GTIN (EAN) | 4050118369861              | poles: 2, Pitch in mm (P): 3.50, Insulated: Yes, Width: 5.5 mm         |
| Qty.       | 60 ST                      |  |
| Type       | ZQV 1.5N/2 BL              | Version  |
| Order No.  | <a href="#">1985530000</a> | Cross-connector (terminal), Plugged, blue, 17.5 A, Number of poles: 2, |
| GTIN (EAN) | 4050118370423              | Pitch in mm (P): 3.50, Insulated: Yes, Width: 5.5 mm                   |
| Qty.       | 60 ST                      |  |
| Type       | ZQV 1.5N/2 RD              | Version  |
| Order No.  | <a href="#">1985650000</a> | Cross-connector (terminal), Plugged, red, 17.5 A, Number of poles: 2,  |
| GTIN (EAN) | 4050118370324              | Pitch in mm (P): 3.50, Insulated: Yes, Width: 5.5 mm                   |
| Qty.       | 60 ST                      |  |
| Type       | ZQV 1.5N/20                | Version  |
| Order No.  | <a href="#">1985600000</a> | Cross-connector (terminal), Plugged, orange, 17.5 A, Number of         |
| GTIN (EAN) | 4050118370225              | poles: 20, Pitch in mm (P): 3.50, Insulated: Yes, Width: 70 mm         |
| Qty.       | 20 ST                      |  |
| Type       | ZQV 1.5N/20 BL             | Version  |
| Order No.  | <a href="#">1985700000</a> | Cross-connector (terminal), Plugged, blue, 17.5 A, Number of poles:    |
| GTIN (EAN) | 4050118370331              | 20, Pitch in mm (P): 3.50, Insulated: Yes, Width: 70 mm                |
| Qty.       | 20 ST                      |  |
| Type       | ZQV 1.5N/20 RD             | Version  |
| Order No.  | <a href="#">1985810000</a> | Cross-connector (terminal), Plugged, red, 17.5 A, Number of poles:     |
| GTIN (EAN) | 4050118370355              | 20, Pitch in mm (P): 3.50, Insulated: Yes, Width: 70 mm                |
| Qty.       | 20 ST                      |  |
| Type       | ZQV 1.5N/3                 | Version  |
| Order No.  | <a href="#">1985480000</a> | Cross-connector (terminal), Plugged, orange, 17.5 A, Number of         |
| GTIN (EAN) | 4050118370096              | poles: 3, Pitch in mm (P): 3.50, Insulated: Yes, Width: 9 mm           |
| Qty.       | 60 ST                      |  |
| Type       | ZQV 1.5N/3 BL              | Version  |
| Order No.  | <a href="#">1985550000</a> | Cross-connector (terminal), Plugged, blue, 17.5 A, Number of poles: 3, |
| GTIN (EAN) | 4050118370485              | Pitch in mm (P): 3.50, Insulated: Yes, Width: 9 mm                     |
| Qty.       | 60 ST                      |  |
| Type       | ZQV 1.5N/3 RD              | Version  |
| Order No.  | <a href="#">1985670000</a> | Cross-connector (terminal), Plugged, red, 17.5 A, Number of poles: 3,  |
| GTIN (EAN) | 4050118370348              | Pitch in mm (P): 3.50, Insulated: Yes, Width: 9 mm                     |
| Qty.       | 60 ST                      |  |
| Type       | ZQV 1.5N/4                 | Version  |
| Order No.  | <a href="#">1985490000</a> | Cross-connector (terminal), Plugged, orange, 17.5 A, Number of         |
| GTIN (EAN) | 4050118370201              | poles: 4, Pitch in mm (P): 3.50, Insulated: Yes, Width: 12.5 mm        |
| Qty.       | 60 ST                      |  |
| Type       | ZQV 1.5N/4 BL              | Version  |
| Order No.  | <a href="#">1985570000</a> | Cross-connector (terminal), Plugged, blue, 17.5 A, Number of poles: 4, |
| GTIN (EAN) | 4050118370317              | Pitch in mm (P): 3.50, Insulated: Yes, Width: 12.5 mm                  |
| Qty.       | 60 ST                      |  |
| Type       | ZQV 1.5N/4 RD              | Version  |
| Order No.  | <a href="#">1985690000</a> | Cross-connector (terminal), Plugged, red, 17.5 A, Number of poles: 4,  |
| GTIN (EAN) | 4050118370515              | Pitch in mm (P): 3.50, Insulated: Yes, Width: 12.5 mm                  |
| Qty.       | 60 ST                      |  |
| Type       | ZQV 1.5N/5                 | Version  |
| Order No.  | <a href="#">1985500000</a> | Cross-connector (terminal), Plugged, orange, 17.5 A, Number of         |
| GTIN (EAN) | 4050118369991              | poles: 5, Pitch in mm (P): 3.50, Insulated: Yes, Width: 16 mm          |
| Qty.       | 20 ST                      |  |

## APGTB 1.5 PE 3C/1

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Accessories

|            |                            |  |
|------------|----------------------------|--|
| Type       | ZQV 1.5N/5 BL              | Version  |
| Order No.  | <a href="#">1985590000</a> | Cross-connector (terminal), Plugged, blue, 17.5 A, Number of poles: 5, |
| GTIN (EAN) | 4050118370430              | Pitch in mm (P): 3.50, Insulated: Yes, Width: 16 mm                    |
| Qty.       | 20 ST                      |  |
| Type       | ZQV 1.5N/5 RD              | Version  |
| Order No.  | <a href="#">1985710000</a> | Cross-connector (terminal), Plugged, red, 17.5 A, Number of poles: 5,  |
| GTIN (EAN) | 4050118370256              | Pitch in mm (P): 3.50, Insulated: Yes, Width: 16 mm                    |
| Qty.       | 20 ST                      |  |
| Type       | ZQV 1.5N/50                | Version  |
| Order No.  | <a href="#">1985620000</a> | Cross-connector (terminal), Plugged, orange, 17.5 A, Number of         |
| GTIN (EAN) | 4050118370300              | poles: 50, Pitch in mm (P): 3.50, Insulated: Yes, Width: 175 mm        |
| Qty.       | 5 ST                       |  |
| Type       | ZQV 1.5N/50 BL             | Version  |
| Order No.  | <a href="#">1985720000</a> | Cross-connector (terminal), Plugged, blue, 17.5 A, Number of poles:    |
| GTIN (EAN) | 4050118370546              | 50, Pitch in mm (P): 3.50, Insulated: Yes, Width: 175 mm               |
| Qty.       | 5 ST                       |  |
| Type       | ZQV 1.5N/50 RD             | Version  |
| Order No.  | <a href="#">1985820000</a> | Cross-connector (terminal), Plugged, red, 17.5 A, Number of poles:     |
| GTIN (EAN) | 4050118370270              | 50, Pitch in mm (P): 3.50, Insulated: Yes, Width: 175 mm               |
| Qty.       | 5 ST                       |  |
| Type       | ZQV 1.5N/6                 | Version  |
| Order No.  | <a href="#">1985510000</a> | Cross-connector (terminal), Plugged, orange, 17.5 A, Number of         |
| GTIN (EAN) | 4050118370188              | poles: 6, Pitch in mm (P): 3.50, Insulated: Yes, Width: 19.5 mm        |
| Qty.       | 20 ST                      |  |
| Type       | ZQV 1.5N/6 BL              | Version  |
| Order No.  | <a href="#">1985610000</a> | Cross-connector (terminal), Plugged, blue, 17.5 A, Number of poles: 6, |
| GTIN (EAN) | 4050118370492              | Pitch in mm (P): 3.50, Insulated: Yes, Width: 19.5 mm                  |
| Qty.       | 20 ST                      |  |
| Type       | ZQV 1.5N/6 RD              | Version  |
| Order No.  | <a href="#">1985730000</a> | Cross-connector (terminal), Plugged, red, 17.5 A, Number of poles: 6,  |
| GTIN (EAN) | 4050118370454              | Pitch in mm (P): 3.50, Insulated: Yes, Width: 19.5 mm                  |
| Qty.       | 20 ST                      |  |
| Type       | ZQV 1.5N/7                 | Version  |
| Order No.  | <a href="#">1985520000</a> | Cross-connector (terminal), Plugged, orange, 17.5 A, Number of         |
| GTIN (EAN) | 4050118370195              | poles: 7, Pitch in mm (P): 3.50, Insulated: Yes, Width: 23 mm          |
| Qty.       | 20 ST                      |  |
| Type       | ZQV 1.5N/7 BL              | Version  |
| Order No.  | <a href="#">1985630000</a> | Cross-connector (terminal), Plugged, blue, 17.5 A, Number of poles: 7, |
| GTIN (EAN) | 4050118370522              | Pitch in mm (P): 3.50, Insulated: Yes, Width: 23 mm                    |
| Qty.       | 20 ST                      |  |
| Type       | ZQV 1.5N/7 RD              | Version  |
| Order No.  | <a href="#">1985750000</a> | Cross-connector (terminal), Plugged, red, 17.5 A, Number of poles: 7,  |
| GTIN (EAN) | 4050118370249              | Pitch in mm (P): 3.50, Insulated: Yes, Width: 23 mm                    |
| Qty.       | 20 ST                      |  |
| Type       | ZQV 1.5N/8                 | Version  |
| Order No.  | <a href="#">1985540000</a> | Cross-connector (terminal), Plugged, orange, 17.5 A, Number of         |
| GTIN (EAN) | 4050118370218              | poles: 8, Pitch in mm (P): 3.50, Insulated: Yes, Width: 26.5 mm        |
| Qty.       | 20 ST                      |  |
| Type       | ZQV 1.5N/8 BL              | Version  |
| Order No.  | <a href="#">1985640000</a> | Cross-connector (terminal), Plugged, blue, 17.5 A, Number of poles: 8, |
| GTIN (EAN) | 4050118370461              | Pitch in mm (P): 3.50, Insulated: Yes, Width: 26.5 mm                  |
| Qty.       | 20 ST                      |  |

## APGTB 1.5 PE 3C/1

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Accessories

|            |                            |  |
|------------|----------------------------|--|
| Type       | ZQV 1.5N/8 RD              | Version  |
| Order No.  | <a href="#">1985770000</a> | Cross-connector (terminal), Plugged, red, 17.5 A, Number of poles: 8,  |
| GTIN (EAN) | 4050118370508              | Pitch in mm (P): 3.50, Insulated: Yes, Width: 26.5 mm                  |
| Qty.       | 20 ST                      |  |
| Type       | ZQV 1.5N/9                 | Version  |
| Order No.  | <a href="#">1985560000</a> | Cross-connector (terminal), Plugged, orange, 17.5 A, Number of         |
| GTIN (EAN) | 4050118370409              | poles: 9, Pitch in mm (P): 3.50, Insulated: Yes, Width: 30 mm          |
| Qty.       | 20 ST                      |  |
| Type       | ZQV 1.5N/9 BL              | Version  |
| Order No.  | <a href="#">1985660000</a> | Cross-connector (terminal), Plugged, blue, 17.5 A, Number of poles: 9, |
| GTIN (EAN) | 4050118370478              | Pitch in mm (P): 3.50, Insulated: Yes, Width: 30 mm                    |
| Qty.       | 20 ST                      |  |
| Type       | ZQV 1.5N/9 RD              | Version  |
| Order No.  | <a href="#">1985790000</a> | Cross-connector (terminal), Plugged, red, 17.5 A, Number of poles: 9,  |
| GTIN (EAN) | 4050118370386              | Pitch in mm (P): 3.50, Insulated: Yes, Width: 30 mm                    |
| Qty.       | 20 ST                      |  |

## Plugs



The plugs for our WeiCoS-System are available for all different connection systems. The product range includes preassembled connectors from 1 to 10 poles and the possibility of an individual assembly. This ensures maximum flexibility for every application. The customized accessories increase the safety and protection against environmental influences.

## General ordering data

|            |                            |   |
|------------|----------------------------|---|
| Type       | APGCE                      | Version   |
| Order No.  | <a href="#">1514490000</a> | Coding element (terminal), Wemid, orange, Width: 3.3 mm |
| GTIN (EAN) | 4050118321906              |   |
| Qty.       | 50 ST                      |   |
| Type       | APGSR 1.5                  | Version   |
| Order No.  | <a href="#">2482730000</a> | Strain relief (terminal), Wemid, orange                 |
| GTIN (EAN) | 4050118493993              |   |
| Qty.       | 25 ST                      |   |
| Type       | APGSR 1.5 - 4P             | Version   |
| Order No.  | <a href="#">2482740000</a> | Strain relief (terminal), Wemid, orange                 |
| GTIN (EAN) | 4050118494204              |   |
| Qty.       | 25 ST                      |   |
| Type       | APGSR 1.5 - 8P             | Version   |
| Order No.  | <a href="#">2482750000</a> | Strain relief (terminal), Wemid, orange                 |
| GTIN (EAN) | 4050118494211              |   |
| Qty.       | 25 ST                      |   |
| Type       | APGLE 1.5                  | Version   |
| Order No.  | <a href="#">2482720000</a> | Locking clips (terminal), Wemid, orange                 |
| GTIN (EAN) | 4050118496253              |   |
| Qty.       | 25 ST                      |   |

## APGTB 1.5 PE 3C/1

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Accessories

|            |                            |  |
|------------|----------------------------|--|
| Type       | APGPC 1.5                  | Version  |
| Order No.  | <a href="#">2482530000</a> | Terminal cover, orange, Wemid, Height: 16 mm, Width: 3.3 mm, |
| GTIN (EAN) | 4050118494563              | Depth: 13 mm, V-0  |
| Qty.       | 50 ST                      |  |

### End plates and partition plates




Partition plates and end plates are essential accessories for terminal blocks. Partition plates provide optical and electrical separation of different potentials and functional groups, increasing safety and ensuring a clear structure inside the control cabinet. End plates close the terminal block row on the sides, protect against contact with live parts, and ensure a clean, stable finish. Both components are precisely matched to the respective Weidmüller terminal block series, contributing to safe, compliant, and professional wiring.

#### General ordering data

|            |                            |                           |
|------------|----------------------------|---------------------------|
| Type       | APP 2                      | Version                   |
| Order No.  | <a href="#">2489090000</a> | A-series, Partition plate |
| GTIN (EAN) | 4050118499308              |                           |
| Qty.       | 50 ST                      |                           |

### End bracket



Weidmüller's range of products includes end brackets that guarantee a permanent, reliable mounting on the terminal rail and prevent sliding. Versions with and without screws are available. The end brackets include marking options, also for group markers, and also a test plug holder.

#### General ordering data

|            |                            |                       |
|------------|----------------------------|-----------------------|
| Type       | AEB 35 SCL/1 V0            | Version               |
| Order No.  | <a href="#">2661280000</a> | A-series, End bracket |
| GTIN (EAN) | 4050118702163              |                       |
| Qty.       | 20 ST                      |                       |
| Type       | AEB 35 SCL/1 V0 BK         | Version               |
| Order No.  | <a href="#">2661300000</a> | A-series, End bracket |
| GTIN (EAN) | 4050118702187              |                       |
| Qty.       | 20 ST                      |                       |
| Type       | AEB 35 SCL/1 V0 GY         | Version               |
| Order No.  | <a href="#">2661290000</a> | A-series, End bracket |
| GTIN (EAN) | 4050118702170              |                       |
| Qty.       | 20 ST                      |                       |

## APGTB 1.5 PE 3C/1

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Accessories

### Slotted screwdriver



Slotted screwdriver with rounded blade SD DIN 5265, ISO 2380/2, output to DIN 5264, ISO 2380/1. ChromTop tip, SoftFinish grip

#### General ordering data

|            |                            |  |  |
|------------|----------------------------|--|--|
| Type       | SDS 0.4X2.0X60             | Version  |  |
| Order No.  | <a href="#">2749260000</a> | Screwdriver, Blade width (B): 2 mm, Blade length: 60 mm, Blade thickness (A): 0.4 mm |  |
| GTIN (EAN) | 4050118895537              |  |  |
| Qty.       | 1 ST                       |  |  |

### Testadapter and testsockets



Test adapters and test plugs are used for the electrical connection between terminal blocks and the test equipment. In this way, an electrical contact can be established in the wired state and measurements can be done easily.

#### General ordering data

|            |                            |  |  |
|------------|----------------------------|--|--|
| Type       | FZS 2/4 RT/80 SAKT4        | Version  |  |
| Order No.  | <a href="#">1276300000</a> | Plug (terminal), Plug-in connection, 2 mm <sup>2</sup> , Number of connections: 2, Number of poles: 1, Width: 9 mm |  |
| GTIN (EAN) | 4008190026080              |  |  |
| Qty.       | 20 ST                      |  |  |