

SM 27/18-22 MM SW VPE100**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



Prevention of incorrect operation: SM

MultiMark device markers can be used with marking materials from different manufacturers. Wherever they are used, they ensure that all components, such as control and signalling devices from different vendors, are clearly assigned.

Your benefits with MultiMark

- “Different materials for various requirements”
- Can be used with equipment from many manufacturers
- Device markers with a familiar design

General ordering data

Version	SwitchMark, Device markers, 47.75 x 27 mm, black
Order No.	2496950000
Type	SM 27/18-22 MM SW VPE100
GTIN (EAN)	4050118508451
Qty.	100 items

SM 27/18-22 MM SW VPE100

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

ROHS	Conform
------	---------

Dimensions and weights

Depth	0.1 mm	Depth (inches)	0.0039 inch
Height	47.75 mm	Height (inches)	1.8799 inch
Width	27 mm	Width (inches)	1.063 inch
Diameter	22 mm	Net weight	0.1 g

Temperatures

Operating temperature range	-40...120 °C
-----------------------------	--------------

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

General data

Adhesive	Acrylate adhesive	Version	halogen-free, Self-adhesive
Width	27 mm	UL 94 flammability rating	V-0
Operating temperature range, max.	120 °C	Operating temperature range, min.	-40 °C
Colour	black	Halogen	No
Basic material	Polyester	Printed characters	without
Size of labelling field	18 x 27 mm	Approval acc. to UL 969	Yes
compatible printer	THM MULTIMARK , THM MULTIMARK PLUS	Operating temperature range	-40...120 °C

Device markers

Diameter	22 mm	Halogen	No
----------	-------	---------	----

Classifications

ETIM 8.0	EC001288	ETIM 9.0	EC001288
ETIM 10.0	EC001288	ECLASS 14.0	27-28-11-04
ECLASS 15.0	27-28-11-04		

Drawings

