

ACT20P-2CI-2CO-12-P

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com



ACT20P: The flexible solution

- Precise and highly functional signal converters
- Release levers simplify handling

General ordering data

| | |
|------------|--|
| Version | Analogue isolating amplifier, Input : 2 x 0(4) - 20 mA, Output : 2 x 4-20 mA, Signal converter/isolator, HART® |
| Order No. | 2489730000 |
| Type | ACT20P-2CI-2CO-12-P |
| GTIN (EAN) | 4050118535174 |
| Qty. | 1 items |

ACT20P-2CI-2CO-12-P

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

| | |
|-----------|---|
| Approvals | CE; CULUS; CULUSEX; DEMKOATEX; IECEXULD; UKEX |
| Approvals | CULUS; |
| Approvals | |



| | |
|---------------------------|----------------------------|
| ROHS | Conform |
| UL File Number Search | UL Website |
| Certificate no. (cULus) | E469563 |
| Certificate no. (cULusEX) | E338066 |

Dimensions and weights

| | | | |
|------------|----------|-----------------|-------------|
| Depth | 113.7 mm | Depth (inches) | 4.4764 inch |
| Height | 127.1 mm | Height (inches) | 5.0039 inch |
| Width | 12.5 mm | Width (inches) | 0.4921 inch |
| Net weight | 130 g | | |

Temperatures

| | | | |
|-----------------------------------|----------------------------|-----------------------|---------------------------|
| Storage temperature | -40 °C...85 °C | Operating temperature | -20 °C...60 °C |
| Humidity at operating temperature | 0...95 % (no condensation) | Humidity | 5...95 %, no condensation |

Probability of failure

| | |
|----------------------------------|------|
| SIL in compliance with IEC 61508 | None |
|----------------------------------|------|

Environmental Product Compliance

| | |
|--------------------------------------|--------------------------------------|
| RoHS Compliance Status | Compliant with exemption |
| RoHS Exemption (if applicable/known) | 7a, 7cl |
| REACH SVHC | Lead 7439-92-1 |
| SCIP | 2f6dd957-421a-46db-a0c2-cf1609156924 |

Input

| | | | |
|---------------|---------------------------------------|---------------|----------------------------|
| Sensor | 4-wire sensor (with own power supply) | Number inputs | 2 |
| Input voltage | ≤ 28 V DC | Input signal | HART signal® bidirectional |
| Input current | 0...20 mA, 4...20mA | Voltage drop | ≤ 1 V |

Output

| | | | |
|-------------------|---|------------------------|--|
| Number of outputs | 2 | Load impedance current | <300 Ω, per channel |
| Type | active, connected control must be passive | Output current | 0...20 mA (if input: 0...20 mA), 4...20 mA (if input: 4...20 mA), HART® digital signal |

General data

| | | | |
|----------------|---------------------|--------------------|----------|
| Accuracy | <0.1 % of end value | Protection degree | IP20 |
| Supply voltage | 20...30 V DC | Step response time | ≤ 0,5 ms |

ACT20P-2CI-2CO-12-P

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

| | | | |
|---------------------------|---|--|-----------|
| Current consumption | ≤100 mA (24V power supply, 20mA output) | Mounting rail | TS 35 |
| Temperature coefficient | 80 ppm/K | Type of signal forwarding according to HART® | unchanged |
| Nominal power consumption | 2 VA | Configuration | none |
| Operating altitude | ≤ 2000 m | | |

Insulation coordination

| | | | |
|---------------------------|--------------------------------------|------------------------|---|
| Impulse withstand voltage | 4 kV (1.2/50 µs) | EMC standards | EN 61326-1, EN 61000-6-4, EN 61000-6-2 |
| Test voltage | 0.3 kV | Surge voltage category | III |
| Pollution severity | 2 | Galvanic isolation | 3-way isolator, between input/output/supply |
| Insulation voltage | 2 kV inputs / outputs / power supply | | |

Data for Ex applications (ATEX)

| | | | |
|---------|------------------------|-----------------------|-----------------|
| Marking | II 3 G Ex ec IIC T5 Gc | IECEx - gas labelling | Ex ec IIC T5 Gc |
|---------|------------------------|-----------------------|-----------------|

Connection data

| | | | |
|---|---------------------|---|---------------------|
| Type of connection | PUSH IN | Tightening torque, min. | 0.4 Nm |
| Tightening torque, max. | 0.6 Nm | Clamping range, rated connection | 2.5 mm ² |
| Clamping range, min. | 0.5 mm ² | Clamping range, max. | 2.5 mm ² |
| Wire connection cross section AWG, min. | AWG 26 | Wire connection cross section AWG, max. | AWG 14 |
| Wire cross-section, solid, min. | 0.2 mm ² | Wire cross-section, solid, max. | 2.5 mm ² |
| Wire connection cross section, finely stranded, min. | 0.5 mm ² | Wire connection cross section, finely stranded, max. | 2.5 mm ² |
| Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/4, min. | 0.5 mm ² | Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/4, max. | 2.5 mm ² |


Part description

| | |
|---------------------|--|
| Product description | <p>The dual-channel, non-adjustable DC isolating amplifier ACT20P-2CI-2CO isolates analogue standard current source signals. An analogue input current signal is linearly converted into an analogue output current signal and is galvanically isolated. The power supply is galvanically isolated from the input and output (5-way isolation).</p> <p>Properties</p> <ul style="list-style-type: none"> • HART-compatible for 0.5 - 2.5 kHz • Operating status display on a front panel LED • Galvanic 5-way isolation between input, output and supply. |
|---------------------|--|


Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 8.0 | EC002653 | ETIM 9.0 | EC002653 |
| ETIM 10.0 | EC002653 | ECLASS 14.0 | 27-21-01-20 |
| ECLASS 15.0 | 27-21-01-20 | | |

Connection diagram




Dimensioned drawing



Similar to illustration



PUSH IN technology




ACT20P-2CI-2CO-12-P

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Accessories

Blank



ESG is the tried-and-tested marker in MultiCard format for use on many well-known electrical devices. The result is high-quality device marking with a high-contrast appearance.

Various types are available for devices from manufacturers like Siemens, ABB, Beckhoff etc.

Advantages at a glance:

- Tags for universal usage, self-adhesive or clip-on tags, depending on type
- For aligned equipment, e.g. circuit breakers, we supply ESG markers for clipping onto tag rails
- Individual laser-quality printing according to specifications

For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

General ordering data

| | | | |
|------------|----------------------------|--|--|
| Type | ESG 8/13.5/43.3 SAI AU | Version | |
| Order No. | 1912130000 | ESG, Device markers x 13.5 mm, PA 66, Colour: Transparent, pluggable | |
| GTIN (EAN) | 4032248541164 | | |
| Qty. | 5 ST | | |
| Type | ESG 6.6/11 BHZ 5.00/02 | Version | |
| Order No. | 1082490000 | ESG, Device markers x 11 mm, PA 66, Colour: white, pluggable | |
| GTIN (EAN) | 4032248845330 | | |
| Qty. | 200 ST | | |