Data sheet

SAIL-M12GM12G-TS-12U

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Product image



Your peripheral devices should be supplied with greater power. With our new M12 plug-in connector, more than 250 V and 2 A is possible without problems. The compact A-, K-, L-, S- and T-coded M12 plug-in connectors are designed for the transmission of up to 630 V AC or 60 V DC and 12 A.

General ordering data

Version	Sensor/actuator line, M12 / M12, Number of poles : 4, 12 m, Male pin, straight - Female socket, straight, Shielded: Yes, LED: No, Sheath material: PUR, Halogen: No
Order No.	2490241200
Type	SAIL-M12GM12G-TS-12U
GTIN (EAN)	4050118690873
Qty.	1 items

Data sheet

SAIL-M12GM12G-TS-12U

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Approvals

Approvals	
ROHS	Conform

Dimensions and weights

Net weight	1000 g

Environmental Product Compliance

RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	6c
REACH SVHC	Lead 7439-92-1
SCIP	e8d8af70-4c85-4483-bc8c-9bc5b598e2a9

Technical specifications for cable

Cable length	12 m	Sheathing colour	black
Resistance to oils	in accordance with IEC 60811:404	Suitable for cable carriers	Yes
Core cross-section	1.5 mm²	Number of wires	4
Shielded	Yes	Halogen	No
Insulation	PP	Acceleration	50 m/s²
Bending radius, min., moving	7.5 x cable diameter	Bending radius, min., stationary	4 x cable diameter
Bending cycles	10 Mio	Resistance to spread of flame	in accordance with IEC 60332-1-2
Speed	5 m/s	Sheath material	PUR
Cable length configurable	No	Outer cladding in accordance with UL AWM style	20939 (80 °C / 600 V)
Type is hybrid cable	No	Irradiation crosslinked	No
Colour coding	brown, white, blue, black	Temperature range, stationary	-40...80 °C
Resistant to welding beads	No	Temperature range, moving	-30...80 °C
Number of poles	4		

General technical data

Coding	T-coded	Connection thread	M12 / M12
Contact surface	Gold-plated	LED	No
Version	Male pin, straight - Female socket, straight	Housing main material	PUR
Insulation resistance	109 Ω	Contact material	Copper alloy
Nominal voltage	60 V	Nominal current	12 A
Protection degree	IP65, IP67, when screwed in	Plugging cycles	100
Pollution severity	3	Threaded ring material	Nickel-plated CuZn
Temperature range of housing	-40 ... +85 ° C	Tightening torque	M12: 0.8 - 1.2 Nm

Electrical properties

Insulation resistance	109 Ω	Nominal voltage	60 V

Data sheet

SAIL-M12GM12G-TS-12U

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

General standards

Connector standard	IEC 61076-2-111

Standards

Connector standard	IEC 61076-2-111

Plug, left

Plug left	M12, T-coded, Number of poles: 4, male contact, straight, plug, shielded

Plug, right

Plug right	M12, T-coded, Number of poles: 4, female contact, straight, plug, shielded

Classifications

ETIM 8.0	EC001855	ETIM 9.0	EC001855
ETIM 10.0	EC001855	ECLASS 14.0	27-06-03-11
ECLASS 15.0	27-06-03-11		


SAIL-M12GM12G-TS-12U

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany


www.weidmueller.com

Drawings


Dimensioned drawing




Dimensioned drawing




Pole scheme



Pole scheme



Wiring diagram



The ideal tool: Screwty ® with torque function

