

**SAIL-M12GM12G-TS-15U****Weidmüller Interface GmbH & Co. KG**Klingenbergstraße 26  
D-32758 Detmold  
Germany

www.weidmueller.com

**Product image**

Your peripheral devices should be supplied with greater power. With our new M12 plug-in connector, more than 250 V and 2 A is possible without problems. The compact A-, K-, L-, S- and T-coded M12 plug-in connectors are designed for the transmission of up to 630 V AC or 60 V DC and 12 A.

**General ordering data**

Version	Sensor/actuator line, M12 / M12, Number of poles : 4, 15 m, Male pin, straight - Female socket, straight, Shielded: Yes, LED: No, Sheath material: PUR, Halogen: No
Order No.	<a href="#">2490241500</a>
Type	SAIL-M12GM12G-TS-15U
GTIN (EAN)	4050118690941
Qty.	1 items

## SAIL-M12GM12G-TS-15U

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technical data

### Approvals

Approvals



ROHS Conform

### Dimensions and weights

Net weight 1000 g

### Environmental Product Compliance

RoHS Compliance Status Compliant with exemption  
 RoHS Exemption (if applicable/known) 6c  
 REACH SVHC Lead 7439-92-1  
 SCIP e8d8af70-4c85-4483-bc8c-9bc5b598e2a9

### Technical specifications for cable

Cable length	15 m	Sheathing colour	black
Suitable for cable carriers	Yes	Core cross-section	1.5 mm <sup>2</sup>
Shielded	Yes	Halogen	No
Insulation	TPE	Acceleration	50 m/s <sup>2</sup>
Bending radius, min., moving	7.5 x cable diameter	Bending radius, min., stationary	4 x cable diameter
Bending cycles	10 Mio	Sheath material	PUR
Configurable cable length	No	Irradiation crosslinked	No
Colour coding	brown, white, blue, black	Temperature range, stationary	-40...80 °C
Resistant to welding beads	Yes	Temperature range, moving	-30...80 °C
Number of poles	4		

### General technical data

Coding	T-coded	Connection thread	M12 / M12
Contact surface	Gold-plated	LED	No
Version	Male pin, straight - Female socket, straight	Housing main material	PUR
Insulation resistance	108 Ω	Nominal voltage	60 V
Nominal current	12 A	Protection degree	IP65, IP67
Plugging cycles	≥ 100	Pollution severity	3
Temperature range of housing	-40 ... +85 °C	Tightening torque	M12: 0.8 - 1.2 Nm

### Electrical properties

Insulation resistance 108 Ω      Nominal voltage 60 V

### General standards

Connector standard IEC 61076-2-111

### Standards

Connector standard IEC 61076-2-111

**SAIL-M12GM12G-TS-15U**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Technical data**

**Classifications**

ETIM 8.0	EC001855	ETIM 9.0	EC001855
ETIM 10.0	EC001855	ECLASS 14.0	27-06-03-11
ECLASS 15.0	27-06-03-11		

**SAIL-M12GM12G-TS-15U**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

**Drawings**

**Dimensioned drawing**




**Dimensioned drawing**



**Pole scheme**



**Pole scheme**



**Wiring diagram**



**The ideal tool: Screwty® with torque function**

