

**HDC XX5E02 MFSXXXX-0700**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Compact**

The new two-pole bus module is extremely compact and can accommodate both megabit and gigabit data inserts. It enables the connection of 2 Gigabit Cat 6A cables (10 gigabit) to one module.

**General ordering data**

|                 |   |
|-----------------|---|
| Order No.       | 2503790700                              |
| Type            | <a href="#">HDC XX5E02 MFSXXXX-0700</a> |
| GTIN (EAN)      | 4050118523317                           |
| Qty.            | 1 items                                 |
| Delivery status | Discontinued                            |
| Available until | 2025-09-30T00:00:00+02:00               |

## HDC XX5E02 MFSXXX-0700

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technical data

## Approvals

|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

## Dimensions and weights

|            |     |
|------------|-----|
| Net weight | 0 g |
|------------|-----|

## Temperatures

|                   |                  |
|-------------------|------------------|
| Limit temperature | -40 °C ... 90 °C |
|-------------------|------------------|

## Environmental Product Compliance

|                                      |                                      |
|--------------------------------------|--------------------------------------|
| RoHS Compliance Status               | Compliant with exemption             |
| RoHS Exemption (if applicable/known) | 6c                                   |
| REACH SVHC                           | Lead 7439-92-1                       |
| SCIP                                 | 2ac5c63f-7f5e-465a-860d-49cfb7bbe5b5 |

## General data

|                       |                  |                       |            |
|-----------------------|------------------|-----------------------|------------|
| Number of poles       | 4                | Cable length          | 7 m        |
| Coding                | D-coded          | Contact surface       | Au (Gold)  |
| Transmission rate     | 100 MBit/s       | Insulation resistance | ≥ 108 Ω    |
| Category              | Cat. 5e          | Nominal voltage       | 250 V      |
| Nominal current       | 4 A              | Plugging cycles       | \u2265 100 |
| Type                  | Pin              | Pollution severity    | 2          |
| Opposite side version | Female, straight | Module side version   | Male       |

## Cable technical specifications

|                  |                             |         |
|------------------|-----------------------------|---------|
| Cable length     | 7 m                         |         |
| Sheathing colour | blue                        |         |
| Shielded         | Yes                         |         |
| Halogen          | Yes, No                     |         |
| Sheath material  | Radox EM 104                |         |
| Colour coding    | white, yellow, blue, orange |         |
| Outside diameter | Diameter                    | 7.25 mm |
|                  | Signs                       | ±       |
|                  | Tolerance                   | 0.3     |
| Outside diameter | 7.25 mm ± 0.3               |         |

## Classifications

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 8.0    | EC002599    | ETIM 9.0    | EC002599    |
| ETIM 10.0   | EC002599    | ECLASS 14.0 | 27-06-03-07 |
| ECLASS 15.0 | 27-06-03-07 |             |             |

Drawings

---

---

| M12 |        | M12 |
|-----|--------|-----|
| 1   | yellow | 1   |
| 2   | white  | 2   |
| 3   | orange | 3   |
| 4   | blue   | 4   |

---

---

---