Data sheet

SAI-4-M-4P-M12-SVV-A03

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



SAI 4-way power distributor with two polarities and galvanically isolated checkback signal via an 8-pole M12. Operating voltage 24 V DC. Total current 32 A. M12 connector, T-coded.

General ordering data

Version	Hood version, M12, 48 V, T-coded, LED: Yes, LED initiator: Yes, Wiring type:
Order No.	2495280000
Type	SAI-4-M-4P-M12-SVV-A03
GTIN (EAN)	4050118504927
Qty.	1 items

Data sheet

SAI-4-M-4P-M12-SVV-A03

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Approvals

Approvals	
ROHS	Conform
UL File Number Search	UL Website
Certificate No. (cURus)	E141197

Dimensions and weights

Net weight	100 g

Temperatures

Operating temperature	-20 - 80

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

Connection data

Conductor O.D., min.	6 mm	Conductor O.D., max.	12 mm
Cable gland	M 20	Conductor cross-section (rated connection), min.	0.5 mm²
Conductor cross-section (rated connection), max.	4 mm²	Distributor outlet	Hood version

Electrical data

Rated voltage, min.	10 V	Rated voltage, max.	48 V
Max. current-carrying capacity per slot	10 A	Total current	32 A
Current per signal	10 A	Insulation resistance	108 Ω
Potential response	Yes		

General technical data

Protection degree	IP68	Plug-in station coding	T-coded
Number of poles	4	Number of contact sockets	4
Connection thread	M12	Pollution severity	3
Fire behaviour	V-0	Plugging cycles	≤ 50
LED	Yes	LED initiator	Yes
LED colour for indicating operation	yellow	LED colour for I/O function	yellow

Material data

Housing main material	Pocan	Material of distributor	Plastic
Housing colour	grey, RAL 7032	Hood sealing material	Viton
Screw socket	Nickel-plated CuZn	Contact material	CuZn
Contact surface	Gold-plated	Contact carrier material	PBT (UL 94 V0)

Technical data cable

Number of poles	4	Conductor O.D., max.	12 mm
Conductor O.D., min.	6 mm	Suitable for cable carriers	No

SAI-4-M-4P-M12-SVV-A03

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Classifications

ETIM 8.0	EC003558	ETIM 9.0	EC003558
ETIM 10.0	EC003558	ECLASS 14.0	27-44-01-11
ECLASS 15.0	27-44-01-11		


SAI-4-M-4P-M12-SVV-A03

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

Dimensioned drawing



Wiring diagram

