Data sheet

# SAIL-7/8G7/8G-5-0.3U

**Weidmüller Interface GmbH & Co. KG**
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



Sensor/actuator cables are used for wiring sensors and actuators and for transmitting data or power in various applications. The moulded cable offers connected and tested connection of the plug-in connector to the cable ex-works. The cables may be exposed to a wide range of conditions, such as humidity, dust, heat, cold, shock or vibration.
The 7/8" cables tend to be used for power supply applications.
Is there something you have not managed to find or you feel needs explanation? Talk to us!

## General ordering data

| | |
|---|---|
| Version | Sensor/actuator line, 7/8", Number of poles : 5 (4 + PE), 0.3 m, pin, straight - socket, straight, Shielded: No, LED: No, Sheath material: PUR, Halogen: No |
| Order No. | 2519450030 |
| Type | SAIL-7/8G7/8G-5-0.3U |
| GTIN (EAN) | 4050118534283 |
| Qty. | 1 items |

# Data sheet

## SAIL-7/8G7/8G-5-0.3U

**Weidmüller Interface GmbH & Co. KG**
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

# Technical data

### Approvals

| | |
|---|---|
| Approvals | |
| ROHS | Conform |

### Dimensions and weights

| | |
|---|---|
| Net weight | 80 g |

### Environmental Product Compliance

| | |
|---|---|
| RoHS Compliance Status | Compliant with exemption |
| RoHS Exemption (if applicable/known) | 6c |
| REACH SVHC | Lead 7439-92-1 |
| SCIP | e8d8af70-4c85-4483-bc8c-9bc5b598e2a9 |

### Technical specifications for cable

| | | | |
|---|---|---|---|
| Cable length | 0.3 m | Sheathing colour | black |
| PE function | Yes | Suitable for cable carriers | Yes |
| Core cross-section | 1.5 mm² | Shielded | No |
| Halogen | No | Insulation | TPM |
| Bending radius, min., moving | 7.5 x cable diameter | Bending cycles | 5 Mio |
| Sheath material | PUR | Cable length configurable | No |
| Outer cladding in accordance with UL AWM style | 20234 (80 °C / 1000 V) | Irradiation crosslinked | No |
| Welding spark resistance | No | Colour coding | brown, white, blue, black, Green/yellow |
| Torsion resistance | 0 °/m | Temperature range, stationary | -50...80 °C |
| Resistant to welding beads | No | Temperature range, moving | -20...80 °C |
| Number of poles | 5 (4 + PE) | Outside diameter | 8.7 mm ± 0.2 mm |

### General technical data

| | | | |
|---|---|---|---|
| Coding | none | Connection thread | 7/8" |
| Contact surface | Au (Gold) | LED | No |
| Version | pin, straight - socket, straight | Housing main material | PUR |
| Insulation resistance | 108 Ω | Contact material | CuZn |
| Nominal voltage | 300 V | Nominal current | 9 A |
| Protection degree | IP68, when screwed in | Plugging cycles | ≥ 100 |
| Pollution severity | 3 | jumpered | No |
| Rated impulse voltage | 2500 V | Rated voltage (UL) | 600 V |
| Threaded ring material | Diecast zinc | Temperature range of housing | -40 ... +85 ° C |
| Tightening torque | 7/8": 1.5 Nm | | |

### Electrical properties

| | | | |
|---|---|---|---|
| Volume resistance | ≤3 mΩ | Insulation resistance | 108 Ω |
| Nominal voltage | 300 V | | |

# SAIL-7/8G7/8G-5-0.3U

**Weidmüller Interface GmbH & Co. KG**
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

## Technical data

### Plug, left

| | |
|---|---|
| Plug left | IP68, male contact, straight, Plastic, unshielded |

### Plug, right

| | |
|---|---|
| Plug right | IP68, female contact, straight, Plastic, unshielded |

### Classifications

| | | | |
|---|---|---|---|
| ETIM 8.0 | EC001855 | ETIM 9.0 | EC001855 |
| ETIM 10.0 | EC001855 | ECLASS 14.0 | 27-06-03-11 |
| ECLASS 15.0 | 27-06-03-11 | | |


# SAIL-7/8G7/8G-5-0.3U

**Weidmüller Interface GmbH & Co. KG**
Klingenbergstraße 26
D-32758 Detmold
Germany


www.weidmueller.com

## Drawings


### Dimensioned drawing




### Pole scheme




### Pole scheme




### Wiring diagram

