

SM 27/18-22 MM GR VPE100**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



Prevention of incorrect operation: SM

MultiMark device markers can be used with marking materials from different manufacturers. Wherever they are used, they ensure that all components, such as control and signalling devices from different vendors, are clearly assigned.

Your benefits with MultiMark

- “Different materials for various requirements”
- Can be used with equipment from many manufacturers
- Device markers with a familiar design

General ordering data

Version	SwitchMark, Device markers, 47.75 x 27 mm, grey
Order No.	2496940000
Type	SM 27/18-22 MM GR VPE100
GTIN (EAN)	4050118508444
Qty.	100 items

SM 27/18-22 MM GR VPE100

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

ROHS Conform

Dimensions and weights

Depth	0.1 mm	Depth (inches)	0.0039 inch
Height	47.75 mm	Height (inches)	1.8799 inch
Width	27 mm	Width (inches)	1.063 inch
Diameter	22 mm	Net weight	0.1 g

Temperatures

Operating temperature range -40...120 °C

Environmental Product Compliance

RoHS Compliance Status Compliant without exemption
 REACH SVHC No SVHC above 0.1 wt%

General data

Adhesive	Acrylate adhesive	Version	halogen-free, Self-adhesive
Width	27 mm	UL 94 flammability rating	V-0
Operating temperature range, max.	120 °C	Operating temperature range, min.	-40 °C
Colour	grey	Halogen	No
Basic material	Polyester	Printed characters	without
Size of labelling field	18 x 27 mm	Approval acc. to UL 969	Yes
compatible printer	THM MULTIMARK , THM MULTIMARK PLUS	Operating temperature range	-40...120 °C

Device markers

Diameter 22 mm Halogen No

Classifications

ETIM 8.0	EC001288	ETIM 9.0	EC001288
ETIM 10.0	EC001288	ECLASS 14.0	27-28-11-04
ECLASS 15.0	27-28-11-04		

Drawings



SM 27/18-22 MM GR VPE100

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Accessories

Ink ribbons



These printers produce excellent printing results thanks to the thermal transfer technique. Different materials and the user-friendly printing system under Windows optimise marking efforts.

General ordering data

Type	RIBBON MM 76/360 SW	Version	
Order No.	2005080000	Ink ribbon	
GTIN (EAN)	4050118389951		
Qty.	1 ST		

THM MULTIMARK



These printers produce excellent printing results thanks to the thermal transfer technique. Different materials and the user-friendly printing system under Windows optimise marking efforts.

General ordering data

Type	MULTIMARK ROLLER 115	Version	
Order No.	1357420000		
GTIN (EAN)	4050118160314		
Qty.	1 ST		

THM MULTIMARK PLUS



These printers produce excellent printing results thanks to the thermal transfer technique. Different materials and the user-friendly printing system under Windows optimise marking efforts.

General ordering data

Type	MULTIMARK PLUS ROLLER 1...	Version	
Order No.	2672590000		
GTIN (EAN)	4050118708097		
Qty.	1 ST		