

**ZQV 16N/2****Weidmüller Interface GmbH & Co. KG**Klingenbergstraße 26  
D-32758 Detmold  
Germany

www.weidmueller.com

**Product image**

The distribution or multiplication of a potential to adjoining terminal blocks is realized via a cross-connection. Additional wiring effort can be easily avoided. Even if the poles are broken out, contact reliability in the terminal blocks is still ensured. Our portfolio offers pluggable and screwable cross-connection systems for modular terminal blocks.

**General ordering data**

Version	Cross-connector (terminal), Plugged, orange, 76 A, Number of poles: 2, Pitch in mm (P): 12.00, Insulated: Yes, Width: 20.6 mm
Order No.	<a href="#">2497290000</a>
Type	ZQV 16N/2
GTIN (EAN)	4050118561906
Qty.	25 items

## ZQV 16N/2

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Approvals

ROHS Conform

## Dimensions and weights

Depth	36.55 mm	Depth (inches)	1.439 inch
Height	5.2 mm	Height (inches)	0.2047 inch
Width	20.6 mm	Width (inches)	0.811 inch
Net weight	9.9 g		

## Temperatures

Storage temperature	-25 °C...55 °C	Ambient temperature	-5 °C...40 °C
Continuous operating temp., min.	-60 °C	Continuous operating temp., max.	130 °C

## Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

## Material data

Basic material	Wemid	Colour	orange
UL 94 flammability rating	V-0		

## System specifications

Version For the terminals

## Additional technical data

Type of fixing	Plugged	Explosion-tested version	No
----------------	---------	--------------------------	----

## Dimensions

Pitch in mm (P) 12.00 mm

## General

Number of poles 2

## Rating data

Rated voltage	400 V	Nominal current	76 A
---------------	-------	-----------------	------

## Classifications

ETIM 8.0	EC000489	ETIM 9.0	EC000489
ETIM 10.0	EC000489	ECLASS 14.0	27-25-03-03
ECLASS 15.0	27-25-03-03		