

HS-HF 1.2-2.4/12 MM Y**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



The heat-shrinkable sleeve is printable on 2 sides and can be used for marking and insulating cables and wires. The flexible, heat-shrink material enables a firm, perfect fit around the conductor and therefore saves space.

General ordering data

Version	Conductor and cable markers, 1.2 - 2.4 mm, 12.7 x 5 mm, yellow
Order No.	2526240000
Type	HS-HF 1.2-2.4/12 MM Y
GTIN (EAN)	4050118537390
Qty.	4000 items

HS-HF 1.2-2.4/12 MM Y

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

ROHS Conform

Dimensions and weights

Depth	0.77 mm	Depth (inches)	0.0303 inch
Height	12.7 mm	Height (inches)	0.5 inch
Width	5 mm	Width (inches)	0.1968 inch
Net weight	0.12 g		

Temperatures

Operating temperature range -55...105 °C

Environmental Product Compliance

RoHS Compliance Status Compliant without exemption
 REACH SVHC No SVHC above 0.1 wt%

General data

Type of printing	neutral	Width	5 mm
Operating temperature range, max.	105 °C	Operating temperature range, min.	-55 °C
Colour	yellow	Halogen	No
Basic material	Polyolefine	Printed characters	without
compatible printer	THM MULTIMARK , THM MULTIMARK PLUS	Operating temperature range	-55...105 °C
Number per roll	4000		

Conductor and cable markers

Halogen	No	Conductor cross-section, max.	0.5 mm ²
Conductor cross-section, min.	0.25 mm ²	Conductor O.D., max.	2.4 mm
Conductor O.D., min.	1.2 mm	Rate of shrinkage	2:1
Recommended shrinking temperature	90 °C	Conductor O.D.	1.2 - 2.4 mm
Cross-section for connected wire	0.25 - 0.5 mm ²		

Classifications

ETIM 8.0	EC001530	ETIM 9.0	EC001530
ETIM 10.0	EC001530	ECLASS 14.0	27-28-11-02
ECLASS 15.0	27-28-11-02		

HS-HF 1.2-2.4/12 MM Y

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Accessories

Ink ribbons



These printers produce excellent printing results thanks to the thermal transfer technique. Different materials and the user-friendly printing system under Windows optimise marking efforts.

General ordering data

Type	RIBBON MM-HS 60/300 SW	Version	
Order No.	2448880000	Ink ribbon	
GTIN (EAN)	4050118462944		
Qty.	1 ST		

THM MULTIMARK



These printers produce excellent printing results thanks to the thermal transfer technique. Different materials and the user-friendly printing system under Windows optimise marking efforts.

General ordering data

Type	MULTIMARK ROLLER 115	Version	
Order No.	1357420000		
GTIN (EAN)	4050118160314		
Qty.	1 ST		

THM MULTIMARK PLUS



These printers produce excellent printing results thanks to the thermal transfer technique. Different materials and the user-friendly printing system under Windows optimise marking efforts.

General ordering data

Type	MULTIMARK PLUS ROLLER 1...	Version	
Order No.	2672590000		
GTIN (EAN)	4050118708097		
Qty.	1 ST		