

**HS-HF 1.2-2.4/12 MM Y**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

www.weidmueller.com



The heat-shrinkable sleeve is printable on 2 sides and can be used for marking and insulating cables and wires. The flexible, heat-shrink material enables a firm, perfect fit around the conductor and therefore saves space.

**General ordering data**

|            |  |
|------------|--|
| Version    | Conductor and cable markers, 1.2 - 2.4 mm, 12.7 x 5 mm, yellow |
| Order No.  | <a href="#">2526240000</a>                                     |
| Type       | HS-HF 1.2-2.4/12 MM Y  |
| GTIN (EAN) | 4050118537390  |
| Qty.       | 4000 items   |

## HS-HF 1.2-2.4/12 MM Y

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technical data

### Approvals

|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

### Dimensions and weights

|            |         |                 |             |
|------------|---------|-----------------|-------------|
| Depth      | 0.77 mm | Depth (inches)  | 0.0303 inch |
| Height     | 12.7 mm | Height (inches) | 0.5 inch    |
| Width      | 5 mm    | Width (inches)  | 0.1968 inch |
| Net weight | 0.12 g  |                 |             |

### Temperatures

|                             |              |
|-----------------------------|--------------|
| Operating temperature range | -55...105 °C |
|-----------------------------|--------------|

### Environmental Product Compliance

|                        |                             |
|------------------------|-----------------------------|
| RoHS Compliance Status | Compliant without exemption |
| REACH SVHC             | No SVHC above 0.1 wt%       |

### General data

|                                   |  |                                   |              |
|-----------------------------------|--|-----------------------------------|--------------|
| Type of printing                  | neutral  | Width                             | 5 mm         |
| Operating temperature range, max. | 105 °C   | Operating temperature range, min. | -55 °C       |
| Colour                            | yellow   | Halogen                           | No           |
| Basic material                    | Polyolefine  | Printed characters                | without      |
| compatible printer                | <a href="#">THM MULTIMARK</a> , <a href="#">THM MULTIMARK PLUS</a> | Operating temperature range       | -55...105 °C |
| Number per roll                   | 4000   |                                   |              |

### Conductor and cable markers

|                                   |                            |                               |                     |
|-----------------------------------|----------------------------|-------------------------------|---------------------|
| Halogen                           | No                         | Conductor cross-section, max. | 0.5 mm <sup>2</sup> |
| Conductor cross-section, min.     | 0.25 mm <sup>2</sup>       | Conductor O.D., max.          | 2.4 mm              |
| Conductor O.D., min.              | 1.2 mm                     | Rate of shrinkage             | 2:1                 |
| Recommended shrinking temperature | 90 °C                      | Conductor O.D.                | 1.2 - 2.4 mm        |
| Cross-section for connected wire  | 0.25 - 0.5 mm <sup>2</sup> |                               |                     |

### Classifications

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 8.0    | EC001530    | ETIM 9.0    | EC001530    |
| ETIM 10.0   | EC001530    | ECLASS 14.0 | 27-28-11-02 |
| ECLASS 15.0 | 27-28-11-02 |             |             |

**Drawings**

