

HS-HF 4.8-9.5/12 MM Y**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



The heat-shrinkable sleeve is printable on 2 sides and can be used for marking and insulating cables and wires. The flexible, heat-shrink material enables a firm, perfect fit around the conductor and therefore saves space.

General ordering data

| | |
|------------|---|
| Version | Conductor and cable markers, 4.8 - 9.5 mm, 12.7 x 16.1 mm, yellow |
| Order No. | 2526320000 |
| Type | HS-HF 4.8-9.5/12 MM Y |
| GTIN (EAN) | 4050118537475 |
| Qty. | 2000 items |

HS-HF 4.8-9.5/12 MM Y

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

ROHS Conform

Dimensions and weights

| | | | |
|------------|---------|-----------------|-------------|
| Depth | 0.77 mm | Depth (inches) | 0.0303 inch |
| Height | 12.7 mm | Height (inches) | 0.5 inch |
| Width | 16.1 mm | Width (inches) | 0.6339 inch |
| Net weight | 0.33 g | | |

Temperatures

Operating temperature range -55...105 °C

Environmental Product Compliance

RoHS Compliance Status Compliant without exemption
 REACH SVHC No SVHC above 0.1 wt%

General data

| | | | |
|-----------------------------------|--|-----------------------------------|--------------|
| Type of printing | neutral | Width | 16.1 mm |
| Operating temperature range, max. | 105 °C | Operating temperature range, min. | -55 °C |
| Colour | yellow | Halogen | No |
| Basic material | Polyolefine | Printed characters | without |
| compatible printer | THM MULTIMARK , THM MULTIMARK PLUS | Operating temperature range | -55...105 °C |
| Number per roll | 2000 | | |

Conductor and cable markers

| | | | |
|-----------------------------------|------------------------|-------------------------------|--------------------|
| Halogen | No | Conductor cross-section, max. | 16 mm ² |
| Conductor cross-section, min. | 4 mm ² | Conductor O.D., max. | 9.5 mm |
| Conductor O.D., min. | 4.8 mm | Rate of shrinkage | 2:1 |
| Recommended shrinking temperature | 90 °C | Conductor O.D. | 4.8 - 9.5 mm |
| Cross-section for connected wire | 4 - 16 mm ² | | |

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 8.0 | EC001530 | ETIM 9.0 | EC001530 |
| ETIM 10.0 | EC001530 | ECLASS 14.0 | 27-28-11-02 |
| ECLASS 15.0 | 27-28-11-02 | | |

Drawings

