

## VPU PV I+II 3 R 1500

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)



### General ordering data

Version	Surge voltage arrester, Low voltage, with remote contact
Order No.	<a href="#">2530590000</a>
Type	VPU PV I+II 3 R 1500
GTIN (EAN)	4050118540802
Qty.	1 items

## VPU PV I+II 3 R 1500

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Approvals

Approvals



ROHS	Conform
UL File Number Search	<a href="#">UL Website</a>
Certificate No. (cURus)	E3542610000

## Dimensions and weights

Depth	86 mm	Depth (inches)	3.3858 inch
Height	102 mm	Height (inches)	4.0157 inch
Width	54 mm	Width (inches)	2.126 inch
Net weight	480 g		

## Temperatures

Storage temperature	-40 °C...85 °C	Operating temperature	-40 °C...85 °C
Humidity	5 - 95% rel. humidity		

## Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

## Rated data UL

Ambient temperature (operational), max. 85 °C	Rated Voltage UN	1500 V
SCCR	In	20 kA
Category	Ambient temperature (operational), min. -40 °C	
Certificate No. (cURus)	VPR ( DC+ /DC-)	4000 V
VPR ( DC-/G)	Voltage type	DC

## Connection data, remote alert

Cross-section for connected wire, solid core, min.	0.25 mm <sup>2</sup>	Stripping length	12 mm
Connection type	PUSH IN	Cross-section for connected wire, solid core, max.	1.5 mm <sup>2</sup>

## General data

Optical function display	green = OK; red = arrester is defective - replace	Version	with remote contact
Design	Installation housing; 3TE, Insta IP 20	UL 94 flammability rating	V-0
Colour	black, orange	Protection degree	IP20
Mounting rail	TS 35	Operating altitude	<4,000 m, see operating instructions, ≤ 4000 m

## Insulation coordination acc. to EN 50178

Surge voltage category	III	Pollution severity	2
------------------------	-----	--------------------	---

## VPU PV I+II 3 R 1500

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technical data

### Photovoltaic technical data

Standards	EN 61643-31, EN 50539-11, UL 1449	Lightning test current Iimp (10/350 µs)	5 kA
Protection level Up (+/-, -/PE, +/-PE)	≤ 5,0 kV	Operating height in ungrounded PV system	≤ 4000 m
Short-circuit current ISCPV	11000 A	Total discharge current I <sub>total</sub> (8/20µs)	40 kA
Discharge current I <sub>n</sub> (8/20 µs)	20 kA	Requirements class	Type I/II
Operating height in the grounded PV system	≤ 2000 m	Total discharge current I <sub>total</sub> (10/350µs)	10 kA
PV system voltage, max. U <sub>cpv</sub>	1500 V		

### Rated data IEC / EN

Number of poles	3	Leakage current at U <sub>n</sub>	30 µA
Signalling contact	250 V 1A 1CO	Rated voltage (DC)	1500 V
Voltage type	DC	Response time / fallback time	≤ 25 ns
Standards	EN 61643-31, EN 50539-11, UL 1449	Lightning test current Iimp (10/350 µs)	5 kA
Energy coordination (≤10 m)	Type I, Type II, Type III	Discharge current I <sub>max</sub> (8/20µs) wire-PE30 kA	
SPD type	T1, T2	Integrated back-up fuse	No

### Connection data

Stripping length	18 mm	Type of connection	Screw connection
Stripping length, rated connection	18 mm	Tightening torque, min.	3 Nm
Tightening torque, max.	4.5 Nm	Clamping range, rated connection	6 mm <sup>2</sup>
Clamping range, min.	1.5 mm <sup>2</sup>	Clamping range, max.	35 mm <sup>2</sup>
Wire cross-section, solid, min.	1.5 mm <sup>2</sup>	Wire cross-section, solid, max.	35 mm <sup>2</sup>
Wire connection cross section, finely stranded, min.	1.5 mm <sup>2</sup>	Wire connection cross section, finely stranded, max.	35 mm <sup>2</sup>
Connection cross-section, stranded, min.	1.5 mm <sup>2</sup>	Connection cross-section, stranded, max.	35 mm <sup>2</sup>

### Electrical data

Voltage type	DC
--------------	----

### General data

Number of poles	3	Protection degree	IP20
Colour	black, orange		

### Guarantee

Time interval	5 years
---------------	---------

### Classifications

ETIM 8.0	EC001457	ETIM 9.0	EC001457
ETIM 10.0	EC001457	ECLASS 14.0	27-17-14-03
ECLASS 15.0	27-17-14-03		

Electric symbol



Circuit diagram