

VPU PV I+II 0 1000

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Approvals

Approvals



ROHS Conform

UL File Number Search [UL Website](#)

Certificate No. (cURus) E354261

Dimensions and weights

Depth	73.5 mm	Depth (inches)	2.8937 inch
Height	45 mm	Height (inches)	1.7716 inch
Width	18 mm	Width (inches)	0.7087 inch
Net weight	89 g		

Temperatures

Storage temperature	-40 °C...85 °C	Operating temperature	-40 °C...85 °C
Humidity	5 - 95% rel. humidity		

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

Rated data UL

Ambient temperature (operational), max. 85 °C	Rated Voltage UN	550 V
SCCR	In	20 kA
Category	Ambient temperature (operational), min. -40 °C	
Certificate No. (cURus)	VPR (DC+/DC-)	2500 V
Voltage type		

General data

Optical function display	green = OK; red = arrester is defective - replace	Version	Surge protection I / II, Spare arrester
Design	Installation housing; 1TE	UL 94 flammability rating	V-0
Colour	orange	Protection degree	IP20
Operating altitude	≤ 4000 m		

Insulation coordination acc. to EN 50178

Surge voltage category	III	Pollution severity	2
------------------------	-----	--------------------	---

Photovoltaic technical data

Standards	EN 61643-31, EN 50539-11, UL 1449	Lightning test current Iimp (10/350 μs)	6.25 kA
Protection level Up (+/-, -/PE, +/-PE)	≤ 3.8 kV	Short-circuit current ISCPV	11000 A
Total discharge current Itotal (8/20μs)	50 kA	Discharge current In (8/20 μs)	20 kA
Requirements class	Type I/II	Operating height in the grounded PV system	≤ 2000 m
Total discharge current Itotal (10/350μs)	12.5 kA	PV system voltage, max. Ucpv	1100 V

VPU PV I+II 0 1000

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Rated data IEC / EN

Number of poles	1	Leakage current at Un	30 µA
Signalling contact	No	Voltage type	DC
Fuse protection	No	Response time / fallback time	≤ 25 ns
Standards	EN 61643-31, EN 50539-11, UL 1449	Lightning test current Iimp (10/350 µs)	6.25 kA
Energy coordination (≤10 m)	Type I, Type II, Type III	SPD type	T1, T2
Integrated back-up fuse	No		

Connection data

Stripping length	18 mm	Type of connection	pluggable
Wire cross-section, solid, min.	1.5 mm ²	Wire cross-section, solid, max.	35 mm ²
Wire connection cross section, finely stranded, max.	35 mm ²		

Electrical data

Voltage type	DC
--------------	----

General data

Number of poles	1	Protection degree	IP20
Colour	orange		

Guarantee

Time interval	5 years
---------------	---------

Classifications

ETIM 8.0	EC001457	ETIM 9.0	EC001457
ETIM 10.0	EC001457	ECLASS 14.0	27-17-14-03
ECLASS 15.0	27-17-14-03		

Drawings

Electric symbol



Circuit diagram