Data sheet

SAISGC-M-5L-5.8/13.5-M12-CF

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



Your peripheral devices should be supplied with greater power. With our new M12 plug-in connector, more than 250 V and 2 A is possible without problems. The compact A-, K-, L-, S- and T-coded M12 plug-in connectors are designed for the transmission of up to 630 V AC or 60 V DC and 12 A.

General ordering data

Version	Field attachable connector, M12 plug
Order No.	2531020000
Type	SAISGC-M-5L-5.8/13.5-M12-CF
GTIN (EAN)	4050118541137
Qty.	1 items

Data sheet

SAISGC-M-5L-5.8/13.5-M12-CF

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Approvals

Approvals	
ROHS	Conform
UL File Number Search	UL Website
Certificate No. (cURus)	E307231

Dimensions and weights

Net weight	43 g

Environmental Product Compliance

RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	6c
REACH SVHC	Lead 7439-92-1
SCIP	ebf89fc8-a87f-4691-b87a-dfb9921774b4

Technical data customisable plug-in connectors

Number of poles	5	Coding	L-coded
Contact surface	Gold-plated	Type of connection	Crimp connection
Housing main material	Zinc diecast	Cable diameter, max.	13.5 mm
Cable diameter, min.	5.8 mm	Contact material	Cu
Conductor cross-section, max.	2.5 mm²	Conductor cross-section, min.	0.5 mm²
Nominal voltage	63 V	Nominal current	16 A
Protection degree	IP67, when screwed in	Plugging cycles	500
Pollution severity	3	Rated current	16 A
Shield connection	Yes	Threaded ring material	Diecast zinc
Temperature range of housing	-40 ... +85 ° C	Connection cross-section, max.	1.5 mm²
Connection cross-section, min.	0.75 mm²		

General Info

Number of poles	5	Connection 1	M12
Connection 2	Crimp	Housing main material	Zinc diecast
Connection thread	M12 plug	Contact material	Cu
Contact surface	Gold-plated	Protection degree	IP67, when screwed in
Plugging cycles	500		

Standards

Connector standard	IEC 61076-2-111

Important note

Product information	Enclosures, inserts and crimp contacts need to be ordered separately. 4 x Crimp contact, Pin / 1 x Crimp contact, Socket for FE-Function.

Classifications

ETIM 8.0	EC002635	ETIM 9.0	EC002635
ETIM 10.0	EC002635	ECLASS 14.0	27-44-01-16
ECLASS 15.0	27-44-01-16		


SAISGC-M-5L-5.8/13.5-M12-CF

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

Dimensioned drawing



Pole scheme

