

IE-FCI-PWB-ISR**Weidmüller Interface GmbH & Co. KG**Klingenbergsstraße 26
D-32758 Detmold
Germanywww.weidmueller.com

FrontCom® Vario integrates multiple functions in only one single frame. The system is easy to install and you can select from a wide range of data, signal and power modules. In addition to being extremely compact, FrontCom® Vario offers a number of unique product features that will make your project planning and work activities secure, fast and future-proof. Furthermore, the FrontCom® Vario system has an attractive housing design that, by the way, offers highest impact-resistance and fully meets the requirements of IP 65 protection class.

General ordering data

Version	FrontCom, Insert Power large, Type H, Socket connector, ISR
Order No.	2531060000
Type	IE-FCI-PWB-ISR
GTIN (EAN)	4050118541175
Qty.	1 items

Technical data**Approvals**

Approvals



RoHS Conform

Dimensions and weights

Net weight 36 g

TemperaturesStorage temperature
Installation temperature Operating temperature -5 °C...40 °C**Environmental Product Compliance**RoHS Compliance Status Compliant without exemption
REACH SVHC No SVHC above 0.1 wt%**General data**Protection degree IP20 Insert type Insert Power large
Connector face Type H**Clampable conductors**

Stripping length	11 mm
Type of connection	Screw connection
Conductor connection cross-section, extremely flexible with wire end ferrule	min. 1.5 mm ² max. 1.5 mm ²
Conductor connection cross-section, rigid	min. 1.5 mm ² max. 2.5 mm ²
Conductor connection cross-section, flexible with wire end ferrule	min. 1.5 mm ² max. 1.5 mm ²
Conductor connection cross-section, flexible without wire end ferrule	...
Conductor connection cross-section, extremely flexible without wire end ferrule	...
Conductor connection cross-section, rigid	1.5 ... 2.5 mm ²
Conductor connection cross-section, flexible with wire end ferrule	1.5 ... 1.5 mm ²
Conductor connection cross-section, extremely flexible with wire end ferrule	1.5 ... 1.5 mm ²

Technical dataRated voltage (AC) 250 V Housing main material PP
Nominal current 16 A**Classifications**ETIM 8.0 EC001121 ETIM 9.0 EC001121
ETIM 10.0 EC001121 ECLASS 14.0 27-18-28-92

IE-FCI-PWB-ISR

Weidmüller Interface GmbH & Co. KG
Klingenbergsstraße 26
D-32758 Detmold
Germany

Technical data

www.weidmueller.com


ECLASS 15.0

27-18-28-92

IE-FCI-PWB-ISR

Weidmüller Interface GmbH & Co. KG
Klingenbergsstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings**Dimensioned drawing****Dimensioned drawing**