

**SCREWTY M12 K+L 2.5 O.SD****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

Weidmüller offers a wide range of tools and accessories for sensor-actuator cabling.

**General ordering data**

|            |                                                                |
|------------|----------------------------------------------------------------|
| Version    | Cable gland tool adapter for moulded M12 lines, K- and L-coded |
| Order No.  | <a href="#">2522710000</a>                                     |
| Type       | SCREWTY M12 K+L 2.5 O.SD                                       |
| GTIN (EAN) | 4050118534566                                                  |
| Qty.       | 1 items                                                        |
| Packaging  | Plastic bag                                                    |

**SCREWTY M12 K+L 2.5 O.SD****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Technical data****Approvals**

|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

**Dimensions and weights**

|            |        |
|------------|--------|
| Net weight | 18.8 g |
|------------|--------|

**Environmental Product Compliance**

|                        |                       |
|------------------------|-----------------------|
| RoHS Compliance Status | Not affected          |
| REACH SVHC             | No SVHC above 0.1 wt% |

**Screwing tools**

|                   |     |      |         |
|-------------------|-----|------|---------|
| Connection thread | M12 | Size | 17.5 mm |
|-------------------|-----|------|---------|

**Classifications**

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 8.0    | EC000149    | ETIM 9.0    | EC000149    |
| ETIM 10.0   | EC000149    | ECLASS 14.0 | 21-01-90-90 |
| ECLASS 15.0 | 21-01-90-90 |             |             |