



Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

Product image















1

Connect efficiently - in a small space: female header with spring connection (PUSH IN) as a plug-in connection level; used together with male headers in 3.50 mm pitch.

General ordering data

Version	PCB plug-in connector, female plug, 3.50 mm, Number of poles: 2, 180°, PUSH IN with actuator, Clamping range, max. : 1.5 mm², Box
Order No.	<u>2537880000</u>
Туре	BLF 3.50/02/180LH SN BK BX
GTIN (EAN)	4050118549539
Qty.	132 items
Product data	IEC: 320 V / 17.5 A / 0.14 - 1.5 mm ²
	UL: 300 V / 10 A / AWG 26 - AWG 16
Packaging	Вох





Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

Technical data

Approvals	Αı	pp	ro	va	Is
-----------	----	----	----	----	----

Approvals	c FL *us
ROHS	Conform
UL File Number Search	<u>UL Website</u>
Certificate No. (cURus)	E60693

Dimensions and weights

Depth	30.05 mm	Depth (inches)	1.1831 inch
Height	15.08 mm	Height (inches)	0.5937 inch
Width	13.9 mm	Width (inches)	0.5472 inch
Net weight	2.15 g		

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

System Parameters

•	OMNIMATE Signal - series BL/SL 3.50 Field connection
Type of connection	Field connection
.,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,	. I total de l'illie d
Wire connection method	PUSH IN with actuator
Pitch in mm (P)	3.50 mm
Pitch in inches (P)	0.138 "
Conductor outlet direction	180°
Number of poles 2	2
L1 in mm	3.50 mm
L1 in inches	0.138 "
Number of rows	1
Pin series quantity	1
Rated cross-section	1.5 mm ²
Touch-safe protection acc. to DIN VDE 57 106	Safe from finger touch
Touch-safe protection acc. to DIN VDE I 0470	IP20 plugged/ IP10 unplugged
Protection degree I	IP20, when fully mounted
Volume resistance	≤5 mΩ
Can be coded	Yes
Stripping length 8	8 mm
Stripping length tolerance	min. 0 mm
	max. 1 mm
Screwdriver blade (0.4 x 2.5
Screwdriver blade standard [DIN 5264-A
Plugging cycles 2	25
Plugging force/pole, max.	6 N
Pulling force/pole, max.	6 N

Material data

Insulating material	PA GF	Colour	black
Colour chart (similar)	RAL 9011	Insulating material group	II
Comparative Tracking Index (CTI)	≥ 400, ≤ 600	Moisture Level (MSL)	
UL 94 flammability rating	V-0	Contact material	Cu-alloy

Creation date 30.11.2025 06:32:44 MEZ





Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

Technical data

Contact surface	tinned	Storage temperature, min.	-40 °C
Storage temperature, max.	70 °C	Operating temperature, min.	-50 °C
Operating temperature, max.	120 °C	Temperature range, installation, min.	-30 °C
Temperature range, installation, max.	100 °C		

Clamping range, min.	0.14 mm ²		
Clamping range, max.	1.5 mm ²		
Wire connection cross section AWG, min.	AWG 26		
Vire connection cross section AWG, max.	AWG 16		
Solid, min. H05(07) V-U	0.14 mm ²		
Solid, max. H05(07) V-U	1.5 mm ²		
Flexible, min. H05(07) V-K	0.14 mm ²		
Flexible, max. H05(07) V-K	1.5 mm ²		
w. plastic collar ferrule, DIN 46228 pt min.	4, 0.28 mm²		
w. plastic collar ferrule, DIN 46228 pt max.	4, 1 mm²		
w. wire end ferrule, DIN 46228 pt 1, min.	0.25 mm ²		
w. wire end ferrule, DIN 46228 pt 1, max.	1 mm ²		
Plug gauge in accordance with EN 60999 a x b; ø	2.4 mm x 1.5 mm		
Clampable conductor	Cross-section for conductor connection	Туре	fine-wired
		nominal	0.25 mm ²
	wire end ferrule	Stripping length	nominal 10 mm
		Recommended wire- end ferrule	H0,25/12 HBL
	Cross-section for conductor connection	Type	fine-wired
		nominal	0.34 mm ²
	wire end ferrule	Stripping length	nominal 10 mm
	wire end ferrule	Stripping length Recommended wire- end ferrule	nominal 10 mm H0,34/12 TK
	wire end ferrule Cross-section for conductor connection	Recommended wire-	
		Recommended wire- end ferrule	H0,34/12 TK
		Recommended wire- end ferrule Type	H0,34/12 TK fine-wired 0.5 mm ²
	Cross-section for conductor connection	Recommended wire- end ferrule Type nominal	H0,34/12 TK fine-wired 0.5 mm ²
	Cross-section for conductor connection	Recommended wire- end ferrule Type nominal Stripping length Recommended wire-	H0,34/12 TK fine-wired 0.5 mm² nominal 10 mm
	Cross-section for conductor connection wire end ferrule	Recommended wire- end ferrule Type nominal Stripping length Recommended wire- end ferrule	H0,34/12 TK fine-wired 0.5 mm ² nominal 10 mm H0.5/14 OR
	Cross-section for conductor connection wire end ferrule	Recommended wire- end ferrule Type nominal Stripping length Recommended wire- end ferrule Type	h0,34/12 TK fine-wired 0.5 mm² nominal 10 mn h0.5/14 OR fine-wired 0.75 mm²
	Cross-section for conductor connection wire end ferrule Cross-section for conductor connection	Recommended wire- end ferrule Type nominal Stripping length Recommended wire- end ferrule Type nominal	h0,34/12 TK fine-wired 0.5 mm² nominal 10 mn h0.5/14 OR fine-wired 0.75 mm²
	Cross-section for conductor connection wire end ferrule Cross-section for conductor connection	Recommended wire- end ferrule Type nominal Stripping length Recommended wire- end ferrule Type nominal Stripping length Recommended wire- end ferrule Type	fine-wired 0.5 mm² nominal 10 mn H0.5/14 OR fine-wired 0.75 mm² nominal 10 mn H0.75/14T HBL fine-wired
	Cross-section for conductor connection wire end ferrule Cross-section for conductor connection wire end ferrule	Recommended wire- end ferrule Type nominal Stripping length Recommended wire- end ferrule Type nominal Stripping length Recommended wire- end ferrule	fine-wired 0.5 mm² nominal 10 mm H0.5/14 OR fine-wired 0.75 mm² nominal 10 mm H0.75/14T HBL

Creation date 30.11.2025 06:32:44 MEZ

3 Catalogue status / Drawings

is to be chosen depending on the product and the rated voltage.





Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

Technical data

Rated data acc. to IEC			
tested acc. to standard	IEC 60664-1, IEC 61984	Rated current, min. number of poles (Tu=20°C)	17.5 A
Rated current, max. number of poles (Tu=20°C)	14.7 A	Rated current, min. number of poles (Tu=40°C)	17.1 A
Rated current, max. number of poles (Tu=40°C)	13.1 A	Rated voltage for surge voltage class / pollution degree II/2	320 V
Rated voltage for surge voltage class / pollution degree III/2	160 V	Rated voltage for surge voltage class / pollution degree III/3	160 V
Rated impulse voltage for surge voltage class/ pollution degree II/2	2.5 kV	Rated impulse voltage for surge voltage class/ pollution degree III/2	2.5 kV
Rated impulse voltage for surge voltage class/ contamination degree III/3	2.5 kV	Short-time withstand current resistance	1 x 1s with 120 A

Rated data acc. to CSA

Rated voltage (Use group B / CSA)	300 V	Rated voltage (Use group C / CSA)	50 V
Rated voltage (Use group D / CSA)	300 V	Rated current (Use group B / CSA)	10 A
Rated current (Use group D / CSA)	10 A	Wire cross-section, AWG, min.	AWG 16
Wire cross-section, AWG, max.	AWG 26		

Rated data acc. to UL 1059

Institute (cURus)	CURUS	Certificate No. (cURus)	E60693
Rated voltage (Use group B / UL 1059)	300 V	Rated voltage (Use group C / UL 1059)	50 V
Rated voltage (Use group D / UL 1059)	300 V	Rated current (Use group B / UL 1059)	10 A
Rated current (Use group D / UL 1059)	10 A	Wire cross-section, AWG, min.	AWG 26
Wire cross-section, AWG, max.	AWG 16	Reference to approval values	Specifications are maximum values, details - see approval certificate.

Packing

Packaging	Box	VPE length	350.00 mm
VPE width	139.00 mm	VPE height	41.00 mm

Type tests

Visual and dimensional test	Standard	IEC 60512-1-1:2002-02	
	Test	dimensional inspection	
	Evaluation	passed	
	Standard	IEC 60512-1-2:2002-02	
	Test	weight check	
	Evaluation	passed	
	Standard	IEC 61984:2001-10 section 6.2	
	Test	visual examination	
	Evaluation	passed	
Test: Durability of markings	Standard	IEC 60068-2-70:1995-12 test Xb	
	Test	mark of origin, type identification, pitch, type of material, date clock, approval marking UL, approval marking CSA	
	Evaluation	available	
	Test	durability	
	Evaluation	passed	
Test: Misengagement (Non- interchangeability)	Standard	IEC 60512-13-5:2006-02	
	Test	180° turned with coding elements, 180° turned without coding elements	
	Evaluation	passed	

Creation date 30.11.2025 06:32:44 MEZ





Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

Technical data

	Test	durability
	Evaluation	passed
Test: Clampable cross section	Standard	IEC 60999-1:1999-11 section 9.1, IEC 60947-1:2011-03 section 8.2.4.5.1
	Conductor type	Type of conductor solid 0.14 mm ² and conductor cross-section
		Type of conductor stranded 0.14 mm ² and conductor cross-section
		Type of conductor solid 1.5 mm ² and conductor cross-section
		Type of conductor stranded 1.5 mm ² and conductor cross-section
		Type of conductor AWG 26/1 and conductor cross-section
		Type of conductor AWG 26/19 and conductor cross-section
		Type of conductor AWG 16/1 and conductor cross-section
		Type of conductor AWG 16/19 and conductor cross-section
	Evaluation	passed
Test for damage to and accidental loosening of conductors	Standard	IEC 60999-1:1999-11 section 9.4 bzw. section 8.10
•	Requirement	0.2 kg
	Conductor type	Type of conductor AWG 26/1 and conductor cross-section
		Type of conductor AWG 26/19 and conductor cross-section
	Evaluation	passed
	Requirement	0.3 kg
	Conductor type	Type of conductor H05V-U0.5 and conductor cross-section
		Type of conductor H05V-K0.5 and conductor cross-section
	Evaluation	passed
	Requirement	0.4 kg
	Conductor type	Type of conductor H07V-U1.5 and conductor cross-section
		Type of conductor H07V-K1.5 and conductor cross-section
		Type of conductor AWG 16/1 and conductor cross-section
		Type of conductor AWG 16/19 and conductor cross-section
	Evaluation	passed
D. II	Standard	IEC 60999-1:1999-11 section 9.5
Pull-out test	Staridard	1EC 00333-1.1333-11 300tion 3.3



Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

Technical data

Conductor type	Type of conductor and conductor cross-section	AWG 26/1
	Type of conductor and conductor cross-section	AWG 26/19
Evaluation	passed	
Requirement	≥20 N	
Conductor type	Type of conductor and conductor cross- section	H05V-U0.5
	Type of conductor and conductor cross-section	H05V-K0.5
Evaluation	passed	
Requirement	≥40 N	
Conductor type	Type of conductor and conductor cross-section	H07V-U1.5
	Type of conductor and conductor cross-section	H07V-K1.5
	Type of conductor and conductor cross-section	AWG 16/1
	Type of conductor and conductor cross-section	AWG 16/19
Evaluation	passed	

Important note

IPC conformity

Conformity: The products are developed, manufactured and delivered according international recognized standards and norms and comply with the assured properties in the data sheet resp. fulfill decorative properties in accordance with IPC-A-610 "Class 2". Further claims on the products can be evaluated on request.

Notes

- Additional variants on request
- Gold-plated contact surfaces on request
- Rated current related to rated cross-section & min. No. of poles.
- Wire end ferrule without plastic collar to DIN 46228/1
- Wire end ferrule with plastic collar to DIN 46228/4
- P on drawing = pitch
- Rated data refer only to the component itself. Clearance and creepage distances to other components are to be designed in accordance with the relevant application standards.
- In accordance with IEC 61984, OMNIMATE-connectors are connectors without breaking capacity (COC). During designated use, connectors are not allowed to be engaged or disengaged when live or under load
- Long term storage of the product with average temperature of 50 °C and maximum humidity 70%, 36 months

Classifications

ETIM 6.0	EC002638	ETIM 7.0	EC002638
ETIM 8.0	EC002638	ETIM 9.0	EC002638
ETIM 10.0	EC002638	ECLASS 9.0	27-44-03-09
ECLASS 9.1	27-44-03-09	ECLASS 10.0	27-44-03-09
ECLASS 11.0	27-46-02-02	ECLASS 12.0	27-46-02-02
ECLASS 13.0	27-46-02-02	ECLASS 14.0	27-46-02-02
ECLASS 15.0	27-46-02-02		

Creation date 30.11.2025 06:32:44 MEZ



Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany


www.weidmueller.com

Drawings


Product image




Dimensional drawing



Derating curve



Derating curve



Product benefits



Solid PUSH IN contactSafe and durable