

**WIL-LWXXXX-6500D024-240MFX1.5BXXXXXXXXXX**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)



The WIL-LED lights family: Only 8mm (9.4mm with magnet) high LED lamp for 24V DC with very high luminous efficacy and high lifespan (greater 60 000h). Very robust construction, by full potting and metal housing - waterproof (IP67). Due to its 6500K light color (daylight) suitable for the various applications. Optionally easily connectable with M12 connection. Due to the low power consumption, a small enough power supply with 24V for operation.

**General ordering data**

Order No.	2527920000
Type	<a href="#">WIL-LWXXXX-6500D024-240M-FX1.5BXXXXXXXXXX</a>
GTIN (EAN)	4050118538908
Qty.	1 items

WIL-LWXXXX-6500D024-240MFX 1.5BXXXXXXXXXX

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technical data

### Approvals

Approvals



ROHS Conform

UL File Number Search [UL Website](#)

Certificate no. (cULus) E354496

### Dimensions and weights

Depth	40 mm	Depth (inches)	1.5748 inch
Height	9.5 mm	Height (inches)	0.374 inch
Width	240 mm	Width (inches)	9.4488 inch
Net weight	150 g		

### Temperatures

Operating temperature -20 - 60°C

### Environmental Product Compliance

RoHS Compliance Status Compliant without exemption

REACH SVHC No SVHC above 0.1 wt%

EPREL Registration number 1326381

### Cable technical specifications

Cable Material	PUR	Sheathing colour	black
Housing main material	hard anodised aluminium	Cable length	1.5 m
Core cross-section	0.34 mm <sup>2</sup>		

### Connection data

LED Modul is attachable	no	Version	Cable end open
Number of poles	2	Coding	none
Connection thread	without	Wiring	Pin 4 (Strand: black) control white LED, Pin 3 (Strand: blue)

### Electric data

Rated voltage	24 V DC	Rated current	0.31 A
Power	7.5 W	Dimmable	Yes

### General technical data

Type of connection	Pre-assembled cable	Electronic equipment on rolling stock	No
Recommended class according to UL for NEC Class 2 use of an power supply		Shape of the LED module	Rectangular
Number of LEDs	14	Light colour (CCT)	6500K, White
Luminosity	3470 cd	Light current	886 lm
Emitting angle	40 °	Illumination level	291 lux
Operating life	60.000 h	Type of mounting	Screw mounting, Magnet

**WIL-LWXXXX-6500D024-240MFX1.5BXXXXXXXXXX**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Technical data

Drill hole spacing	225 mm	Impact resistance	IK05
Protection degree	IP67	Efficiency class (according to EU Directive No. 874/2012)	Not required

### Material data

Material of LED cover	ESG	Housing main material	hard anodised aluminium
Material of end caps	PBT		

### Classifications

ETIM 8.0	EC000996	ETIM 9.0	EC000996
ETIM 10.0	EC000996	ECLASS 14.0	27-11-06-35
ECLASS 15.0	27-11-06-35		

WIL-LWXXXX-6500D024-240MFX1.5BXXXXXXXXXX

Weidmüller Interface GmbH & Co. KG  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

Drawings

www.weidmueller.com

Dimensioned drawing



Detailed drawing



WIL-LWXXXX-6500D024-240MFX 1.5BXXXXXXXXXX

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Accessories

### PUR halogen-free black (U)



Sensor/actuator cables are used for wiring sensors and actuators and for transmitting data or power in various applications. The moulded cable offers connected and tested connection of the plug-in connector to the cable ex-works. The cables may be exposed to a wide range of conditions, such as humidity, dust, heat, cold, shock or vibration.

Our developers have focused specifically on this issue and designed a host of different M8 and M12 sensor-actuator cables so you are bound to find the solution you need for your application.

The M8 and M12 sensor-actuator cables are supplied as standard with brass nickel-plated nuts. However if you are looking to use our products in an extremely harsh environment, we can also supply a variant with a plastic nut. This enables use in environments where cables with nickel-plated M8 and M12 nuts would rust.

Is there something you have not managed to find or you feel needs explanation? Talk to us!

### General ordering data

Type	SAIP-M12BG-3-3.0U	Version
Order No.	<a href="#">1108730300</a>	Sensor/actuator line, One end without connector, M12, Number of
GTIN (EAN)	4032248888481	poles : 3, 3 m, Female socket, straight, Shielded: No, LED: No, Sheath
Qty.	1 ST	material: PUR, Halogen: No
Type	SAIL-M12BG-3-3.0U	Version
Order No.	<a href="#">9457820300</a>	Sensor/actuator line, One end without connector, M12, Number of
GTIN (EAN)	4032248228195	poles : 3, 3 m, Female socket, straight, Shielded: No, LED: No, Sheath
Qty.	1 ST	material: PUR, Halogen: No

### Screw terminal connector



Individual cable lengths are often required nowadays. In order to meet these demands, Weidmüller offers a wide range of plug-in connectors for custom assembly. Male plugs and female socket for customisable assembly for M8, M12, M16 and 7/8" connections which are highly robust and ideally suited to machine engineering, for instance. The M12 plug-in connectors offer a choice of 5 different connection systems.

The screw connection can be used in a wide range of applications. With this technology the conductor, optionally with wire-end ferrules, can be plugged into connection elements and secured with a screw. It is the classic, cheapest form of connection technology that also supports multi-conductor connections.

### General ordering data

Type	SAIBGS-P-4A-4/6-M12	Version
Order No.	<a href="#">9457240000</a>	Field attachable connector, M12
GTIN (EAN)	4008190312275	
Qty.	1 ST	

## WIL-LWXXXX-6500D024-240MFX 1.5BXXXXXXXXXX

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Accessories

Type	SAISGS-P-4A-4/6-M12	Version	
Order No.	<a href="#">9457550000</a>	Field attachable connector, M12	
GTIN (EAN)	4032248167647		
Qty.	1 ST		

### Motion sensor screw connection



Motion detector for the WIL-LED luminaire with screw connection. Switching time adjustable.

### General ordering data

Type	WIL-BM-SK	Version	
Order No.	<a href="#">2537720000</a>		
GTIN (EAN)	4050118549157		
Qty.	1 ST		

### Motion sensor screw connection with cable



Motion detector for the WIL-LED luminaire with screw connection, 3m supply cable and M12 cable for connection to the WIL lamp. Switching time adjustable.

### General ordering data

Type	WIL-BM-SK-M12-3.0U	Version	
Order No.	<a href="#">2537700000</a>		
GTIN (EAN)	4050118549140		
Qty.	1 ST		

**WIL-LWXXXX-6500D024-240MFX1.5BXXXXXXXXXX**
**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Accessories

### Motion sensor Jackpac®



Motion detector for the WIL-LED luminaire with screw connection, 3m supply cable and M12 cable for connection to the WIL lamp. Switching time adjustable.

#### General ordering data

Type	WIL-BM-JP-M12-3.0U	Version	
Order No.	<a href="#">2537710000</a>		
GTIN (EAN)	4050118549164		
Qty.	1 ST		

### Door switch



The WIL door switch is pre-assembled with an M12 cable and an access line. This allows for a simple Plug and Produce feature with our WIL LED lamp series.

## Door Switch

#### General ordering data

Type	WIL-TS-M12	Version	
Order No.	<a href="#">2537730000</a>		
GTIN (EAN)	4050118549188		
Qty.	1 ST		

### Swivelling holder



Swivel bracket for WIL lights Very high quality version without detent

## Swivelling holder

#### General ordering data

Type	WIL-SCHWENKHALTER	Version	
Order No.	<a href="#">2614220000</a>		
GTIN (EAN)	4050118651249		
Qty.	1 ST		

## WIL-LWXXX-6500D024-240MFX1.5BXXXXXXXXXX

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Accessories

### WIL power supply



Power supply IP65 for WIL standard family 85V-264V AC input, 24V DC output 400mA

## Power Supply

### General ordering data

Type	WIL-NT-STANDARD	Version	
Order No.	<a href="#">2598350000</a>		
GTIN (EAN)	4050118611168		
Qty.	1 ST		

### Connect Power INSTA POWER



The single-phase INSTA-POWER switching power supplies are characterised by a wide power spectrum, compact design and good value for money. They are suitable for temperature ranges from -25°C to +70°C, have international approvals and a wide voltage input range. This makes them suitable for a wide range of applications. This also includes signal and telecommunications systems as well as automation systems with a low power requirement up to 96 Watt.

### General ordering data

Type	PRO INSTA 30W 24V 1.3A	Version	
Order No.	<a href="#">2580190000</a>	Power supply, switch-mode power supply unit, 24 V	
GTIN (EAN)	4050118590920		
Qty.	1 ST		