

## VPU PV I+II 0 1000

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)



### General ordering data

Version	Surge voltage arrester, Low voltage, Accessories, Surge protection I / II, Spare arrester
Order No.	<a href="#">2530600000</a>
Type	VPU PV I+II 0 1000
GTIN (EAN)	4050118540819
Qty.	9 items

## VPU PV I+II 0 1000

Weidmüller Interface GmbH & Co. KG  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

www.weidmueller.com

## Technical data

## Approvals

Approvals



ROHS Conform

UL File Number Search [UL Website](#)

Certificate No. (cURus) E354261

## Dimensions and weights

Depth	73.5 mm	Depth (inches)	2.8937 inch
Height	45 mm	Height (inches)	1.7716 inch
Width	18 mm	Width (inches)	0.7087 inch
Net weight	89 g		

## Temperatures

Storage temperature	-40 °C...85 °C	Operating temperature	-40 °C...85 °C
Humidity	5 - 95% rel. humidity		

## Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

## Rated data UL

Ambient temperature (operational), max. 85 °C	Rated Voltage UN	550 V
SCCR	In	20 kA
Category	Ambient temperature (operational), min. -40 °C	
Certificate No. (cURus)	VPR ( DC+/DC-)	2500 V
Voltage type	DC	

## General data

Optical function display	green = OK; red = arrester is defective - replace	Version	Surge protection I / II, Spare arrester
Design	Installation housing; 1TE	UL 94 flammability rating	V-0
Colour	orange	Protection degree	IP20
Operating altitude	≤ 4000 m		

## Insulation coordination acc. to EN 50178

Surge voltage category	III	Pollution severity	2
------------------------	-----	--------------------	---

## Photovoltaic technical data

Standards	EN 61643-31, EN 50539-11, UL 1449	Lightning test current Iimp (10/350 μs)	6.25 kA
Protection level Up (+/-, -/PE, +/-PE)	≤ 3.8 kV	Short-circuit current ISCPV	11000 A
Total discharge current Itotal ( 8/20μs)	50 kA	Discharge current In (8/20 μs)	20 kA
Requirements class	Type I/II	Operating height in the grounded PV system	≤ 2000 m
Total discharge current Itotal (10/350μs)	12.5 kA	PV system voltage, max. Ucpv	1100 V

## VPU PV I+II 0 1000

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Technical data

### Rated data IEC / EN

Number of poles	1	Leakage current at Un	30 µA
Signalling contact	No	Voltage type	DC
Fuse protection	No	Response time / fallback time	≤ 25 ns
Standards	EN 61643-31, EN 50539-11, UL 1449	Lightning test current Iimp (10/350 µs)	6.25 kA
Energy coordination (≤10 m)	Type I, Type II, Type III	SPD type	T1, T2
Integrated back-up fuse	No		

### Connection data

Stripping length	18 mm	Type of connection	pluggable
Wire cross-section, solid, min.	1.5 mm <sup>2</sup>	Wire cross-section, solid, max.	35 mm <sup>2</sup>
Wire connection cross section, finely stranded, max.	35 mm <sup>2</sup>		

### Electrical data

Voltage type	DC		
--------------	----	--	--

### General data

Number of poles	1	Protection degree	IP20
Colour	orange		

### Guarantee


Time interval	5 years		
---------------	---------	--	--

### Classifications

ETIM 8.0	EC001457	ETIM 9.0	EC001457
ETIM 10.0	EC001457	ECLASS 14.0	27-17-14-03
ECLASS 15.0	27-17-14-03		

Drawings

Electric symbol



Circuit diagram

## Accessories

### Crosshead screwdriver Phillips



VDE insulated crosshead screwdriver, for Phillips screws, SDIK PH DIN 7438, ISO 8764/2-PH, output to ISO 8764-PH, SoftFinish grip

#### General ordering data

Type	SDIK PH1 X 80	Version	
Order No.	<a href="#">2749890000</a>	Screwdriver, Blade width (B): 1 mm, 80 mm, Blade thickness (A): 1	
GTIN (EAN)	4050118897098		
Qty.	1 ST		

### Slotted screwdriver




VDE insulated slot-head screwdriver, SDI DIN 7437, ISO 2380/2, drive output acc. to DIN 5264, ISO 2380/1. SoftFinish grip

#### General ordering data

Type	SDIS 1.0X5.5X125	Version	
Order No.	<a href="#">2749850000</a>	Screwdriver, Blade width (B): 5.5 mm, Blade length: 125 mm, Blade thickness (A): 1 mm	
GTIN (EAN)	4050118897050		
Qty.	1 ST		

### Blank



ESG is the tried-and-tested marker in MultiCard format for use on many well-known electrical devices. The result is high-quality device marking with a high-contrast appearance.

Various types are available for devices from manufacturers like Siemens, ABB, Beckhoff etc.

Advantages at a glance:

- Tags for universal usage, self-adhesive or clip-on tags, depending on type
- For aligned equipment, e.g. circuit breakers, we supply ESG markers for clipping onto tag rails
- Individual laser-quality printing according to specifications

For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

## VPU PV I+II 0 1000

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Accessories

### General ordering data

Type	ESG 6/15 K MC NE WS	Version	
Order No.	<a href="#">1880100000</a>	ESG, Device markers x 15 mm, PA 66, Colour: white, Self-adhesive	
GTIN (EAN)	4032248478781		
Qty.	200 ST		

### VPU Series



Extensive accessories round off the product range

### General ordering data

Type	VPU LOCKING CLIP L	Version	
Order No.	<a href="#">2735070000</a>		
GTIN (EAN)	4050118816402		
Qty.	10 ST		