

THM ET DIA 55 WS

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



The THM labels offer brilliant printing quality thanks to the thermal transfer technology. Different materials and the user-friendly printing system M-Print® PRO under Windows optimise all labelling efforts.

- High-quality polyester labels in different colours
- Due to their flexible material and the thick adhesive layer, the THM GEW can be used on angled or round objects such as cables or hoses
- Roll-packaged THM ET S7 can be used to label the Simatic 200S, S7-300 and S7-400 modules from Siemens
- Labels are automatically positioned in the printer for perfectly centred prints on each label.
- Labelling with the THM MultiMark or THM MultiMark Plus thermal transfer printers

General ordering data

Version	Conductor and cable markers, white
Order No.	2539400000
Type	THM ET DIA 55 WS
GTIN (EAN)	4050118570168
Qty.	1000 items

THM ET DIA 55 WS

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

ROHS Conform

Dimensions and weights

Depth	0.35 mm	Depth (inches)	0.0138 inch
Diameter	55 mm	Net weight	1.07 g

Temperatures

Operating temperature range	-50...100 °C	Continuous operating temp., min.	-50 °C
Continuous operating temp., max.	100 °C		

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

General data

Version	Self-adhesive	UL 94 flammability rating	HB
Operating temperature range, max.	100 °C	Operating temperature range, min.	-50 °C
Colour	white	Halogen	No
Basic material	Polypropylene	Printed characters	without
Operating temperature range	-50...100 °C		

Conductor and cable markers

Halogen No

Classifications

ETIM 8.0	EC001288	ETIM 9.0	EC001288
ETIM 10.0	EC001288	ECLASS 14.0	27-28-11-04
ECLASS 15.0	27-28-11-04		

